

Kit 71090089: Maintenance Kit Oxymax H COS22Z



Depending on the configuration you will get one of the following parts optional:

- Electrolyte 25 ml for COS22D/E standard or trace
- Inner glass body COS22D/E standard or trace
- Shaft sleeve

Kit Content	Pcs.	Pos.
Process Sealing (FKM or FKM Ex)	3/10	a
O-Rings (EPDM/FDA FKM or FFKM)	3/10	b
Disassembly- and O-ring assembly tool	1	c
Membrane Bodies	3/10	d
Optional: Shaft sleeve	1	e
Optional: Inner glass body COS22D/E standard or trace	1	f
Optional: Electrolyte 25ml for COS22D/E standard or trace	1	g