



OFFICIAL LISTING

NSF certifies that the products appearing on this Listing conform to the requirements of
NSF/ANSI/CAN 61 - Drinking Water System Components - Health Effects

This is the Official Listing recorded on March 12, 2025.

Endress + Hauser SE + Co. KG
Hauptstrasse1
79689 Maulburg
Germany
49 7622 28 1957

Endress+Hauser 
People for Process Automation

Facility: Maulburg, Germany

Mechanical Devices

Trade Name	Size	Water Contact Temp	Water Contact Material
Switches/Sensors^[1]			
Cerabar M PMC51	[2]	CLD 23	MLTPL
Cerabar M PMC51B	[2]	CLD 23	MLTPL
Cerabar M PMP51	[2]	CLD 23	MLTPL
Cerabar M PMP51B	[2]	CLD 23	MLTPL
Cerabar PMC43	[2]	CLD 23	MLTPL
Cerabar PMP43	[2]	CLD 23	MLTPL
Cerabar S PMC71	[2]	CLD 23	MLTPL
Cerabar S PMC71B	[2]	CLD 23	MLTPL
Cerabar S PMP71	[2]	CLD 23	MLTPL
Cerabar S PMP71B	[2]	CLD 23	MLTPL
Deltabar FMD71	[5]	CLD 23	MLTPL
Deltabar FMD72	[5]	CLD 23	MLTPL
Deltabar M PMD55	170mm x 122mmx 104mm	CLD 23	MLTPL
Deltabar M PMD55B	[5]	CLD 23	MLTPL
Deltabar PMD71B	[5]	CLD 23	MLTPL
Deltabar PMD72B	[5]	CLD 23	MLTPL
Deltabar S PMD75	223mm x 155mmx 127mm	CLD 23	MLTPL
Deltabar S PMD75B	[5]	CLD 23	MLTPL
Deltabar S PMD78B	[5]	CLD 23	MLTPL
Deltapilot M FMB50	[3]	CLD 23	MLTPL
Deltapilot M FMB51	[4]	CLD 23	MLTPL
Deltapilot M FMB52	43 mm x 236 mm	CLD 23	MLTPL
Deltapilot M FMB53	43 mm x 236 mm	CLD 23	MLTPL
Deltapilot S FMB70	[3]	CLD 23	MLTPL
Micropilot FMR20B ^[6]	1.5-3in	CLD 23	
Micropilot FMR30B ^[6]	1.5-3in	CLD 23	
Waterpilot FMX 167	22 mm x 220 mm	CLD 23	MLTPL
Waterpilot FMX21	22 mm x 259 mm	CLD 23	MLTPL

[1] Certified for a minimum flow rate of 10,000 L/day.

[2] All Cerabar models

Note: Additions shall not be made to this document without prior evaluation and acceptance by NSF International.



G 1/2" - 2"
1/2" - 2" NPT
Flanges DN25 - DN80 (1" - 4")
Flange DN25 - DN80 (1" to 3")
Thread G 1/2" - 2"
Thread MNPT1/2"-2"
Thread M20x1.5
NEUMO BioControl DN25 - DN 80
Ingeldstutzen
Aseptoflex
DIN11851 DN25 - DN80
DRD Connection
SMS Connection 1" - 2"
Varivent F and N
Tri-Clamp DN18 - DN76.1 (3/4" - 3")

[3] Deltapilot S FMB70 and Deltapilot M FMB50:
G 1 1/2"
1 1/2" NPT
Flanges DN40 - DN100 (1 1/2" - 4")
Sanitary connections DN40 - DN50 (1 1/2" - 2")

[4] Deltapilot M FMB51:
G 1 1/2"
1 1/2" NPT
Flanges DN40 - DN100 (2" - 4")
Rod length up to 4m

[5] All Deltabar models:
1/4" NPT
1/4" RC

[6] Certified for use in tanks 5 gallons and greater.

NOTE: Only products bearing the NSF Mark on the product, product packaging, and/or documentation shipped with the product are Certified.

Facility: Greenwood, IN

Mechanical Devices

Trade Name	Size	Water Contact Temp	Water Contact Material
Switches/Sensors ^{[1] [2]}			
Cerabar M PMC51	[3]	CLD 23	MLTPL
Cerabar M PMC51B	[3]	CLD 23	MLTPL
Cerabar M PMP51	[3]	CLD 23	MLTPL
Cerabar M PMP51B	[3]	CLD 23	MLTPL
Cerabar S PMC71	[3]	CLD 23	MLTPL
Cerabar S PMC71B	[3]	CLD 23	MLTPL
Cerabar S PMP71	[3]	CLD 23	MLTPL
Cerabar S PMP71B	[3]	CLD 23	MLTPL
Deltabar FMD71	[6]	CLD 23	MLTPL
Deltabar FMD72	[6]	CLD 23	MLTPL
Deltabar M PMD55 ^[6]	17 mm x 122mmx 104mm	CLD 23	MLTPL
Deltabar M PMD55B	[6]	CLD 23	MLTPL
Deltabar PMD71B	[6]	CLD 23	MLTPL
Deltabar PMD72B	[6]	CLD 23	MLTPL
Deltabar S PMD75 ^[6]	223mmx 155mmx 127mm	CLD 23	MLTPL
Deltabar S PMD75B	[6]	CLD 23	MLTPL
Deltabar S PMD78B	[6]	CLD 23	MLTPL
Deltapilot M FMB50	[5]	CLD 23	MLTPL
Deltapilot M FMB51	[4]	CLD 23	MLTPL
Deltapilot M FMB52	43 mm x 236 mm	CLD 23	MLTPL
Deltapilot M FMB53	43 mm x 236 mm	CLD 23	MLTPL
Deltapilot S FMB70	[5]	CLD 23	MLTPL

Note: Additions shall not be made to this document without prior evaluation and acceptance by NSF International.



Micropilot FMR200 ^[7]	1.5-3in	CLD 23	
Micropilot FMR300 ^[7]	1.5-3in	CLD 23	
Waterpilot FMX 167	22 mm x 220 mm	CLD 23	MLTPL
Waterpilot FMX21	22 mm x 259 mm	CLD 23	MLTPL

[1] Certified for a minimum flow rate of 10,000 L/day.

[2] Only products bearing the NSF Mark on the product, product packaging, and/or documentation shipped with the product are Certified.

[3] All Cerabar models
G 1/2" - 2"
1/2" - 2" NPT
Flanges DN25 - DN80 (1" - 4")

[4] Deltapilot M FMB51:
G 1 1/2"
1 1/2" NPT
Flanges DN40 - DN100 (2" - 4")
Rod length up to 4m

[5] Deltapilot S FMB70 and Deltapilot M FMB50:
G 1 1/2"
1 1/2" NPT
Flanges DN40 - DN100 (1 1/2" - 4")
Sanitary connections DN40 - DN50 (1 1/2" - 2")

[6] All Deltabar models:
1/4" NPT
1/4" RC

[7] Certified for use in tanks 5 gallons and greater.

Note: Additions shall not be made to this document without prior evaluation and acceptance by NSF International.