



Notes

1. Control room equipment may not use or generate voltages over 250 VRMS
2. Install per the national electrical code (NEC)
3. Warning: Substitution of components may impair intrinsic safety.

The relation between maximum process fluid temperature, ambient temperature and temperature class is shown in following table:

Temperature class	Max. process fluid temperature	Max. ambient temperature of the electronic insert
T6	85°C	70°C
T5	100°C	70°C
T4	135°C	70°C
T3	200°C	70°C

Agency controlled drawing.
No changes without prior
Agency approval.

ZD 023F/00/en/10.98/EHF
FM / A 24.10.97



Control drawing
960383-0017 A

Multicap
Separate enclosure

Endress + Hauser

