Safety Instructions **Memograph M, RSG45**

Advanced Data Manager

ATEX: Ex pxb IIC Gb

Ex pxb IIIC Db

Safety instructions for electrical apparatus

in explosion-hazardous areas







Memograph M, RSG45 XA01362R

Memograph M, RSG45

Advanced Data Manager

Table of contents

About this document
Associated documentation
Supplementary documentation
Manufacturer's certificates5
Manufacturer address
Safety instructions: 5
Safety instructions: Installation
Safety instructions: Special conditions \ldots 6
Temperature tables
Electrical connection data 6

Endress+Hauser 3

XA01362R Memograph M, RSG45


About this document



This document has been translated into several languages. Legally determined is solely the English source text.

The document translated into EU languages is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Manuals and Datasheets -> Type: Ex Safety Instruction (XA) -> Text Search: ...
- In the Device Viewer: www.endress.com -> Product tools -> Access device specific information -> Check device features



Associated documentation

This document is an integral part of the following Operating Instructions:

• Operating instructions: BA01338R

Brief operating instructions: KA01177R

■ Technical information: TI01180R

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

In the download area of the Endress+Hauser website:
www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP000217.

• On the CD for devices with CD-based documentation

4 Endress+Hauser

Memograph M, RSG45 XA01362R

Manufacturer's certificates

ATEX certificate

Certificate number: EPS 15 ATEX 1 810 U

EU Declaration of Conformity Declaration number: EC_00066


Manufacturer address

Endress+Hauser Wetzer GmbH + Co. KG

Obere Wank 1

87484 Nesselwang, Germany

Safety instructions:



 $\blacksquare 1$ Installation of the Advanced Data Manager

Endress+Hauser 5

A0050435

XAO1362R Memograph M, RSG45

Safety instructions: Installation

- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and any other valid standards and regulations (e.g. EN/IEC 60079-14).
- The housing of the Advanced Data Manager must be connected to the potential matching line.
- The Advanced Data Manager is suitable for installation in a certified cabinet with "px" or "pz" or "py" type of protection.
- The permitted operating temperature range (inside and outside) is -10 to +50°C.
- When mounting the front, ensure that IP65 protection as per EN/IEC 60529 is maintained

Safety instructions: Special conditions

- A separate conformity assessment procedure must be performed for the installation of this component.
- Under fault conditions, the temperature outside on the front of the Advanced Data Manager Memograph M, RSG45 reaches a maximum of +65°C.

Temperature tables

Туре	Ambient temperature range
RSG45	-10°C ≤ Ta ≤ +50°C

Electrical connection data

Туре	Electrical connection v	Electrical connection values		
RSG45	Power supply supply voltage:	100 to $230~V_{AC}$ (±10%) / $24~V_{AC/DC}$ (-10%; +15%)		
	Frequency:	50 / 60 Hz		
	Power consumption:	40 VA / 30 VA		

Category	Type of protection (ATEX)	Туре
II2G	Ex pxb IIC Gb	RSG45
II2D	Ex pxb IIIC Db	

6 Endress+Hauser



www.addresses.endress.com