# Technical Information **Dipfit CLA140**

Immersion assembly with flange connection for very demanding processes



# Sensor holder with bayonet lock

## Application

- Chemical industry, e.g. in
  - production of synthetic materials and dyes
  - production or pesticides and fertilizers
  - oil or wastewater separation
  - condensate treatment
- Power stations and incinerator plants, e.g. in
  - cooling water monitoring
  - flue gas cleaning
- Metal extraction and metal processing

#### Your benefits

- Simple installation and removal of the sensor holder thanks to bayonet lock technology
- Reliable sealing even in media containing solid particles
- Suitable for use at high pressures and temperatures
- Immersion depth from 500 to 2500 mm
- Reduced condensation thanks to breathable GORE-TEX® filter
- Variety of flange connections (DIN, ANSI, JIS) for flexible connection to the process

# Function and system design


# Measuring system

A complete measuring system comprises:

- Immersion assembly Dipfit CLA140
- Conductivity sensor with cable, e.g. Indumax CLS50D
- Transmitter, e.g. Liquiline CM442

## Optional:

Extension cable, e.g. CYK11



- $\blacksquare$  1 Example of a measuring system (process and process connections are not illustrated)
- 1 Immersion assembly Dipfit CLA140, here as PVDF version
- 2 Transmitter CM442
- 3 Sensor cable
- 4 CLS50D inductive conductivity sensor

2


# **Environment**

Ambient temperature range	-10 to +70 °C (+10 to +160 °F)
Storage temperature	-10 to +70 °C (+10 to +160 °F)
Degree of protection	IP65

# **Process**

Process temperature	PVDF version Stainless steel version	0 to 120 °C (32 to 250 °F) -15 to 150 °C (5 to 300 °F), for all seals except EPDM -15 to 140 °C (5 to 280 °F), for EPDM seal
Process pressure	PVDF version Stainless steel version	Max. 6 bar (87 psi), absolute Max. 10 bar (145 psi), absolute

# Pressure-temperature ratings




A0037394-Eĭ

- $\blacksquare$  2 Pressure-temperature ratings
- a Stainless steel version
- a PVDF version

# Mechanical construction


#### Design PVDF version



**■** 3 PVDF version

- 1 Dummy plug Pg 16
- 2 Assembly head
- 3
- M4 screws GORE-TEX® filter
- Sensor holder with bayonet lock
- Wrench grip AF55
  Lap joint flange, depending on version
  Cable gland Pg 13.5


## Stainless steel version



€ 4 Stainless steel version

- Dummy plug Pg 16 Assembly head M4 screws 1
- 3
- 4 5
- GORE-TEX® filter Sensor holder with bayonet lock
- 6
- Wrench grip AF55
  Fixed flange, depending on version
  Installation aids (screw-in lifting eyes) 8
- Cable gland Pg 13.5

# Dimensions




**₽** 5 Flange dimensions,  $\rightarrow$  Table

Stainless steel version PVDF version Α


В

	Stainless steel assembly version			PVDF assembly version		
	DN80 PN16	ANSI 3" 150 lbs	JIS 10K 80A	DN80 PN16	ANSI 3" 150 lbs	JIS 10K 80A
a [mm (in)]	18 (0.71)	19 (0.75)	19 (0.75)	18 (0.71)	19 (0.75)	19 (0.75)
b [mm (in)]	20 (0.79)	23.8 (0.94)	18 (0.71)	22 (0.87)	22 (0.87)	18 (0.71)
c [mm (in)]	63.5 (2.50)	63.5 (2.50)	63.5 (2.50)	110 (4.33)	110 (4.33)	110 (4.33)
d [mm (in)]	160 (6.30)	152.4 (6.00)	150 (5.91)	160 (6.30)	152 (5.98)	150 (5.91)
e [mm (in)]	200 (7.87)	190.5 (7.50)	185 (7.28)	200 (7.87)	200 (7.87)	185 (7.28)
Screws	M16	M16	M16	M16	M16	M16
Bore holes	8	4	4	8	4	4



■ 6 Stainless steel version, dimensions in mm (in)

y Immersion depth,  $\rightarrow$  Configurator on product page



■ 7 PVDF version, dimensions in mm (in)

y Immersion depth,  $\rightarrow$  Configurator on product page

Sensor not included in the assembly delivery!

# Weight Depends on version (material, immersion depth):

PVDF 2.5 to 3.0 kg (5.5 to 6.6 lbs) Stainless steel 8.0 to 12.0 kg (17.6 to 26.5 lbs)

# **Materials** In contact with medium, depending on version

Immersion tube	PVDF / stainless steel 1.4404 (AISI 316L)
O-rings	EPDM / VITON / Chemraz / Fluoraz
Sensor holder	PVDF / stainless steel 1.4404 (AISI 316L)

Not in contact with medium, depending on version

Assembly head	PP-GF 20
Lap joint flange	UP-GF / stainless steel 1.4404 (AISI 316L)
Installation aids <sup>1)</sup>	Stainless steel 1.4301 (AISI 304)

Only for stainless steel version

#### **Process connections**

Depending on version:

- None
- Flange DN 80 / PN 16
- Flange ANSI 3" / 150 lbs
- Flange JIS 10K 80A

#### Cable glands

1 x Pg 13.5 and 2 x dummy plug Pg 16

#### Sensor mounting slots

1 x G3/4

#### Immersion depth

Depending on version:

- 500 mm (19.7 in)
- 1000 mm (39.4 in)
- 1500 mm (59.1 in)
- 2000 mm (78.7 in)
- 2500 mm (98.4 in)

# Certificates and approvals

# Pressure Equipment Directive 2014/68/EU

The assembly has been manufactured according to good engineering practice as per Article 4, Paragraph 3 of the Pressure Equipment Directive 2014/68/EU and is therefore not required to bear the CE label.

## Inspection certificate

A test certificate 3.1 in accordance with EN 10204 is supplied depending on the version ( $\rightarrow$  Product Configurator on the product page).

# Ordering information

#### Product page

www.endress.com/cla140

## **Product Configurator**

On the product page there is a **Configure** button to the right of the product image.

- 1. Click this button.
  - ► The Configurator opens in a separate window.
- 2. Select all the options to configure the device in line with your requirements.
  - In this way, you receive a valid and complete order code for the device.
- 3. Export the order code as a PDF or Excel file. To do so, click the appropriate button on the right above the selection window.
- For many products you also have the option of downloading CAD or 2D drawings of the selected product version. Click the **CAD** tab for this and select the desired file type using picklists.

# Scope of delivery

The scope of delivery comprises:

- Ordered version of assembly
- Operating Instructions

► If you have any queries: Please contact your supplier or local sales center.

# Accessories

The following are the most important accessories available at the time this documentation was issued.

► For accessories not listed here, please contact your Service or Sales Center.

#### Indumax CLS50D / CLS50

- High-durability inductive conductivity sensor
- For standard and hazardous area applications
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cls50d or www.endress.com/cls50

