

Company Endress+Hauser Flowtec AG, Kaegenstrasse 7, 4153 Reinach BL1, Switzerland

erklärt als Hersteller, dass die folgenden Durchflussmessgeräte
being the manufacturer, declares that the following flow meters

Product Proline Promass F

Product	Promass F 100/200/300/500 8F1B**-, 8F2B**-, 8F3B**-, 8F5B**-, 08F1B**-, 08F3B**-, 08F5B**-,
product feature	Order code options
060 Measuring tube	Stainless Steel (316L/1.4404/904L/1.4539) options: BC, LA, SA, SB, SC, SD, SE, SF, TS Alloy C22/2.4602 options: HA, TH, TT, TU Special products indicated with 99 on request only
070 Process Connection	All stainless steel (316L/1.4404) connection with pressure rating ≤ 51.7 bar / Cl.300 ≤ 63 bar / PN63 All Alloy C22/2.4602 options with pressure rating ≤ 103.4 bar / Cl600, ≤ 100 bar / PN100 Special products indicated with 999 on request only
570 Service	Verified cleaned, O2 service suitable (wetted parts), declaration; order code option: HB

Proline Promass O

product	Promass O 100/200/300/500 801B**-, 802B**-, 803B**-, 805B**-, 0803B**-, 0805B**-,
product feature	Order code options
060 Measuring tube	All stainless steel (S32750/1.4410), except 99 Special products indicated with 99 on request only
070 Process Connection	All stainless steel (F53/1.4410) with pressure rating < 103.4 bar / Cl600, < 100 bar / PN100 Special products indicated with 999 on request only
570 Service	Verified cleaned, O2 service suitable (wetted parts), declaration; order code option: HB

in den oben dargestellten Produktausprägungen ihre Tauglichkeit für den Einsatz in
Sauerstoffmessung in speziellen Abbrandtests bewiesen haben.

*with configurations mentioned above have proven their suitability for use in oxygen service in
oxygen pressure surge tests.*

Regulation EN ISO 10524-2 Druckminderer zur Verwendung mit medizinischen Gasen - Teil 2 / *Pressure regulators for use with medical gases - Part 2*

Conditions Prüfort / *test location*: WHA INTERNATIONAL, INC., 5605 Dona Ana Road, Las Cruces, NM 88007. Sample Promass F, DN08, 316L/904L, Alloy C22 (Prüfbericht Nr. / *test report no.* **R-WHA-19176-00-A-EX1**).

WHA bestätigt Prüfdurchführung und Prüfergebnisse, die auf alle Gerätegrößen übertragbar sind.

WHA approves test procedure and results which can be extended to all other sizes.

Alle Angaben in der Technischen Information (TI) sind unbedingt vom Betreiber einzuhalten, im Besonderen:

- Druck-/Temperaturkurven
- Druckstufen der Prozessanschlüsse
- gültiger Temperaturbereich von -196°C bis 200°C.


All data of the technical information (TI) must be satisfied by the operator, in particular:

- pressure/temperature curves*
- pressure classes of process connections*
- valid temperature range between -196°C and 200°C*

Dies befreit den Abnehmer insbesondere nicht davon, selbst die Eignung unserer Produkte für den beabsichtigten Verwendungszweck zu prüfen. Diese Herstellererklärung ist nur gültig für Standardprodukte im Auslieferungszustand, die vor dem 31. Dezember 2026 gefertigt werden.

This is to emphasize that the customer is obliged to verify the suitability of our products with regard to the intended application. This declaration of conformity is only valid for standard products in their delivery status produced before December 31st, 2026.

Reinach, 01.03.2021
Endress+Hauser Flowtec AG



S. Anliker
(Direktor Operations/Director Operations)



ppa. Christian Jarms
Bereichsleiter QM/Head of Division Quality Management