

Temperature range

ω

0

O

Ta -20°C ... +50°C ASSOCIATED INTRINSICALLY SAFE

Class I, II, III/ Div. 1+2 / Groups ABCDEFG

Class I, Zone 0 [Ex ia] IIC

ASSOCIATED NONINCENDIVE

Class I / Div. 2 / Groups ABCD

N

Supply L/L+ N/L 20 ... 250VDC/AC 50/60Hz

Ground PE

Output O+ O- 4 ... 20mA

(HART Communication) OH

Output (Terminals +I and -I)

Uo or Voc = 27.3 V Io or Isc = 87.6 mA Po = 597 mW

## Installation Notes RN 221 N

- CSA Approved Apparatus must be installed in accordance with manufacturer's instructions.

- Depending on location install per National Electrical Code (CEC) using wiring methods.

- Use supply wires suitable for 5°C above surroundings.

- Install the device of Protection Ratings of least IP20, NEMA 1, Type 1.

- The active Barrier must be connected to a suitable ground.

## INTRINSICALLY SAFE

Class I / Groups ABCD

- The device is an Associated intrinsically safe equipment and must be installed only in nonhazardous locations.

- Installation should be in accordance with the Canadian Electrical Code (CEC).


For entity installations use certified equipment that satisfy the following condition
 Uo/Voc ≤ Vmax/Ui
 Io/Isc ≤ Imax/Ii
 Po ≤ Pi
 Co/Ca ≥ Ci + Ccable
 Lo/ La ≥ Li + Lcable

- The Terminal of the intrinsically safe circuit must be placed at a distances of least 50mm from terminals of the non intrinsically safe circuits, or adequate separators (e.g. ground metal partitions) must be used.

## NONINCENDIVE Field WIRING INSTALLATION Class I / Div. 2 / Groups ABCD

 The device is an Associated Nonincendive safe equipment and must be installed only in nonhazardous locations.

The Nonincendive Field Wiring Circuit Concept allows interconnection of Nonincendive Field Wiring
Apparatus with Associated Nonincendive Field Wiring Apparatus or Associated Intrinsically Safe Apparatus or
Associated Apparatus not specifically examined in combination as a system using any of the wiring methods
permitted for unclassified locations, when Voc ≤ Vmax, Ca ≥ Ci + Ccable, La ≥ Li + Lcable.



ယ

4

O

0

0