

Temperature range

0

T4 -40°C ... +85°C T5 -40°C ... +70°C T6 -40°C ... +55°C

INTRINSICALLY SAFE NONINCENDIVE, FIELD WIRING IS Class I / Div. 1 / Groups ABCD NI Class I / Div. 2 / Groups ABCD

Sensor circuits (Terminals 3...6)

Uo or Voc or Vt = 6.0 V

In or Isc = 2.5 mA

Po = 3.75 mW

N

Group A, B resp. IIC

Co or Ca = 40μ F

Lo or La = 100 mH

Group C, D resp. IIB, IIA Co or Ca = 1000μ F Lo or La = 100 mH

Installation Notes TMT 182

- FM Approved Apparatus must be installed in accordance with manufacturer instructions.
- Use supply wires suitable for 5°C above surroundings.
- Only simple apparatus should be terminated to the sensor connection. Simple apparatus are components as defined by the NEC (1.2 V, 0.1 A, 0.25 mW or 20 ul).
- Warning: Substitution of components may impair intrinsic safety or suitability for Class I. Division 2.

INTRINSICALLY SAFE

IS Class I / Div. 1 / Groups ABCD

Oi

APPROVED

 \triangleright

ω

0

- Installation should be in accordance with ANSI/ISA RP 12.6.01 "Installation of Intrinsically safe systems for Hazardous (classified) locations" and the National Electrical Code (ANSI/NFPA 70).
- FM Approved Associated Apparatus must meet the following parameters:

 $IJ_0 < IJ_1$ $I_0 < IJ_1$ $P_0 < P_i$ Ca > Ci + Ccable La > Li + Lcable

Transmitter entity parameters are as follows: Ci = 0

Ui or $Vmax \le 30 V DC$

Ii or Imax ≤ 100 mA Li = 0

≤ 750 mW

 Voc + Voc of Handheld device < Vmax, Isc + Isc of Handheld device < Imax, Po + Po of Handheld device < Pi, Ca > Ci + Ccable + Ci of Handheld device, La > Li + Lcable + Li of Handheld device, when Programming Handheld device is used.

NONINCENDIVE

NI Class I / Div. 2 / Groups ABCD

- Depending on location install per National Electrical Code (NEC) using wiring methods described in article 500 through article 510.

Intrinsic safety barrier not required. Vmax \leq 30 V DC.

- Warning: Do not disconnect equipment unless power has been switched off or the area is known to be nonhazardous.
- Nonincendive field wiring installation

The Nonincendive Field Wiring Circuit Concept allows interconnection of Nonincendive Field Wiring Apparatus with Associated Nonincendive Field Wiring Apparatus or Associated Intrinsically Safe Apparatus or Associated Apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations, when $Voc \le Vmax$, $Ca \ge Ci + Ccable$, $La \ge Li + Lcable$. Transmitter Nonincendive Field Wiring parameters are as follows:

Ui or $Vmax \le 30 VDC$

Ci = 0

Ii = 0

4

Ii or Imax = see following note below

For these current controlled circuits, the parameter Imax is not required and need not to be aligned with parameter Isc and It of the Associated Nonincendive Field Wiring Apparatus or Associated Apparatus.

Functional ratings

These ratings do not supersede Hazardous Location values

Unom \leq 30 DC Inom \leq 4 to 20 mA

	Approved	Date (yyyy-mm-dd)	Drawing No.	Dwg.rev.	Revision no.	Revision date (yyyy-mm-dd)	Name	Material	510 04842		\neg
	Kellermann	2001-04-24	14 06 00 111	Α	T04n04	2004-11-20	Meroth	ZD 014R/0	9/en/11.04	Endress+Hauser	
Volume (mm³)	Designed	Date (yyyy-mm-dd)	Unit	Scale	Title						
	Kellermann	2001-04-24	iTEMP TMT182	1:1	CONTRO	ITROL DRAWING FM			ies		
Refer to protection notice ISO 16016	Edge of working parts ISO 13715	Geometrical tolerancing ISO 2768-mH-E	Part No.	Format A4	IS, NI			Objekt version		Endress + Hauser Wetze GmbH+Co. KG Nesselwang/German	

ယ