# Safety Instructions Liquiphant FailSafe FTL80, FTL81, FTL85

Control Drawing NI

**Products** 



Document: XA00675F-B

Safety instructions for electrical apparatus for explosion-hazardous areas classified according to the National Electrical Code (NEC) and Canadian Electrical Code (CEC)



# Liquiphant FailSafe FTL80, FTL81, FTL85

### Table of contents

| Associated documentation                  | 4  |
|---|----|
| Extended order code                       | 4  |
| Class I, Div. 2 and Zone 2 installation   | 6  |
| Process seal                              | 7  |
| Zone concept (X-marking)                  | 7  |
| Explosion protection with heat insulation | 7  |
| Temperature tables                        | 8  |
| Connection data                           | 11 |

### Associated documentation

This document is an integral part of the following Operating Instructions: BA01037F/00

The Operating Instructions pertaining to the device apply.

### Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

### Structure of the extended order code

```
FTL8x - ********** + A*B*C*D*E*F*G*..

Device type Basic specifications Optional specifications
```

### \* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

### Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

### Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = test, certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

### Device type: FTL80, FTL81, FTL82


### Basic specifications

| Position |                       | Selected option |                       | Description  |
|----------|-----------------------|-----------------|-----------------------|--|
| 1, 2     | Approval              | FTL8x:          | FC                    | FM NI, Cl. I, Div. 2, Gr. A-G, T6  |
| 3        | Electronics; Output   | FTL8x:          | S                     | FEL85; 2-wire, 4-20 mA   |
| 4        | Display; Operating    | FTL8x:          | A                     | LED; switch  |
| 5        | Housing               | FTL8x:          | C<br>D<br>E<br>H<br>I | F17 Alu, IP66/67 NEPA Type 4X Encl.<br>F13 Alu, IP66/68 NEPA Type 4X/6P Encl.<br>T13 Alu, separate conn. compartment, IP66/68<br>NEPA Type 4X/6P Encl.<br>F15 316L hygiene, IP66/67 NEPA Type 4X Encl.<br>F27 316L, IP66/68 NEPA Type 4X/6P Encl.  |
| 6        | Electrical Connection | FTL8x:          | A<br>B<br>C<br>D<br>E | Gland M20<br>Thread M20<br>Thread G1/2<br>Thread NPT1/2<br>Thread NPT3/4   |
| 7        | Application           | FTL80:          | A<br>C<br>D           | Process max. 150 °C/302 °F, 64 bar/928 psi<br>Process max. 230 °C/446 °F, 100 bar/1450 psi;<br>incl. gas-tight feed through<br>Process max. 280 °C/536 °F, 100 bar/1450 psi;<br>incl. gas-tight feed through<br>Process max. 300 °C/572 °F, 100 bar/1450 psi   |
|          |                       | FTL81:          | A<br>B<br>C<br>D      | Process max. 150 °C/302 °F, 64 bar/928 psi<br>Process max. 150 °C/302 °F, 100 bar/1450 psi<br>Process max. 230 °C/446 °F, 100 bar/1450 psi;<br>incl. gas-tight feed through<br>Process max. 280 °C/536 °F, 100 bar/1450 psi;<br>incl. gas-tight feed through<br>Process max. 300 °C/572 °F, 100 bar/1450 psi |
|          |                       | FTL85:          | N<br>P<br>T           | ECTFE, Process max. 120 °C/248 °F, 40 bar/580 psi<br>PFA, Process max. 150 °C/302 °F, 40 bar/580 psi<br>Enamel, Process max. 150 °C/302 °F, 25 bar/362 psi   |
| 9        | Surface Refinement    | FTL85:          | N<br>P<br>Q<br>R<br>T | Coating ECTFE Coating PFA (Edlon) Coating PFA (RubyRed) Coating PFA (conductive) Coating Enamel  |

## Optional specifications

| ID |                   | Selected option |                            | Description   |
|----|-------------------|-----------------|----------------------------|---|
| Mx | Sensor Design     | FTL8x:          | MP<br>MR<br>MS             | Ambient temperature -50 °C/-58 °F<br>Temperature separator<br>Pressure tight feed through,<br>incl. temperature separator                                       |
| Nx | Accessory Mounted | FTL8x:          | NA<br>NC<br>ND<br>NE<br>NH | Cover, housing F16 PA, transparent Cover, housing F17 Alu, window Cover, housing F13 Alu, window Cover, housing T13 Alu, window Cover, housing F15 316L, window |

### Installation drawing NI



**1** 

- A Class I, Div. 2, Groups A, B, C, D; Class II, Div. 2, Groups E, F, G; Class III Zone 2, AEx/Ex nA IIC T6
- 1 Power supply, 4...20 mA transmitter
- 2 External load
- 3 4...20 mA
- 4 Supply
- 5 Ground stud
- 6 Endress+Hauser transmitter Liquiphant FailSafe, Nivotester FTL825

Class I, Div. 2 and Zone 2 installation

# NI Class I, Div. 2, Groups A, B, C, D, Class II, Div. 2, Groups E, F, G, Class III; Zone 2 AEx/Ex nA IIC T6 (only for NPT conduit entries)

### Hazardous locations installations

• Installation shall be in accordance with National Electrical Code (NEC) or Canadian Electrical Code (CEC) using wiring methods acceptable for Division/Zone 2.

### Nonincendive Field Wiring (NIFW) installation

- The Nonincendive Field Wiring circuit concept allows interconnection of nonincendive field wiring apparatus with associated nonincendive field wiring apparatus or associated apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations, when the following conditions are met:  $V_{max} \ge V_{oc}$  or  $V_t$ ,  $C_a \ge C_i + C_{cable}$ ,  $L_a \ge L_i + L_{cable}$ .  $\rightarrow \boxminus 11$ , "Connection data" section.
- Warning: Explosion hazard Do not disconnect equipment unless power has been switched off or the area is known to be non-hazardous.
- Warning: Open circuit before removing cover.
- Warning: Substitution of components may impair suitability for Class I, Div. 2.

### Polyester housing

• Not suitable for Class II, Div. 2 application.

### Process seals

### Single/Dual Seal per ANSI/ISA 12.27.01

Single seal device:

• Gas-tight conduit seal not required for FTL80, FTL81, FTL85: For version without gas-tight glass feed-through (Basic specification, Position 7 (Application) = A, B, N, P, T)

• Gas-tight conduit seal not required for FTL80, FTL81: For version with gas-tight glass feed-through (Basic specification, Position 7 (Application) = C, D, Y).

### Zone concept (X-marking)

### Electrostatic/impact sparks

Gas group IIC

• If electrostatic charging of the probe can be avoided (e.g. through friction, cleaning, maintenance, strong medium flow), a probe coated with non-conductive material can be used.

• A probe coated with non-conductive material can be used.

Device type FTL85, Basic specification, Position 9 (Surface Refinement) = N, P, Q

- The probe can be electrostatically charged.
- Warning: Avoid electrostatic charqing of the plastic surfaces, for plastic process connections or plastic coatings.
- Not suitable for dust application.


Basic specification, Position 5 (Housing) = C, D, E

Avoid sparks caused by impact and friction.

### Explosion protection with heat insulation

Device type FTL80, FTL81, Basic specification, Position 7 (Application) = C, D, Y

- While observing the "temperature derating", the device is suitable for process temperatures up to 300 °C (→ 🖺 10).
- When operating, ensure that you rule out contact between hot component surfaces and potentially explosive atmospheres beyond the limits of the corresponding temperature class  $( \rightarrow \cong )$ . Suitable measures: e.g. thermal insulation at container and/or pipes.
- The temperature of 85 °C specified at the reference point may not be exceeded.
- To protect the electronics, observe the specified ambient temperature at the electronics housing.



**2** 

 $T_a$ Ambient temperature

 $T_p$ Process temperature

- 1 Sensor
- 2 Temperature class, e.g. T6
- 3 Housing
- Reference point: max. +85 ℃
- E.g. thermal insulation

### Temperature tables



Note!

Observe the permitted probe temperature range.

### Application in gas

### Ambient temperature electronics

| When used in Zone 2 |  |
|---------------------|--|
| -50+70 °C           |  |

### Process temperature sensor

Device type FTL80, FTL81, Basic specification, Position 7 (Application) = A, B, C, D, Y

| When used in Zone 2 |
|---------------------|
| -50+150 °C (A, B)   |
| −60+230 °C (C)      |
| -60+280 ℃ (D)       |
| -60+300 °C (Y)      |

Device type FTL85, Basic specification, Position 7 (Application) = N, P, T

| When used in Zone 2 |
|---------------------|
| −50+120 °C (N)      |
| −50+150 °C (P, T)   |

### Application in dust

| When used in Zone 22 |                     |  |
|----------------------|---------------------|--|
| T =                  | T <sub>a</sub> +10K |  |
| T <sub>500</sub>     | $= T_a + 30K$       |  |

The dependency of the ambient and process temperatures upon the temperature class:

Device type FTL80, FTL81, Basic specification, Position 7 (Application) = A, B

| Temperature class | Process temperature $T_p$ (process): sensor | Ambient temperature $T_a$ (ambient): electronics  |
|-------------------|---|---|
| T6                | -50+ 85 °C                                  | −50+60 °C   |
| T5                | −50+100 °C                                  | −50+70 °C   |
| T4                | -50+135 ℃                                   | Additional temperature range for sensors with Optional specification $Mx = MR$ , $MS \rightarrow \square$ 3 |
| Т3                | −50+150 °C                                  | opuonai specification wix – wix, wis 7 🖼 5  |


Device type FTL80, FTL81, Basic specification, Position 7 (Application) = C, D, Y

| Temperature class | Process temperature T <sub>p</sub> (process): sensor | Ambient temperature T <sub>a</sub> (ambient): electronics |
|-------------------|--|---|
| Т6                | −60+ 85 °C   | −50+60 °C   |
| T5                | −60+100 °C   | −50+70 °C   |
| T4                | −60+135 °C   | For restrictions $\rightarrow \blacksquare 4$             |
| T3                | −60+200 °C   |   |
| T2                | -60+230 °C (C)<br>-60+280 °C (D)<br>-60+300 °C (Y)   |   |

Device type FTL85, Basic specification, Position 7 (Application) = N, P, T

| Temperature class | Process temperature $T_p$ (process): sensor | Ambient temperature T <sub>a</sub> (ambient): electronics                              |
|-------------------|---|--|
| T6                | −50+ 85 °C                                  | −50+60 °C  |
| T5                | −50+100 °C                                  | −50+70 °C  |
| T4                | −50+120 °C (N)                              | Additional temperature range for sensors with Optional specification Mx = MR, MS → 📵 3 |
| T4                | −50+135 °C (P, T)                           | Optional specification vix – Ivik, Ivis 7 🖶 3  |
| T3                | −50+150 °C (P, T)                           |  |


Device type FTL80, FTL81, Basic specification, Position 7 (Application) = A, B Device type FTL85, Basic specification, Position 7 (Application) = N, P, T



**3** 

- **A** Additional temperature range for sensors with optional specifications Mx = MR, MS
- 1 Temperature separator or pressure tight feed through
- 2  $T_a$  for T6: -50...+60 °C
- 3 ECTFE
- 4 PFA, Enamel

Device type FTL80, FTL81, Basic specification, Position 7 (Application) = C, D, Y



**2**€4

- 1 Temperature separator:
- 1.1 insulated
- 1.2 free-standing
- 2  $T_a$  for T6: -50...+60 °C

### Connection data

Basic specification, Position 1, 2 (Approval) = FC

### Nonincendive

Power supply:

- Intrinsic safety barrier not required
- Endress+Hauser transmitter: Liquiphant FailSafe, Nivotester FailSafe



Note

Only connect the device to terminals 1 and 2 or terminals 2 and 3, respectively.

Field Wiring circuit concept

Class I, Division 2 and Zone 2 installation

Terminal 1 (-) Max. level safety Terminal 2 (+) Terminal 3 (-) Min. level safety

Power supply:

 $U_{max} \le 30 \text{ V DC}$ 

 $I_{max}$  = For these current and voltage controlled circuits, the parameter  $I_{max}$  is not required and need not to be aligned with parameters  $I_{sc}$  and  $I_t$  of the associated nonincendive field wiring or associated apparatus.

effective inner inductance  $L_i$  = 0 mH effective inner capacitance  $C_i \leq$  16 nF

Class II, Class III installation (without barrier)

Terminal 1 (-) Max. level safety Terminal 2 (+)

Terminal 3 (-) Min. level safety

Functional ratings:

 $\begin{array}{l} U_{Nom} \leq 30 \text{ V DC} \\ I_{Nom} = 4...20 \text{ mA} \\ P_{max} \leq 660 \text{ mW} \end{array}$ 



www.addresses.endress.com

