

















Safety Instructions

Proline Prowirl 72, 73

Ex i version

NEPSI Zone 1

Ex documentation

This document is an integral part of the following Operating Instructions:

- BA00084D, Proline Prowirl 72 HART
- BA00085D, Proline Prowirl 72 PROFIBUS PA
- BA00095D, Proline Prowirl 72 FOUNDATION Fieldbus
- BA00094D, Proline Prowirl 73 HART
- BA00093D, Proline Prowirl 73 PROFIBUS PA
- BA00096D, Proline Prowirl 73 FOUNDATION Fieldbus

Contents

General warnings	2
Special conditions	
Installation instructions	2
COC certificates of conformity	3
Description of measuring system	3
Nameplates	4
Type code	5
Temperature table compact version	6
Temperature table remote version	7
Design of measuring system	7
Cable entries	
Cable specification	7
Potential equalization	ς
Electrical connection	ç
Connecting the supply voltage or signal cable	10
Service adapter	1 1
Tasknical Data	1 1





General warnings

- For installation, use and maintenance of the flow meter, the instruction manual and the following standards shall be observed:
 - GB50257-1996 "Code for construction and acceptance of electric device for explosive atmospheres and fire hazard electrical equipment installation engineering"
 - GB3836.13-1997 "Electrical apparatus for explosive gas atmospheres Part 13: Repair and overhaul for apparatus used in explosive gas atmospheres"
 - GB3836.15-2000 "Electrical apparatus for explosive gas atmospheres Part 15: Electrical installations in hazardous area (other than mines)"
 - GB3836.16-2006 "Electrical apparatus for explosive gas atmospheres Part 16: Inspection and maintenance of electrical installation (other than mines)"
- The flow meter shall not be modified in order to ensure the explosion protection performance of the equipment. Any change may impair safety.
- Mounting, electrical installation, commissioning and maintenance of the devices may only be performed by technical staff trained in the area of expolsion protection.
- Compliance with all of the technical data of the device (see nameplate) is mandatory.
- To guarantee resistance to dust and water, the transmitter housing, the connection housing of the remote version and the cable entries must be tightly sealed.
- The device's suitability in the event of gas-air mixture occurring simultaneously requires further assessment.

Special conditions

- Ga/Gb in Ex marking means that the interior of the sensor tube can be used in zone 0, but the enclosure
 which are made of aluminium alloy must be installed. So that, even in the event of rare incidences, ignition
 sources due to impact and friction sparks are excluded.

Installation instructions

- The measuring device must only be used in the permitted temperature class.
 The values of the individual temperature classes can be found in the temperature tables on → \$\bigsim 5\$.
- The cable entries and openings not used must be sealed tight with suitable components.
- The manufacturer's specifications for all devices connected to the intrinsically safe circuits must be taken into consideration.
- To rotate the transmitter housing, please follow the same procedure as for non-Ex versions. The transmitter housing may also be rotated during operation.
- The continuous service temperature of the cable must correspond at least to the temperature range of -40 °C to +10 °C above the ambient temperature present (-40 °C ... (T_a +10 °C)).
- If Prowirl 72 or Prowirl 73 devices are interconnected with certified intrinsically safe circuits of Category ib, explosion group IIC, the explosion protection changes from Ex ia to Ex ib IIC.
- The dielectric strength between the various intrinsically safe circuits must be at least 500 Vrms (affects outputs/inputs: (Prowirl 72****-************A and Prowirl 73****-************A)).
- The device may only be used for fluids against which the wetted materials are sufficiantly resistant.
- The service connector may not be connected in a potentially explosive atmosphere.

COC certificates of conformity

COC certificates of conformity

By affixing the certification number the product conforms with the following standards:

- GB3836.1 2010
- GB3836.4 2010
- GB3836.20 2010

Certification numbers:

■ GYJ12.1048X

Inspection body


NEPSI, National Supervision and Inspection Centre for Explosion Protection and Safety of Instrumentation

Description of measuring system

The measuring system consists of transmitters and sensors.

Two versions are available:

- Compact version: transmitters and sensors form a mechanical unit.
- Remote version: transmitters and sensors are installed separately and connected to each other via connecting cables.



Nameplates

The nameplates, which are mounted in a clearly visible position on the transmitter and sensor, contain all of the relevant information about the measuring system.





Fig. 1: Example for nameplates of a transmitter and of a sensor

- A Transmitter nameplate
- B Sensor nameplate
- 1 Production site
- 2 Transmitter or sensor type
- 3 Order code and serial number
- 4 Power supply
- 5 Output
- 6 Associated Ex documentation
- 7 Year of manufacture
- 8 Type of protection
- *Type of enclosure protection*
- 10 Number of the NEPSI certificate of conformity
- 11 Ambient temperature range
- 12 Maximum cable temperature
- 13 C-Tick symbol
- 14 NEPSI Symbol
- 15 Nominal diameter/nominal pressure
- 16 Calibration factor/zero point
- 17 Materials in contact with the medium
- 18 Sensor seal material
- 19 Fluid temperature range
- 20 Additional specification, e.g. 3.1 = 3.1 certificate for wetted material



Type code

The type code describes the exact design and the equipment of the measuring system. It can be read on the nameplate of the transmitter and sensor and is structured as follows:



Electronics (Item No. 2 in type code $\rightarrow \stackrel{\triangle}{=} 4$)

*	Transmitter	Electronics/housing	
2	Prowirl 72	- Intrinsically safe transmitter electronics	
3	Prowirl 73	munisically sale transmitter electronics	

Approvals (Item No. 13 in type code)

*	Approval	_	Explosion protection G	Certification		
		inputs	Compact	number		
c	Zono 1	A, W	Ex ia IIC T1-T6 Ga/Gb	Ex ia[ia Ga] IIC T6 Gb	Ex ia IIC T1-T6 Ga/Gb	GYI12.1048X
3	Zone 1	Н, К	Ex-ia IIC T1-T4 Ga/Gb	Ex ia[ia Ga] IIC T6 Gb	Ex ia IIC T1-T4 Ga/Gb	G1)12,1040A

Type (compact/remote; Item No. 14 in type code)

*	Туре
A, J	Compact
E, F, K, L, M, N, O, P, Q, R, S, T	Remote

Outputs/inputs (Item No. 18 in type code)

*	Approval
A, W	T1 ~ T6
Н, К	T1 ~ T4

Note!



Temperature table compact version

	T _a	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
	−40 °C +40 °C	80	95	130	195	280	280
Prowirl 72***-**0*******	−40 °C +60 °C	_	95	130	195	280	280
	−40 °C +70 °C	-	_	130	195	280	280
Prowirl 72***-**1******** Prowirl 72***-**2*******	−40 °C +40 °C	80	95	130	195	290	440
Prowirl 72***_**3******** Prowirl 72***_**6********	−40 °C +60 °C	1	95	130	195	290	440
Prowirl 73***_*4******** Prowirl 73***-*2*******	−40 °C +70 °C	-	-	130	195	290	440

Dependency of the minimum fluid temperature $T_{\mbox{\footnotesize{med}}}$ on the DSC sensor:

T _{med} -200 °C	T _{med} -50 °C	T _{med} -40 °C
Prowirl 72***-**1*******	Prowirl 72F***-**6*******	Prowirl 72***-**0*******
Prowirl 72***-**2******		
Prowirl 72***-**3*******		
Prowirl 73***-**4******		
Prowirl 73***-**2*******		

⚠ Warning!



Temperature table remote version

Sensor

Maximum fluid temperature [°C] depending on the ambient temperature T_a and the DSC sensor used (Item No. 9 in the type code $\rightarrow \stackrel{\cong}{=} 4$).

	T _a	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
	−40 °C +40 °C	80	95	130	195	280	280
Prowirl 72***-**0*******	−40 °C +60 °C	_	95	130	195	280	280
	−40 °C +85 °C	_	1	130	195	280	280
Prowirl 72***_**1******** Prowirl 72***_**2*******	−40 °C +40 °C	80	95	130	195	290	440
Prowirl 72***_**3******** Prowirl 72***_**6********	−40 °C +60 °C	_	95	130	195	290	440
Prowirl 73***-*4******* Prowirl 73***-*2*******	−40 °C +85 °C	_	-	130	195	290	440

Dependency of the minimum fluid temperature $T_{\mbox{\scriptsize med}}$ on the DSC sensor:

T _{med} -200 °C	T _{med} -50 °C	T _{med} -40 °C
Prowirl 72***-**1*******	Prowirl 72F***-**6*******	Prowirl 72***-**0*******
Prowirl 72***-**2*******		
Prowirl 72***-**3*******		
Prowirl 73***-**4******		
Prowirl 73***-**2*******		

⚠ Warning!

Transmitter

Fig. 2


The minimum ambient temperature is -40 °C.

The maximum ambient temperature [°C] depending on the device used is:

	T6 (85 °C)	T5 (100 °C)	T4 (135 °C)	T3 (200 °C)	T2 (300 °C)	T1 (450 °C)
Prowirl 72****_**********A Prowirl 72****_*********W Prowirl 73****_*********** Prowirl 73****_********************************	40	60	80	80	80	80
Prowirl 72************************************	_	_	80	80	80	80


Design of measuring system

Compact/remote version design



- A Transmitter housing (compact/remote version)
- B Transmitter housing (remote version)
- C Sensor connection housing (remote version)
- a Screw terminal for connecting to potential matching system
- b Remote version connecting cable (see also below)
- c Terminal/electronics compartment cover (see below)
- d -

Terminal assignment and connection data $\rightarrow \stackrel{\triangle}{=} 8$.



Cable entries

Thread for cable entry M20x1.5 or $\frac{1}{2}$ "-NPT or G $\frac{1}{2}$ ", as required.

Cable specification

The sensor cable connection between the sensor and the transmitter has Ex ia explosion protection.

The maximum capacitance per unit length of the cable connection is $1\mu F/km$.

The maximum inductance of the cable is 1 mH/km.

The maximum inductance of the cable lenght is 100 m.

The cable supplied by Endress+Hauser (max. 30 m) complies with these requirements.

Potential equalization





Caution!


- There must be potential matching along the circuits (inside and outside the hazardous area).
- The transmitter must be safely included in the potential matching system by means of the screw terminal (c) on the outside of the transmitter housing or by means of the corresponding ground terminal in the connection compartment (f).
- Alternatively, the sensor and the transmitter (compact version) or the connection housing of the sensor can
 be included in the potential matching system by means of the pipeline if a ground connection, performed
 as per the specifications, is ensured.

Electrical connection

Connection compartment








PROFIBUS PA

Fig. 6





- e Service connector (see also $\rightarrow \stackrel{ riangle}{=} 9$)
- f HART ground terminal: if the potential matching is routed via the cable and if two cables are used, both cables must be connected to the potential matching system if a connection is not already established to screw terminal (a). PROFIBUS and FOUNDATION Fieldbus: between the stripped fieldbus cable and the ground terminal, the cable shielding must not exceed 5 mm in length
- g HART (one cable): cable for supply voltage and/or pulse output HART (two cables): cable for supply voltage PROFIBUS: cable of input and output circuits) FOUNDATION Fieldbus: cable of input and output circuits
- Optional pulse/frequency output, can also be operated as a status output (not for PROFIBUS PA and FOUNDATION Fieldbus)

Note!

PFM output (pulse/frequency modulation) for Prowirl 73: connection as illustrated in $\rightarrow \square 3$ or $\rightarrow \square 4$; only together with flow computer RMC or RMS 621



Connecting the supply voltage or signal cable

The terminal assignment and the connection data for the supply voltage are identical for all devices, regardless of the device version (type code).

Note

A graphic illustration of the electrical connections is provided on \rightarrow $\stackrel{\text{\tiny le}}{=}$ 7.

Terminal assignment /connection data

Terminals		1 (+) 2 (-)			
Prowirl 72***-***** Prowirl 73****-*****		Transmitter power supply / 420 mA HART			
Intr. safe circuit	ntr. safe circuit Ex ia or Ex ib				
	Ui	30 V			
	Ii	300 mA			
Safety-related values	P _i	1 W			
	L _i	negligible			
	C _i	5.28 nF			

Terminals		1 (+)	2 (-)	3 (+)	4 (-)	
Prowirl 72****-*********A Prowirl 73****-**********A		Transmitter power supply / 420 mA HART		Optional pulse/status output		
Intr. safe circuit		Ex ia or Ex ib		Ex ia or Ex ib		
	Ui	30 V		30 V		
	I _i	300	mA	300	mA	
Safety-related values	Pi	1	W	1	W	
	Li	L _i negligible		negli	negligible	
	C _i	5.28 nF		negligible		

Terminals		1 (+)	2 (-)
Prowirl 72****-***********H Prowirl 73****-********************************		PROFIBUS PA	
Intr. safe circuit		Ex ia or Ex ib	
Functional values	U _B	932 V DC	
	I _B	16 mA	
	P	≤ 1 W	
Safety-related values	Ui	17.5 V	
	I _i	500 mA	
	P _i	8.5 W	
	Li	≤ 10 µF	
	C _i	≤ 5 nF	


1 (+)	2 (-)				
PROFIBUS PA					
Ex ia or Ex ib					
932 V DC					
16 mA					
≤ 1 W					
24 V					
250 mA					
1.2 W					
≤ 10 µF					
≤ 5 nF					

Terminals		1 (+)	2 (-)
Prowirl 72****-********K Prowirl 73****-********K		FOUNDATION Fieldbus	
Intr. safe circuit		Ex ia or Ex ib	
Functional values	U_B	932 V DC	
	I_B	16 mA	
	P	≤ 1 W	
Safety-related values	Ui	17.5 V	
	Ii	500 mA	
	P_{i}	5.5 W	
	Li	≤ 10 µF	
	C _i	≤ 5 nF	

1 (+)	2 (-)			
FOUNDATION Fieldbus				
Ex ia or Ex ib				
932 V DC				
16 mA				
≤ 1 W				
24 V				
250 mA				
1.2 W				
\leq 10 μ F				
≤ 5 nF				

or

When the code for outputs/inputs equals "H" or "K" the flow meter meets all requirements for a FISCO Field Device (IEC 600079-27).



Service adapter

The service connector (for connection, see $\rightarrow \bigcirc 3... \rightarrow \bigcirc 7$, e) is only used to connect service interfaces approved by Endress+Hauser.

Only the "PROLINE EX TWO-WIRE CABLE" connecting cable can be used to connect a Prowirl 72 or 73 with the service interface FXA 193.

The service connector may not be connected in a potentially explosive atmosphere.

Technical Data

Dimensions

The dimensions of the Ex transmitter housing and the sensor correspond to the standard versions. Please refer to the respective Technical Information for these dimensions:

• Prowirl 72F, 72W, 73F, 73W: TI00070D

www.endress.com/worldwide



People for Process Automation