

Co or Ca = $160 \mu F$

Co or Ca = $1000 \mu F$

Lo or La = 946 mH

Lo or La = 1.893 H

N

Group C, D resp. IIB

Group C, D resp. IIA

O

Installation Notes TMT82

- CSA approved apparatus must be installed in accordance with manufacturer's instructions.
- Install per Canadian Electrical Code.
- Temperature Sensor assembly must be CSA approved for appropriate area classification.
- Use supply wires suitable for 5°C above surroundings.
- Keep tight when circuits alive.
- Warning: Substitution of components may impair intrinsic safety or suitability for Class I, Division 2.

EXPLOSION PROOF DUST IGNITION PROOF

Class I / Div. 1 / Groups ABCD Class II, III / Div. 1 / Groups EFG CI

0

0

O

- All conduits must be assembled with a minimum of five full threads engagement.
- Seal all conduits within 18 inches of enclosure.
- In Class II use a dust tight seal.
- Warning: Do not disconnect equipment unless power has been switched off or the area is known to be non hazardous.

NONINCENDIVE

Class I / Div. 2 / Groups ABCD

- Intrinsic safety barrier not required.
- Warning: Do not disconnect equipment unless power has been switched off or the area is known to be non hazardous.
- Nonincendive field wiring installation:

The Nonincendive Field Wiring Circuit Concept allows interconnection of Nonincendive Field Wiring Apparatus with Associated Nonincendive Field Wiring Apparatus or Associated Intrinsically Safe Apparatus or Associated Apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations, when $Voc \le Vmax$, $Ca \ge Ci + Ccable$, $La \ge Li + Lcable$.

Transmitter Nonincendive Field Wiring parameters are as follows:

Ui or $Vmax \le 35 \text{ V DC Ci} = 0 \text{ nF Li} = 0$

Ii or Imax = see following note below

For these current controlled circuits, the parameter Imax is not required and need not to be aligned with parameter Isc and It of the Associated Nonincendive Field Wiring Apparatus or Associated Apparatus.

Functional ratings

These ratings do not supersede Hazardous Location values

IJnom < 42 DC Inom < 4 to 20 mA

	Approved	Date (yyyy-mm-dd)	Drawing No.	Dwg.rev.	Revision no.	Revision date (yyyy-mm-dd)	Name	Material 7	71161263		
	Pfanzelt	2011-06-08	34 05 00 114							Endress+Hauser	لنكا
Volume (mm³)	Designed	Date (yyyy-mm-dd)	Unit	Scale	Title		•				
	Pfanzelt	2011-06-06	iTEMP TMT82	1:1	CONTRO	L DRAWING	DRAWING CSA		es		
Refer to protection notice	Edge of working parts	Geometrical tolerancing	Part No.	Format	XP, NI, DI	IP		Objekt version	Sheet	Endress + Hauser We	etzer
ISO 16016	ISO 13715	ISO 2768-mH-E	-	A4	7,,				1 of 1	GmbH+Co. KG Nesselwang / G	

ယ

4

Oi