



IECEx Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification Scheme for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.:	IECEx UL 15.0112X	Issue No: 1	<u>Certificate history:</u> Issue No. 1 (2016-03-10) Issue No. 0 (2015-12-15)
Status:	Current	Page 1 of 4	
Date of Issue:	2016-03-10		
Applicant:	Endress+Hauser Flowtec AG Kaegenstrasse 7, Reinach BL1, CH-4153 Switzerland		
Electrical Apparatus:	Nanomass Density Meter		
<i>Optional accessory:</i>			
Type of Protection:	Intrinsic Safety "ia"		
Marking:	Ex ia IIC T4 Ga Ex ia IIC T4 Gb -20°C ≤ Ta ≤ +60°C		

Approved for issue on behalf of the IECEx
Certification Body:

Lucy Frieders

Position:

Staff Engineer

Signature:
(for printed version)

Date:

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting the [Official IECEx Website](#).

Certificate issued by:

UL LLC
333 Pfingsten Road
Northbrook IL 60062-2096
United States of America





IECEx Certificate of Conformity

Certificate No: IECEx UL 15.0112X

Issue No: 1

Date of Issue: 2016-03-10

Page 2 of 4

Manufacturer: **Endress+Hauser Flowtec AG**
Kaegenstrasse 7,
Reinach BL1, CH-4153
Switzerland

Additional Manufacturing
location(s):

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended.

STANDARDS:

The electrical apparatus and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards:

IEC 60079-0 : 2011 Edition:6.0	Explosive atmospheres - Part 0: General requirements
IEC 60079-11 : 2011 Edition:6.0	Explosive atmospheres - Part 11: Equipment protection by intrinsic safety "i"
IEC 60079-26 : 2006 Edition:2	Explosive atmospheres - Part 26: Equipment with equipment protection level (EPL) Ga

*This Certificate **does not** indicate compliance with electrical safety and performance requirements other than those expressly included in the Standards listed above.*

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in

Test Report:

[US/UL/ExTR15.0128/01](#)

Quality Assessment Report:

[DE/TUN/QAR06.0004/05](#)



IECEx Certificate of Conformity

Certificate No: IECEx UL 15.0112X

Issue No: 1

Date of Issue: 2016-03-10

Page 3 of 4

Schedule

EQUIPMENT:

Equipment and systems covered by this certificate are as follows:

The apparatus is intended to measure the density of liquids and gases

See Annex for additional information.

CONDITIONS OF CERTIFICATION: YES as shown below:

For Zone 0:

The apparatus enclosure contains aluminium. Care must be taken to avoid ignition hazards due to impact or friction.

For Zone 0 and Zone 1:

Disconnect power before servicing.

Do not connect to USB and Power simultaneously.



IECEx Certificate of Conformity

Certificate No: IECEx UL 15.0112X

Issue No: 1

Date of Issue: 2016-03-10

Page 4 of 4

DETAILS OF CERTIFICATE CHANGES (for issues 1 and above):

Issue 1: Update to latest Edition of IEC 60079-11. Revision to construction and documentation not affecting safety.

Annex:

[Annex to IECEx UL 15.0112X Issue 1.pdf](#)

Annex to IECEx UL 15.0112X Issue No.: 1
Applicant: Endress+Hauser Flowtec AG

The model nomenclature is as follows:

Nanomass abcdefghijklmnopqr, where

a	b	c	d	e	f	g	h	i	j	k	l	m	n	o	p	q	r
I	II	III	IV	V	VI	VII	VIII	IX	X	XI	XII	XIII	XIV	XV	XVI	XVII	XVIII

- I. a = Root; DCDB for Liquid Density, DCEB for Gas Density
- II. b = Nominal diameter manifold; alphanumeric characters.
- III. c = Approval; AA = Non-hazardous area, BA = ATEX+IEC II1G Ex ia IIC T4, BB = ATEX+IEC II2G Ex ia IIC T4, 8A = ATEX+IEC II1G Ex ia IIC T4 + UL C/US Class I, Groups A, B, C, D, T4, Class I Zone 0 AEx/Ex ia IIC T4
- IV. d = Power supply, alphanumeric characters.
- V. e = Output, input; A = 2 x 4-20 mA, passive, USB Interface, cable, B = 2 x 4-20 mA, passive, RS 232 plug, C = 2 x 4-20 mA, passive, RS 232, cable, D = 2 x 4-20 mA, passive, RS 232 plug, cable,
- VI. f = Display; alphanumeric characters.
- VII. g = Housing, alphanumeric characters
- VIII. h = Cable; alphanumeric characters.
- IX. i = Electrical connection; alphanumeric characters.
- X. j = Reserved for fluid applications; alphanumeric characters.
- XI. k = Reserved for process connections; alphanumeric characters
- XII. l = Factory calibration density; alphanumeric characters.
- XIII. m = Customized parameters; alphanumeric characters.
- XIV. n = Reserved for functional applications; alphanumeric characters.
- XV. o = Reserved for Test, certificate; alphanumeric characters.
- XVI. p = Additional approval; alphanumeric characters.
- XVII. q = Accessories enclosed; alphanumeric characters.
- XVIII. r = Reserved for customer marking; alphanumeric characters.

The following entity parameters are declared by the manufacturer for the Power input:

$U_i = 30V$, $I_i = 300 \text{ mA}$, $P_i = 1.10W$, $C_i = 55nF$, $L_i = 220\mu H$.

The following entity parameters are declared by the manufacturer for the RS-232 input:

$U_i = 15V$, $I_i = 90mA$, $P_i = 1.10W$, $C_i = 700nF$, $L_i = 1000\mu H$.

The following entity parameters are declared by the manufacturer for the 4-20mA circuits:

$U_i = 30V$, $I_i = 320 \text{ mA}$, $P_i = 1.1W$, $C_i = 48nF$, $L_i = 150\mu H$.

The apparatus has following output entity parameters:

$U_o = 5.88V$, $I_o = 400 \text{ mA}$, $P_o = 0.6W$, $C_o = 41000nF$, $L_o = 20\mu H$

Non Hazardous Location



Appropriate Third Party certified IECEx Barrier or Associated Apparatus

Capped off *

Appropriate Third Party certified IECEx Barrier or Associated Apparatus

Hazardous (Classified) Location

Nanomass: for installation in Zone 0, Zone 1 or Zone 2
Type of explosion protection Ex ia IIC T4 Ga
 $-20^{\circ}\text{C} \leq T_a \leq +60^{\circ}\text{C}$



4-20 mA connector

USB-B connector

Power connector

External sensor connector

4-20 mA connector

Channel 1 Channel 2
1, 2 3, 4
+ - or - +, polarity insensitive
Passive

Mini USB-B connector

Mini USB-B connection

Warnings:

- * Use restricted to E+H Service during production, test, repair or overhaul.
- * USB data download and configuration done only in non-hazardous location.
- Do not have both, power applied and USB connected simultaneously

Power connector

DC 8 – 30 V

External sensor connector

Pins	Pressure	Temperature
1	+ 5VDCout power	Iout
2	V+ (0-4.5 VDC) signal in	V+
3	V- (0 VDC) signal in	V-
4	Ground	Ireturn

Connect simple apparatus

- Or Endress+Hauser UC2 – T3C sensor - cable length max. 30.5 m
- Or Entity parameters: $U_o=5.88\text{ V}$, $I_o=400\text{ mA}$, $P_o=0.6\text{ W}$, $C_o=41000\text{ nF}$, $L_o=20\text{ }\mu\text{H}$
 $P_o = (I_o * U_o) / 4$

Notes : Intrinsically safe installation for type of explosion protection Ex ia IIC T4.

1. Associated apparatus must be installed in accordance with the manufacturer's operation manual and the appropriate national or international standard (e.g. IEC 60079-14)
2. Use entity certified safety barrier or other associated equipment that satisfies the following conditions:
 $U_o \leq U_i$ and $I_o \leq I_i$ and $P_o \leq P_i$ and $C_o \geq C_i + C_{\text{cable}}$ and $L_o \geq L_i + L_{\text{cable}}$
Where C_{cable} and L_{cable} are not know the following parameters shall be used: $C_{\text{cable}}=200\text{ pF/m}$, $L_{\text{cable}}=1000\text{ nH/m}$
3. 4-20 mA circuits should be separated by individually grounded shields.
4. No user replacable parts inside
5. Associated apparatus output current must be limited by a resistor such that the output voltage-current plot has a linear characteristic.
6. Warning: Disconnect power before servicing.
Zone 0 Warning: Apparatus enclosure contains aluminium. Care must be taken to avoid ignition hazards due to impact or friction.
7. For additional product information see FES0254.

Änderungen:

A	20.11.2015 / utz	F
B	17.02.2016 / utz	G
C		H
D		J
E		K

Mat. No.

Ersteller: FES / utz

FILE: M:\ZEICHNUNG\FES0238\B\FES0253B.doc

Entity Parameters

	V_{max}, U_i	I_{max}, I_i	P_i	C_i	L_i
Power	30 V	300 mA	1.1 W	55 nF	0.22 mH
4-20 mA	30 V	320 mA	1.1 W	48 nF	0.15 mH

IECEx Installation Drawing Entity Concept Ex ia IIC T4

Nanomass, USB version

Endress+Hauser

Flowtec AG, Kaegenstrasse 7, CH-4153 Reinach BL1, Postfach

Gezeichnet	17.02.2016	utz
Geprüft		
Ex-geprüft	17.02.2016	utz
Gesehen		

FES0253B

1/1

Nanomass is suitable for density and/or concentration measurement of fluids (< 30 kg/m³)

Nameplate:

The diagram shows a rectangular nameplate for an Endress+Hauser device. It contains the following fields and symbols, numbered 1 through 23:

- 1: Order code
- 2: Ser. no.
- 3: Ext. ord. od.
- 4: FW
- 5: Dev. Rev.
- 6: p max
- 7: Tm/Ta
- 8: Density range
- 9: Suitable medium
- 10: CRN no.
- 11: Warning symbol (triangle with exclamation mark)
- 12: Safety symbol (book icon)
- 13: Date
- 14: 2-D-matrix code
- 15: IP, type of ingress protection
- 16: Manufacturing date: year - month
- 17: Diameter of process connection
- 18: Allowed fluid density range
- 19: Allowed ambient temperature and fluid temperature
- 20: Allowed fluids
- 21: Additional information for special product design
- 22: CE-mark, C-Tick
- 23: Certificate information for type of explosion protection

Contact information: www.addresses.endress.com

Ambient temperature range: -20 ... + 60 °C
Allowed maximum process pressure: 20 bar (290 psi)

Installation shall be done by qualified personnel.
National installation standards shall be observed.
For installation at wall or on solid support, use installation holes and M6 screws. For installation at pole use use pole mounting set.
Normally, the measuring instrument is installed in a bypass.
Mounting in the measuring tube is realized by means of tube fitting.

Maintenance:
Do not clean with high-pressure steam.
External: clean with mild soap solution or similar products.
Internal: clean with isopropanol or similar products.
For repair or alteration follow Endress+Hauser instructions or contact the Endress+Hauser organization. Use only original spare parts.

- 1 Owner of certificate
- 2 Product name
- 3 Order code
- 4 Serial number
- 5 Extended order code
- 6 Electrical ratings: e.g. available I/Os, supply voltage
- 7 Firmware-Version
- 8 Diameter of micro channel
- 9 Maximum nominal system pressure
- 10 Allowed ambient temperature and fluid temperature
- 11 Allowed fluid density range
- 12 Allowed fluids
- 13 Additional information for special product design
- 14 CE-mark, C-Tick
- 15 Additional information on version: certificates, approvals
- 16 Device revision level
- 17 Diameter of process connection
- 18 IP, type of ingress protection
- 19 Manufacturing date: year - month
- 20 2-D-matrix code
- 21 Number of safety relevant document
- 22 Certification information on CRN
- 23 Certificate information for type of explosion protection

By affixing the certification number IECEx UL 15.0112X compliance with the following standards is confirmed:
IEC 60079-0: 2011, IEC 60079-11: 2006 , IEC 60079-26: 2006

A	20.11.2015 / utz	u		Mat. No.
B		G		
C		H		Ersteller: FES / utz
D		J		FILE: M:\ZEICHN\VFES0238\A\FES0254A.doc
E		K		

Operational manual information	Gezeichnet	20.11.2015	utz
	Geprüft		
	Gesehen	20.11.2015	utz

Nanomass	
Endress+Hauser	
Flowtec AG, Kaegenstrasse 7, CH-4153 Reinach BL1, Postfach	

FES0254A	1/1
-----------------	------------