# Technical Information **Memosens CPS76E**

pH/ORP sensor for process technology



### Digital with Memosens 2.0 technology

### Application

Process technology and monitoring of processes with:

- Rapidly changing pH values
- High proportion of electrode poisons such as H<sub>2</sub>S

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals for use in hazardous areas Zone 0, Zone 1 and Zone 2.

### Your benefits

- Simultaneous measurement of pH, ORP and rH value (in rH mode)
- Platinum electrode for measuring reference impedance
- Newly developed, acrylamide-free gel as bridging electrolyte, sterilizable and very resistant to chemical corrosion
- Suitable for CIP/SIP cleaning, autoclavable
- Long service life thanks to poison-resistant reference with ion trap
- Integrated NTC 30K temperature sensor for effective temperature compensation
- Glass breakage and blockage detection by measuring:
  - Resistance of glass membrane
  - Reference impedance

### Other advantages provided by Memosens technology

- $\ \ \, \blacksquare$  Maximum process safety thanks to non-contact, inductive signal transmission
- Data security thanks to digital data transmission
- $\ \ \, \ \ \,$  Very easy to use as sensor data are saved in the sensor
- Predictive maintenance can be performed by recording sensor load data in the sensor



# Function and system design

### Measuring principle

### pH measurement

The pH value is used as a unit of measurement for the acidity or alkalinity of a medium. The membrane glass of the electrode delivers an electrochemical potential that depends on the pH value of the medium. This potential is generated by the selective accumulation of  $H^+$  ions on the outer layer of the membrane. As a result, an electrochemical boundary layer with an electrical potential difference forms at this point. An integrated Ag/AgCl reference system serves as the required reference electrode.

The measured voltage is converted to the corresponding pH value using the Nernst equation.

### **ORP** measurement

The ORP potential is a unit of measurement for the state of equilibria between oxidizing and reducing components of a medium. The ORP is measured using a platinum or gold electrode. Similar to pH measurement, an integrated Aq/AqCl reference system is used as a reference electrode.

### rH measurement

The rH value is defined as the negative logarithm of partial pressure of hydrogen in a solution. The pH value and ORP value of a solution must be measured simultaneously to calculate the rH value. The value is calculated using the following equation:

 $rH = 2 \cdot (mV/S) + 2 pH$ 

рН	Measured pH value	
mV	Measured ORP value in mV + 207 mV (Ag/AgCl system)	
S	Slope of pH electrode	

The rH value is an indicator of the oxidation or reducing power of a process solution. The rH scale runs from 0 to 42.

rH values	Process medium	
0 to 9	Strong reducing power	
9 to 17	Weak reducing power	
17 to 25	Undetermined medium	
25 to 34	Weak oxidizing power	
34 to 42	Strong oxidizing power	


### Measuring system

A complete measuring system comprises:

- pH/ORP sensor CPS76E
- Memosens data cable CYK10 or CYK20
- Transmitter, e.g. Liquiline CM44, Liquiline CM42
- Assembly
  - Immersion assembly, e.g. Dipfit CPA111
  - Flow assembly, e.g. Flowfit CPA250
  - Retractable assembly, e.g. Cleanfit CPA871
  - Permanent installation assembly, e.g. Unifit CPA842

Additional options are available depending on the application:

Automatic cleaning and calibration system, e.g. Liquiline Control CDC90



- **₽** 1 Example of a measuring system for pH measurement
- Retractable assembly Cleanfit CPA871 pH/ORP sensor CPS76E
- 2
- Memosens data cable CYK10
- Liquiline M CM42 two-wire transmitter for hazardous areas

# Communication and data processing

#### Communication with the transmitter



Always connect digital sensors with Memosens technology to a transmitter with Memosens technology. Data transmission to a transmitter for analog sensors is not possible.

Digital sensors can store measuring system data in the sensor. These include the following:

- Manufacturer data
  - Serial number
  - Order code
  - Date of manufacture
- Calibration data
  - Calibration date
  - Slope at 25 °C (77 °F)
  - Zero point at 25 °C (77 °F)
  - Offset of integrated temperature sensor
  - Offset of ORP measurement
  - Number of calibrations
  - Calibration history
  - Serial number of the transmitter used to perform the last calibration or adjustment
- Application data
  - Temperature application range
  - pH application range
  - ORP application range
  - Date of initial commissioning
  - Maximum temperature value
  - Hours of operation under extreme conditions
  - Number of sterilizations
  - CIP counter

The data listed above can be displayed with Liquiline CM42, CM44x, and Memobase Plus CYZ71D.

### Dependability

### Reliability

### Easy handling

Sensors with Memosens technology have integrated electronics that store calibration data and other information (e.g. total hours of operation or operating hours under extreme measuring conditions). Once the sensor has been connected, the sensor data are transferred automatically to the transmitter and used to calculate the current measured value. As the calibration data are stored in the sensor, the sensor can be calibrated and adjusted independently of the measuring point. The result:

- Easy calibration in the measuring lab under optimum external conditions increases the quality of the calibration.
- Pre-calibrated sensors can be replaced quickly and easily, resulting in a dramatic increase in the availability of the measuring point.
- Thanks to the availability of the sensor data, maintenance intervals can be accurately defined and predictive maintenance is possible.
- The sensor history can be documented on external data carriers and evaluation programs, e.g. Memobase Plus CYZ71D,.
- The saved application data of the sensor can be used to determine the continued use of the sensor in a targeted manner.

### Integrity

### Data security thanks to digital data transmission

Memosens technology digitizes the measured values in the sensor and transmits the data to the transmitter via a non-contact connection that is free from potential interference. The result:

- If the sensor fails or there is an interruption in the connection between the sensor and transmitter, this is reliably detected and reported.
- The availability of the measuring point is reliably detected and reported.

4

### Safety

### Maximum process safety

With inductive transmission of the measured value using a non-contact connection, Memosens guarantees maximum process safety and offers the following benefits:

- All problems caused by moisture are eliminated:
  - No corrosion at the connection
  - Measured values cannot be distorted by moisture
- The transmitter is galvanically decoupled from the medium. Issues concerning "symmetrical highimpedance" or "asymmetry" or the type of impedance converter are a thing of the past.
- Electromagnetic compatibility (EMC) is guaranteed by screening measures for the digital transmission of measured values.
- Intrinsically safe electronics mean operation in hazardous areas is not a problem. Complete flexibility thanks to individual Ex approvals for all components, such as sensors, cables and transmitters.

### Input

### Measured variable

- pH value
- ORP
- rH value
- Temperature

### Measuring range

ORP: -1500 to 1500 mV

### Application B

- pH: 0 to 14
- Temperature: 0 to 140 °C (32 to 284 °F)

### Application H


- pH: 0 to 12
- Temperature: 0 to 140 °C (32 to 284 °F)



Pay attention to the operating conditions in the process.

# Power supply

### **Electrical connection**



■ 2 Measuring cable CYK10 or CYK20

► Connect the Memosens measuring cable, e.g. CYK10 or CYK20 to the sensor.

For further information on cable CYK10, see BA00118C

### Performance characteristics

### Reference system

TB and TU reference system: Ag/AgCl reference lead with ion trap, bridging electrolyte: gel KCl,

3M, AgCl-free

TP reference system: Ag/AgCl reference lead with ion trap, bridging electrolyte: gel KCl,

3M, AgCl-free, pressurized 7 bar (102 psi) (absolute); display via

pressure indicator

### Installation

### Orientation


- Do not install the sensors upside-down.
- The angle of inclination from the horizontal must be at least 15°.

### NOTICE

### Angle of inclination of the sensor less than 15°

An air bubble forms in the glass bulb and there is then no guarantee that the pH membrane is completely covered with inner electrolyte!

► Select the installation angle of the sensor so that it does not drop below 15°.




A002803

- 3 Installation angle at least 15° from the horizontal
- A Permitted orientation
- B Forbidden orientation

### Orientation of sensors for upside-down installation:

- The sensors are suitable for upside-down installation in accordance with the order code for "Reference system".
- Install the sensors at any angle.



A0028040

 $\blacksquare$  4 Any installation angle

### **Installation instructions**

For detailed installation instructions for the assembly: refer to the Operating Instructions of the assembly used.

1. Before screwing in the sensor, make sure the assembly thread, the O-rings and the sealing surface are clean and undamaged and that the thread runs smoothly.

2. Screw in the sensor and tighten by hand with a torque of 3 Nm (2.21 lbf ft) (specifications only apply if installing in Endress+Hauser assemblies).



NOTICE

For detailed information on removing the moistening cap, see BA02142C

### **Environment**

Ambient temperature range	Risk of damage from frost!  Do not use the sensor at temperatures below.	
Storage temperature	0 to 50 °C (32 to 122 °F)	
Degree of protection	IP 68 (10 m (33 ft) water column, 25 °C (77 °F), 45 days, 1 M KCl)	

# Electromagnetic compatibility (EMC)

Interference emission and interference immunity as per:

- EN 61326-1:2013EN 61326-2-3:2013
- NAMUR NE21:2017

### **Process**

Process temperature range	Applications B and H: 0 to $140 ^{\circ}$ C (32 to $284 ^{\circ}$ F)
Frocess temperature range	

Version TB: 0 to 140 °C (32 to 284 °F)

Version TU, TP (pressurized 0 to 140 °C (32 to 284 °F) (140 °C (284 °F) only for sterilization)

reference): Maximum 100 °C (212 °F) in continuous operation due to

increasing pressure loss at T > 100  $^{\circ}$ C (212  $^{\circ}$ F)

### Process pressure range

### **A** CAUTION

### Pressurization of sensor due to prolonged use under increased process pressure

Possibility of sudden rupture and injury from glass splinters!


- Avoid fast heating of these pressurized sensors if they are used under reduced process pressure or under atmospheric pressure.
- ▶ When handling these sensors, always wear protective goggles and appropriate protective gloves.

Application B: 0.8 to 14 bar (11.6 to 203 psi) absolute
Application H 0.8 to 7 bar (11.6 to 101.5 psi) absolute

### Conductivity

 $10~\mu\text{S/cm}$  (at atmospheric pressure, without flow) (minimized flow; pressure and temperature must remain constant)

# Pressure/temperature ratings




■ 5 Pressure/temperature ratings

- B Application B
- H Application H
- x Atmospheric pressure

## **Mechanical construction**

### Design, dimensions



A004581

- 6 CPS76E. Engineering unit: mm (in)
- 1 Memosens plug-in head with process connection
- 2 O-ring with thrust collar
- *3 Reference with ion trap*
- 4 ORP measuring element
- 5 Ceramic junction
- 6 Temperature sensor
- 7 Ag/AgCl reference lead
- 8 pH glass membrane

### Weight

Installed length	120 mm (4.72 in)	225 mm (8.86 in)	360 mm (14.17 in)	425 mm (16.73 in)
Weight	40 g (1.4 oz)	60 g (2.1 oz)	90 g (3.2 oz)	100 g (3.5 oz)

**Process connections** 

Materials Sensor shaft Glass to suit process pH membrane glass Type B Type N Metal lead Ag/AgCl Open aperture Ceramic junction, zirconium dioxide ORP measuring element Platinum FKM 0-ring Process coupling PPS fiber-glass reinforced Nameplate Ceramic metal oxide Temperature sensor NTC 30K Plug-in head Memosens plug-in head for digital, non-contact data transmission, pressure resistance 16 bar (232 psi) (relative)

# Certificates and approvals

**C€ mark**The product meets the requirements of the harmonized European standards. As such, it complies with the legal specifications of the EU directives. The manufacturer confirms successful testing of the product by affixing to it the **C€** mark.

### Ex approval ATEX

II 1G Ex ia IIC T3/T4/T6 Ga

### IECEx

Pg 13.5

Ex ia IIC T3/T4/T6 Ga

### **NEPSI**

Ex ia IIC T3/T4/T6 Ga

### CSA C/US

- IS CL I DIV 1, GP A, B, C, D Ex ia IIC T3/T4/T6
- CL 1 Zone O, AEx ia IIC T3/T4/T6 Ga

### Japan Ex

Ex ia IIC T3/T4/T6 Ga

### **INMETRO**

Ex ia IIC T3/T4/T6 Ga



Pay attention to the instructions for Memosens data cable CYK10 and transmitters CM82 and CM42.

### Additional certification TÜV certificate for Memosens plug-in head

Pressure resistance 16 bar (232 psi) relative, minimum three times the safety pressure

### EAC

The product has been certified according to guidelines TP TC 004/2011 and TP TC 020/2011 which apply in the European Economic Area (EEA). The EAC conformity mark is affixed to the product.

# **Ordering information**

Product page www.endress.com/cps76e

### **Product Configurator**

On the product page there is a **Configure** button to the right of the product image.

- 1. Click this button.
  - ► The Configurator opens in a separate window.
- 2. Select all the options to configure the device in line with your requirements.
  - └ In this way, you receive a valid and complete order code for the device.
- 3. Export the order code as a PDF or Excel file. To do so, click the appropriate button on the right above the selection window.
- For many products you also have the option of downloading CAD or 2D drawings of the selected product version. Click the **CAD** tab for this and select the desired file type using picklists.

### Scope of delivery

The delivery comprises:

- Sensor in the version ordered
- Operating Instructions
- Safety instructions for the hazardous area (for sensors with Ex approval)

### Accessories

The following are the most important accessories available at the time this documentation was issued.

► For accessories not listed here, please contact your Service or Sales Center.

### Device-specific accessories

### Assemblies

#### Unifit CPA842

- Installation assembly for food, biotechnology and pharmaceutics
- With EHEDG and 3A certificate
- Product Configurator on the product page: www.endress.com/cpa842



Technical Information TI01367C

### Cleanfit CPA875

- Retractable process assembly for sterile and hygienic applications
- For in-line measurement with standard sensors with 12 mm diameter, e.g. for pH, ORP, oxygen
- Product Configurator on the product page: www.endress.com/cpa875



Technical Information TI01168C

### Dipfit CPA140

- pH/ORP immersion assembly with flange connection for very demanding processes
- Product Configurator on the product page: www.endress.com/cpa140



Technical Information TI00178C

### Cleanfit CPA871

- Flexible process retractable assembly for water, wastewater and the chemical industry
- $\ \ \, \blacksquare$  For applications with standard sensors with 12 mm diameter
- Product Configurator on the product page: www.endress.com/cpa871



Technical Information TI01191C

### Cleanfit CPA450

- Manual retractable assembly for installing sensors with a diameter of 12 mm and a length of 120 mm in tanks and pipes
- Product Configurator on the product page: www.endress.com/cpa450



Technical Information TI00183C

### Cleanfit CPA473

- Stainless steel process retractable assembly with ball valve shutoff for particularly reliable separation of the medium from the environment
- Product Configurator on the product page: www.endress.com/cpa473



Technical Information TI00344C

### Cleanfit CPA474

- Plastic process retractable assembly with ball valve shutoff for particularly reliable separation of the medium from the environment
- Product Configurator on the product page: www.endress.com/cpa474



Technical Information TI00345C

### Dipfit CPA111

- Immersion and installation assembly made of plastic for open and closed vessels
- Product Configurator on the product page: www.endress.com/cpa111



Technical Information TI00112C

### Flowfit CPA240

- pH/ORP flow assembly for processes with stringent requirements
- Product Configurator on the product page: www.endress.com/cpa240



Technical Information TI00179C

### Flowfit CPA250

- Flow assembly for pH/ORP measurement
- Product Configurator on the product page: www.endress.com/cpa250



Technical Information TI00041C

### **Ecofit CPA640**

- Set comprising adapter for 120 mm pH/ORP sensors and sensor cable with TOP68 coupling
- Product Configurator on the product page: www.endress.com/cpa640



Technical Information TI00246C

### **Buffer solutions**

### High-quality buffer solutions from Endress+Hauser - CPY20

The secondary buffer solutions have been referenced to primary reference material of the PTB (German Federal Physico-technical Institute) or to standard reference material of NIST (National Institute of Standards and Technology) according to DIN 19266 by a laboratory accredited by the DAkkS (German accreditation body) according to DIN 17025.

Product Configurator on the product page: www.endress.com/cpy20

### **ORP buffer solution CPY3**

- 220 mV, pH 7
- 468 mV, pH 0.1

Product Configurator on the product page: www.endress.com/cpy3

### Measuring cable

### Memosens data cable CYK10

- For digital sensors with Memosens technology
- Product Configurator on the product page: www.endress.com/cyk10



Technical Information TI00118C

### Memosens laboratory cable CYK20

- For digital sensors with Memosens technology
- Product Configurator on the product page: www.endress.com/cyk20



www.addresses.endress.com

