

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.: IECEx DEK 12.0018X

Page 1 of 4

Certificate history:

Status: Current

Issue No: 1

Issue 0 (2012-09-28)

Date of Issue:

2021-10-20

Applicant:

Endress+Hauser Wetzer GmbH+Co. KG

Obere Wank 1

87484 Nesselwang

Germany

Equipment:

Resistance-Thermometer Omnigrad, Types TR10, TR11, TR12 and TR13 and Thermocouple-Thermometer

Omnigrad, Types TC10, TC12 and TC13

Optional accessory:

Type of Protection: ta/tb

Marking: Ex ta/tb IIIC T85 °C...T450 °C Da/Db

Approved for issue on behalf of the IECEx

Certification Body:

Position: Certification Manager

Signature:

Date:

(for printed version)

2021-10-20

L.G. van Schie

1. This certificate and schedule may only be reproduced in full.

2. This certificate is not transferable and remains the property of the issuing body.

The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.



Certificate issued by:

DEKRA Certification B.V. Meander 1051 6825 MJ Arnhem Netherlands





Certificate No.: IECEx DEK 12.0018X Page 2 of 4

Date of issue: 2021-10-20 Issue No: 1

Manufacturer: Endress+Hauser Wetzer GmbH+Co. KG

Obere Wank 1 87484 Nesselwang

Germany

Additional manufacturing

locations:

Endress+Hauser Wetzer (Suzhou)
Co. Ltd.

Jiang-Tian-Li-lu No.31, 215021 Suzhou-SIP (P.R. China)

China

Endress+Hauser Wetzer USA Inc. 2350 Endress Place

Greenwood, IN 46143
United States of America

Endress+Hauser Wetzer (India) Pvt.

M-171/173, MIDC, Waluj, Aurangabad - 431 136 India

-

Endress+Hauser Sicestherm S.r.l.

Via Martin Luther King 7/9 I-20060 Pessano con Bornago (MI)

Italy

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended

STANDARDS:

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

IEC 60079-0:2017

Explosive atmospheres - Part 0: Equipment - General requirements

Edition:7.0

IEC 60079-31:2013 Explosive atmospheres - Part 31: Equipment dust ignition protection by enclosure "t"

Edition:2

This Certificate **does not** indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

NL/DEK/ExTR12.0017/01

Quality Assessment Report:

DE/TUN/QAR06.0009/09



Certificate No.: IECEx DEK 12.0018X Page 3 of 4

Date of issue: 2021-10-20 Issue No: 1

EQUIPMENT:

Equipment and systems covered by this Certificate are as follows:

The Resistance-Thermometer Omnigrad, Types TR10, TR11, TR12, TR13 and Thermocouple-Thermometer Omnigrad, Types TC10, TC12, TC13 consists of a certified enclosure type TA30A or TA30D, containing terminals or a transmitter (type TMT...) and a direct connected temperature sensor in a thermowell. The enclosure can be provided with a blind or windowed cover.

For more information, electrical data and thermal data see Annex 1 to Report No. NL/DEK/ExTR12.0017/01.

SPECIFIC CONDITIONS OF USE: YES as shown below:

For temperature code and ambient temperature range see Annex 1 to Report No. NL/DEK/ExTR12.0017/01.



Certificate No.: IECEx DEK 12.0018X Page 4 of 4

Date of issue: 2021-10-20 Issue No: 1

DETAILS OF CERTIFICATE CHANGES (for issues 1 and above)

- Assessed per IEC 60079-0 Ed. 7 and IEC 60079-31 Ed. 2

- minor editorial changes in documentation

Annex:

225621800-Annex1 to ExTR12.0017.01.pdf

Annex 1 to Report No. NL/DEK/ExTR12.0017/01



Description and thermal data

The Resistance-Thermometer Omnigrad, Types TR10, TR11, TR12, TR13 and Thermocouple-Thermometer Omnigrad, Types TC10, TC12, TC13 consists of a certified enclosure type TA30A or TA30D, containing terminals or a transmitter (type TMT...) and a direct connected temperature sensor in a thermowell. The enclosure can be provided with a blind or windowed cover.

The ambient and process temperature range, depending on transmitter version and temperature code, is listed in the following table:

Assembled head	Temperature	Ambient temperature	Process temperature
transmitter	code	range	range
TMT18x and	T85 °C	-40 °C to +65 °C	-50 °C to +70 °C
TMT8x	T100 °C	-40 °C to +80 °C	-50 °C to +80 °C
(with or without display module)	T135 °C	-40 °C to +85 °C	-50 °C to +120 °C
Without	T85 °C	-50 °C to +70 °C	-50 °C to +70 °C
transmitter	T100 °C	-50 °C to +80 °C	-50 °C to +80 °C
	T135 °C	-50 °C to +120 °C	-50 °C to +120 °C
	T200 °C	-50 °C to +120 °C	-50 °C to +185 °C
	T300 °C	-50 °C to +120 °C	-50 °C to +285 °C
	T450 °C	-50 °C to +120 °C	-50 °C to +435 °C

The enclosure provides a degree of protection IP66/IP67 in accordance with EN/IEC 60529.

Electrical data

Supply and output circuit: max. 42 Vdc, 23 mA (TMT82)

max. 35 Vdc, 23 mA (TMT180/TMT181/TMT182/TMT84/TMT85)

Sensor: max. 10 Vdc, 1 mA