Technical Information **Memosens CPS92E**

ORP sensor for use in heavily polluted media



Digital with Memosens 2.0 technology

Application

- Chemical processes
- Pulp and paper industry
- Contaminated media:
- Solids
- Emulsions
- Precipitation reactions
- Dispersions

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals for use in hazardous areas Zone 0, Zone 1 and Zone 2.

Your benefits

- With open aperture for use in heavily polluted media
- Low maintenance thanks to gel filling
- Long service life thanks to stabilized bridging electrolyte gel
- Not affected by fluctuations in pressure and temperature
- Integrated NTC 30K temperature sensor for effective temperature compensation

Other advantages provided by Memosens technology


- Maximum process safety thanks to non-contact, inductive signal transmission
- Data security thanks to digital data transmission
- Very easy to use as sensor data are saved in the sensor
- Predictive maintenance can be performed by recording sensor load data in the sensor



Measuring principle	ORP measurement The ORP potential is a unit of measurement for the state of equilibria between oxidizing and reducing components of a medium. The ORP is measured using a platinum or gold electrode. Similar to pH measurement, an integrated Ag/AgCl reference system is used as a reference electrode.
Measuring system	A complete measuring system comprises at least: ORP sensor CPS92E Transmitter, e.g. Liquiline CM42, CM44x Memosens data cable CYK10 or CYK20 Assembly Immersion assembly, e.g. Dipfit CPA111 Flow assembly, e.g. Flowfit CPA240 Retractable assembly, e.g. Cleanfit CPA871

Function and system design

Additional options are available depending on the application: Automatic cleaning and calibration system, e.g. Liquiline Control CDC90



Example of a measuring system for pH measurement

- 1 Retractable assembly Cleanfit CPA871
- 2 ORP sensor CPS92E
- 3 Memosens data cable CYK10
- 4 Liquiline M CM42 two-wire transmitter for hazardous areas

Communication and data	Communication with the transmitter		
processing	Always connect digital sensors with Memosens technology to a transmitter with Memosens technology. Data transmission to a transmitter for analog sensors is not possible.		
	Digital sensors can store measuring system data in the sensor, including: Manufacturer data Serial number Order code Date of manufacture Calibration data Calibration date Offset of integrated temperature sensor Offset of ORP measurement Number of calibrations Calibration history Serial number of the transmitter used to perform the last calibration or adjustment Operating data Temperature application range ORP application range Date of initial commissioning Maximum temperature value Hours of operation under extreme conditions CIP counter		
	The data listed above can be displayed with Liquiline CM42, CM44x, and Memobase Plus CYZ71D		
Dependability	Reliability		

Easy handling

Sensors with Memosens technology have an integrated electronics unit that stores calibration data and other information (e.g. total hours of operation or operating hours under extreme measuring conditions). Once the sensor has been connected, the sensor data are transferred automatically to the transmitter and used to calculate the current measured value. As the calibration data are stored in the sensor, the sensor can be calibrated and adjusted independently of the measuring point. The result:

- Easy calibration in the measuring lab under optimum external conditions increases the quality of the calibration.
- Pre-calibrated sensors can be replaced quickly and easily, resulting in a dramatic increase in the availability of the measuring point.
- Thanks to the availability of the sensor data, maintenance intervals can be accurately defined and predictive maintenance is possible.
- The sensor history can be documented on external data carriers and evaluation programs, e.g. Memobase Plus CYZ71D.
- The saved application data of the sensor can be used to determine the continued use of the sensor in a targeted manner.

Interference immunity

Data security thanks to digital data transmission


Memosens technology digitizes the measured values in the sensor and transmits the data to the transmitter via a non-contact connection that is free from potential interference. The result:

- If the sensor fails or there is an interruption in the connection between the sensor and transmitter, this is reliably detected and reported.
- The availability of the measuring point is reliably detected and reported.

Safety
 Maximum process safety With inductive transmission of the measured value using a non-contact connection, Memosens guarantees maximum process safety and offers the following benefits: All problems caused by moisture are eliminated: No corrosion at the connection Measured values cannot be distorted by moisture The transmitter is galvanically decoupled from the medium. Issues concerning "symmetrical high-impedance" or "asymmetry" or the type of impedance converter are a thing of the past. Electromagnetic compatibility (EMC) is guaranteed by screening measures for the digital transmission of measured values. Intrinsically safe electronics mean operation in hazardous areas is not a problem. Complete flexibility thanks to individual Ex approvals for all components, such as sensors, cables and transmitters.
Input

Measured variable	ORP
	Temperature
Measuring range	-1500 to 1500 mV
	Pay attention to the operating conditions in the process.

Power supply



An installation angle $<15^{\circ}$ is not permitted, as otherwise the electrolyte may separate from the junction at elevated temperatures. The electrolytic contact is then no longer guaranteed.

	A B 15°
	A0028039 Installation angle at least 15° from the horizontal
	A Permitted orientation B Incorrect orientation
Installation instructions	 Before screwing in the sensor, make sure the assembly thread, the O-rings and the sealing surface are clean and undamaged and that the thread runs smoothly. Pay attention to the installation instructions provided in the Operating Instructions of the assembly used.
	 Screw in the sensor and tighten by hand with a torque of 3 Nm (2.21 lbf ft) (specifications only apply if installing in Endress+Hauser assemblies).
	For detailed information on removing the moistening cap, see BA01988C

Environment

Ambient temperature range	NOTICERisk of damage from frost!► Do not use the sensor at temperatures below .
Storage temperature	0 to 50 °C (32 to 122 °F)
Degree of protection	IP 68 (10 m (33 ft) water column, 25 °C (77 °F), 45 days, 1 M KCl)
Electromagnetic compatibility (EMC)	Interference emission and interference immunity as per: • EN 61326-1:2013 • EN 61326-2-3:2013 • NAMUR NE21:2017


Process

Process temperature range	0 to 110 °C (32 to 230 °F)		
Process pressure range	0.8 to 14 bar (11.6 to 203 psi) (absolute)		
	 CAUTION Pressurization of sensor due to prolonged use under increased process pressure Possibility of sudden rupture and injury from glass splinters! Avoid fast heating of these pressurized sensors if they are used under reduced process pressure or under atmospheric pressure. When handling these sensors, always wear protective goggles and appropriate protective gloves. 		



> 500 µS/cm (minimized flow; pressure and temperature must remain constant)

Pressure/temperature ratings




4 Pressure/temperature ratings

P Application P

x Atmospheric pressure

Mechanical construction



■ 5 CPS92E with Memosens plug-in head. Engineering unit: mm (in)

- 1 Memosens plug-in head with process connection
- 2 O-ring with thrust collar
- 3 Ag/AgCl reference lead
- 4 Internal reference lead5 Open aperture
- Open aperture Temperature sensor
- 6 Temperature se7 Platinum cap

Installed length	120 mm (4.72 in)	225 mm (8.86 in)	360 mm (14.17 in)
Weight	40 g (1.4 oz)	60 g (2.1 oz)	90 g (3.2 oz)
Sensor shaft		Glass to suit process	
ORP measuring element		Platinum	
Metal lead		Ag/AgCl	
O-ring		FKM	
Process coupling		PPS fiber-glass reinforced	
Nameplate		Ceramic metal oxide	
NTC 30K			
Memosens plug-in head for digital, non-contact data transmission, pressure resistance 16 bar (232 psi) (relative)			
Pg 13.5			
	Weight Sensor shaft ORP measuring ele Metal lead O-ring Process coupling Nameplate NTC 30K Memosens plug-in 16 bar (232 psi) (r	Weight 40 g (1.4 oz) Sensor shaft ORP measuring element Metal lead O-ring Process coupling Nameplate NTC 30K Memosens plug-in head for digital, non-com 16 bar (232 psi) (relative)	Weight 40 g (1.4 oz) 60 g (2.1 oz) Sensor shaft Glass to suit process ORP measuring element Platinum Metal lead Ag/AgCl O-ring FKM Process coupling PPS fiber-glass reinfor Nameplate Ceramic metal oxide NTC 30K Memosens plug-in head for digital, non-contact data transmission, pr 16 bar (232 psi) (relative) O-ring

Certificates and approvals

C€ mark	The product meets the requirements of the harmonized European standards. As such, it complies with the legal specifications of the EU directives. The manufacturer confirms successful testing of the product by affixing to it the CC mark.
Ex approval	ATEX II 1G Ex ia IIC T4/T6 Ga
	IECEx Ex ia IIC T4/T6 Ga
	NEPSI Ex ia IIC T4/T6 Ga
	CSA C/US IS Cl. I Div 1, GP A-D Ex ia IIC T4/T6 IS Cl. I Zone 0, AEx ia IIC T4/T6
	Japan Ex Ex ia IIC T4/T6 Ga
	INMETRO Ex ia IIC T4/T6 Ga
	Ex versions of digital sensors with Memosens technology are identified by an orange-red ring on the plug-in head.
	Pay attention to the instructions for Memosens data cable CYK10 and transmitter CM82.
Additional certification	TÜV certificate for Memosens plug-in head
	Pressure resistance 16 bar (232 psi) relative, minimum three times the safety pressure
	EAC
	The product has been certified according to guidelines TP TC 004/2011 and TP TC 020/2011 which apply in the European Economic Area (EEA). The EAC conformity mark is affixed to the product.

Ordering information

Product	page
---------	------

www.endress.com/cps92e

Product Configurator	On the product page there is a Configure button to the right of the product image.			
	1. Click this button.			
	The Configurator opens in a separate window.			
	2. Select all the options to configure the device in line with your requirements.In this way, you receive a valid and complete order code for the device.			
	3. Export the order code as a PDF or Excel file. To do so, click the appropriate button on the right above the selection window.			
	For many products you also have the option of downloading CAD or 2D drawings of the selected product version. Click the CAD tab for this and select the desired file type using picklists.			
Scope of delivery	 The delivery comprises: Sensor in the version ordered Operating Instructions Safety instructions for the hazardous area (for sensors with Ex approval) 			
	Accessories			
	The following are the most important accessories available at the time this documentation was issued.			
	• For accessories not listed here, please contact your Service or Sales Center.			
Device-specific accessories	Assemblies			
	 Cleanfit CPA871 Flexible process retractable assembly for water, wastewater and the chemical industry For applications with standard sensors with 12 mm diameter Product Configurator on the product page: www.endress.com/cpa871 			
	Technical Information TI01191C			
	 Cleanfit CPA875 Retractable process assembly for sterile and hygienic applications For in-line measurement with standard sensors with 12 mm diameter, e.g. for pH, ORP, oxygen Product Configurator on the product page: www.endress.com/cpa875 			
	Technical Information TI01168C			
	 Dipfit CPA140 pH/ORP immersion assembly with flange connection for very demanding processes Product Configurator on the product page: www.endress.com/cpa140 			
	Technical Information TI00178C			
	 Cleanfit CPA473 Stainless steel process retractable assembly with ball valve shutoff for particularly reliable separation of the medium from the environment Product Configurator on the product page: www.endress.com/cpa473 			
	Technical Information TI00344C			
	 Cleanfit CPA474 Plastic process retractable assembly with ball valve shutoff for particularly reliable separation of the medium from the environment Product Configurator on the product page: www.endress.com/cpa474 			
	Technical Information TI00345C			

Dipfit CPA111

- Immersion and installation assembly made of plastic for open and closed vessels
- Product Configurator on the product page: www.endress.com/cpa111

Technical Information TI00112C

Flowfit CPA240

- pH/ORP flow assembly for processes with stringent requirements
- Product Configurator on the product page: www.endress.com/cpa240

Technical Information TI00179C


Flowfit CPA250

- Flow assembly for pH/ORP measurement
- Product Configurator on the product page: www.endress.com/cpa250

Technical Information TI00041C

Ecofit CPA640

- Set comprising adapter for 120 mm pH/ORP sensors and sensor cable with TOP68 coupling
- Product Configurator on the product page: www.endress.com/cpa640



Buffer solutions

ORP buffer solution CPY3

- 220 mV, pH 7
- 468 mV, pH 0.1

Product Configurator on the product page: www.endress.com/cpy3

Measuring cable

Memosens data cable CYK10

- For digital sensors with Memosens technology
- Product Configurator on the product page: www.endress.com/cyk10
- Technical Information TI00118C

Memosens laboratory cable CYK20

- For digital sensors with Memosens technology
- Product Configurator on the product page: www.endress.com/cyk20



www.addresses.endress.com

