


XPC0001-*+QA/QB/QC: Wetted sealings for process connection DN25/G 1 ¼", single chamber




Kit Content	Pcs.	Pos.
Molded seal	1	2
O-ring 18.72 mm x 2.62 mm	4	3
O-ring 23.52 mm x 1.78 mm	1	4
O-ring 31.42 mm x 2.62 mm	1	5
O-ring 21.95 mm x 1.78 mm	1	6
Slide bushing for service chamber	1	15
O-Ring dismounting tool	1	a

Material: EPDM (+QA), FKM (+QB), FFKM (+QC)


The color of the sealings may differ.

Certificates must be ordered as additional option.

Mounting positions



XPC0001-*+QF/QG/QH: Wetted sealings for all process connections NOT DN25/G 1 1/4", single chamber




Kit Content	Pcs.	Pos.
Aseptic process seal	1	1
Molded seal	1	2
O-ring 18.72 mm x 2.62 mm	3	3
O-ring 23.52 mm x 1.78 mm	1	4
O-ring 31.42 mm x 2.62 mm	1	5
Slide bushing for service chamber	1	15
TPE sealing disk	1	16
O-Ring dismantling tool	1	a

Material: EPDM (+QF), FKM (+QG), FFKM (+QH)

The color of the sealings may differ.

Certificates must be ordered as additional option.


XPC0001-*+QI/QJ/QK: Wetted sealings for double chamber




Material: EPDM (+QI), FKM (+QJ), FFKM (+QK)
The color of the sealings may differ.
Certificates must be ordered as additional option.

Kit Content	Pcs.	Pos.
Aseptic process seal	1	1
Molded seal	1	2
O-ring 18.72 mm x 2.62 mm	1	3
O-ring 23.52 mm x 1.78 mm	1	4
O-ring 25.07 mm x 2.62 mm	2	7
TPE sealing disk	2	16
O-Ring dismantling tool	1	a

Mounting positions



XPC0001-*+QL: Non-wetted sealings



The color of the sealings may differ.

Kit Content	Pcs.	Pos.
O-ring 23.52 mm x 1.78 mm	1	4
O-ring 31.42 mm x 2.62 mm	1	5
O-ring 34.59 mm x 2.62 mm	1	8
O-ring 34.65 mm x 1.78 mm	1	9
O-ring 14.00 mm x 1.78 mm	1	10
O-ring 30.00 mm x 2.00 mm	1	11
O-ring 29.82 mm x 2.62 mm	1	12
O-ring 60.00 mm x 1.50 mm	1	13
O-ring 11.00 mm x 1.50 mm	1	14
O-Ring dismounting tool	1	a

Mounting positions

