



TYPE APPROVAL CERTIFICATE

Certificate No:
TAA0000215
Revision No:
5

This is to certify:

That the Temperature Sensor

with type designation(s)
Omnigrad S TR63, TR66, TM131

Issued to
Endress+Hauser Wetzer GmbH+Co. KG
Nesselwang, Germany

is found to comply with
DNV rules for classification – Ships, offshore units, and high speed and light craft

Application :

Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV.

Location classes:

Temperature	B
Humidity	B
Vibration	A
EMC	B
Enclosure	C

Issued at **Hamburg** on **2024-02-07**

for **DNV**

This Certificate is valid until **2028-09-17**.

DNV local station: **Augsburg**

Approval Engineer: **Holger Jansen**

.....
Joannis Papanuskas
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



Product description

RTD thermometer with 1x or 2x Pt100 (2-, 3- or 4-wire)	
Measuring temperature:	Up to 600°C
Process connection:	Thread, flange or compression fitting or thermowell (of external supply)
Electrical connection:	DNV certified Endress+Hauser head transmitter, terminal block or flying leads
Max. tube length (TR63, TM131):	Neck tube length incl. extension max. 196 mm Insert length without fixation max. 750 mm; fixation every 750 mm
Max. tube length (TR66):	Neck tube length incl. extension max. 209 mm Insert length without fixation max. 1000 mm; fixation every 1000 mm
Degree of protection:	IP 66

Places of Production

Endress + Hauser Sigestherm S.r.l., Via Martin Luther King, 7 20060 Pessano con Bornago (MI), Italy	Endress+Hauser Wetzer (Suzhou) Co. Ltd. China-Singapore-Suzhou Industry Park (SIP) 31 Jiang-Tian-Li-lu, JiangSu Province Suzhou 215126, China
---	--

Application/Limitation

The Type Approval covers hardware listed under Product description. When the hardware is used in applications to be classed by DNV, documentation for the actual application is to be submitted for approval by the manufacturer of the application system in each case. Reference is made to DNV rules for classification of ships Pt.4 Ch.9 Control and monitoring systems.

Ex-certification is not covered by this certificate. Application in hazardous area to be approved in each case according to DNV Rules and Ex-Certification / Special Condition for Safe Use listed in valid Ex-certificate issued by a notified/recognized Certification Body.

DNV type approval certificate(s) for head transmitters to be observed (e. g. TAA000026V)

Type Approval documentation

Test report: [No. 07-1702 of paconsult \(18.10.07\)](#)
Technical Information: [TI282/02/en/07.05 \(TR63\)](#), [TI284T/02/en/07.05 \(TR66\)](#)
Electrical drawings acc. to the submitted file
DNV Certificate TAA000026V
Type approval assessment reports issued at Augsburg on 2023-05-23

Tests carried out

Applicable tests according to class guideline DNV-CG-0339, August 2021.

Marking of product

The products to be marked with:

- manufacturer name
- model name
- serial number
- power supply ratings

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the type are complied with, and that no alterations are made to the product design or choice of systems, software versions, components and/or materials.

The main elements of the assessment are:

- Ensure that type approved documentation is available
- Inspection of factory samples, selected at random from the production line (where practicable)
- Review of production and inspection routines, including test records from product sample tests and control routines
- Ensuring that systems, software versions, components and/or materials used comply with type approved documents and/or referenced system, software, component and material specifications
- Review of possible changes in design of systems, software versions, components, materials and/or performance, and make sure that such changes do not affect the type approval given
- Ensuring traceability between manufacturer's product type marking and the type approval certificate

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE