



Certificate of Compliance

Certificate:	80021719	Master Contract:	205557
Project:	80238458	Date Issued:	2025-08-26
Issued to:	Endress+Hauser Conducta GmbH & Co. KG Dieselstraße 24 Gerlingen, Baden- Württemberg 70839 Germany	Issued by:	Awais Hameed Awais Hameed

Attention: Marco Rottmann

The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.



PRODUCTS

Class 2258 04 PROCESS CONTROL EQUIPMENT - Intrinsically Safe, Entity - For Hazardous Locations

Class 2258 84 PROCESS CONTROL EQUIPMENT - Intrinsically Safe, Entity - For Hazardous Locations - Certified to US Standards

Model(s)

Inductive sensor-cable connection system MEMOSENS

Ex ia IIC T6...T4 Ga

Class I, Zone 0 AEx ia IIC T6...T4 Ga

IS Class I, Division 1, Groups A, B, C and D T6...T4



Certificate: 80021719

Master Contract: 205557

Project: 80238458

Date Issued: 2025-08-26

Inductive sensor-cable connection system MEMOSENS, consisting of a sensor and the measuring cable type xYK10 or type xYK20 is used to measure different parameters of fluid media.

The sensors in conjunction with measuring cable xYK10, xYK20 (max. length 100m) may be connected to the intrinsic safe digital sensor module FSDG1 output of CSA certified Liquiline CM42, Communication module 2DS Ex-i of the transmitter CM44x, Digital sensor interface (Memosens, terminals 87, 88, 97, 98) of the Liquiline transmitter CM42B or equivalent providing the following maximum values as described below. In particular the effective inner inductivity and capacity of the approved, intrinsic safe sensor output may not exceed the values given below. Install per control drawing (*safety instruction*) XA02844C.

1. Entity Parameter Set	2. Entity Parameter Set
U _o = 5.1 V	U _o = 5.04 V
I _o = 130 mA	I _o = 80 mA
P _o = 166 mW (linear output characteristic)	P _o = 112 mW (trapezoid output characteristic)
C _i = 15 µF	C _i = 14.1 µF
L _i = 95 µH	L _i = 237.2 µH

Furthermore, the connection of power limited Memosens sensors (P_i is defined) to the power limited inductive coupling of measuring cable xYK10 and xYK20 is possible considering of the following value:

Maximum output power P_o = 178 mW (except for sensor type CLS50D).

Digital sensor types are:

- pH/ORP Sensor **xPS##D-abbcddee+f**
 - x = O, C or OC (no ex-relevance)
 - ## = 16, 76, 96
 - a = Version (no Ex-relevance)
 - bb = Application range (no Ex-relevance)
 - c = Shaft length, maximum 600 mm (no Ex-relevance)
 - d = Approval (no ex-relevance)
 - eee = three characters determining customer version; Only if x = O, OC (no Ex-relevance)
 - f = one or more characters determining optional features (no Ex-relevance)
- pH/ORP Sensor **xPS171D-aabcddefff+g**
 - x = O, C or OC (no ex-relevance)
 - aa = Approval (no ex-relevance)
 - b = Electrode type (no Ex-relevance)
 - c = Application range (no Ex-relevance)
 - dd = Reference system (no Ex-relevance)
 - e = Shaft length (no ex-relevance)
 - fff = three characters determining customer version; Only if x = O, OC (no Ex-relevance)



Certificate: 80021719

Master Contract: 205557

Project: 80238458

Date Issued: 2025-08-26

g = one or more characters determining optional features (no Ex-relevance)

- pH ISET sensor type **xPS4x1D-bdegaaff+***

b = 7, basic version; 8, SIL version, for xPS11D, xPS71D and xPS91D use only

d = 1 character for shaft length, maximum 600mm (not relevant for safety)

e = 1 character for electrolyte supply for xPS4xD and xPS441D use only (not relevant for safety)

g = 1 character for application specified or additional feature (not relevant for safety)

aa = 1 or 2 character identifier for Approval agency in Hazardous area (CC, C2, G, O, F, BA, 8A etc.)

fff = 3 character determining OEM label partner (not relevant for safety)

+* = 1 or more characters for optional features (not relevant for safety)

- Memosens **xLS16D-aabbccddd+e**

x = O, C or OC (no ex-relevance)

aa = Process Connection (no Ex-relevance)

bb = Additional Option (no Ex-relevance)

c = Approval (no Ex-relevance)

ddd = three characters determining customer version; Only if x = O, OC (no Ex-relevance)

e = one or more characters determining optional features (no Ex-relevance)

- Memosens **xLS50D-aabcdefff+g**

x = O, C or OC (no ex-relevance)

aa = Approval (no Ex-relevance)

b = Process Connection (no Ex-relevance)

c = Sensor-, Seal-, Adapter Material

B = PEEK/ VITON/ PEEK,

C = PEEK/Chemraz/ PEEK,

D = PFA/ Chemraz/ 1.4571 material shaft/thread,

E = PEEK; Viton; 1.4571

d = Cable length (no Ex-relevance)

e = Cable connection:

1 = Fixed cable; crimp sleeves

2 = Fixed cable; M12-plug

fff = three characters determining customer version; Only if x = O, OC (no Ex-relevance)

g = one or more characters determining optional features (no Ex-relevance)

The cable types are:

- Measuring cable **xYK10-abbccddd**

x = O, C or OC (no ex-relevance)



Certificate: 80021719

Master Contract: 205557

Project: 80238458

Date Issued: 2025-08-26

a = Approval (no Ex-relevance)

bb = Cable length; max. 100 m (no Ex-relevance)

c = Cable connection (no Ex-relevance)

ddd = three characters determining customer version; Only if x = O, OC (no Ex-relevance)

• Measuring cable **xYK20-aabbccddd**

x = O, C or OC (no ex-relevance)

aa = Approval (no Ex-relevance)

bb = Cable length; max. 100 m (no Ex-relevance)

cc = Cable connection (no Ex-relevance)

ddd = three characters determining customer version; Only if x = O, OC (no Ex-relevance)

Name	Type	Ambient Temperature	Process Temp. Range
Orbisint pH/ORP electrode	xPS16D	0 °C ≤ Ta ≤ +55 °C (T4) ; 0 °C ≤ Ta ≤ +50 °C (T6)	-15 °C ≤ Tp ≤ +120 °C (T4) ; -15 °C ≤ Tp ≤ +70 °C (T6)
Tophit	xPS441D, xPS471D		
Tophit	xPS491D		-15 °C ≤ Tp ≤ +110 °C (T4) ; -15 °C ≤ Tp ≤ +70 °C (T6)
Ceragel pH/ORP electrode	xPS76D	0 °C ≤ Ta ≤ +55 °C (T4) ; 0 °C ≤ Ta ≤ +50 °C (T6)	0 °C ≤ Tp ≤ +120 °C (T4) ; 0 °C ≤ Tp ≤ +70 °C (T6)
pH Sensor	xPS171D		
Orbipore pH/ORP electrode	xPS96D		0 °C ≤ Tp ≤ +110 °C (T4) ; 0 °C ≤ Tp ≤ +70 °C (T6)
Condumax W	CLS15D-A		-20 °C ≤ Tp ≤ +120 °C (T4) ; -20 °C ≤ Tp ≤ +70 °C (T6)
Condumax H	CLS16D		-5 °C ≤ Tp ≤ +115 °C (T4) ; -5 °C ≤ Tp ≤ +65 °C (T6)
Indumax	CLS50D-***B CLS50D-***C		-20 °C ≤ Tp ≤ +120 °C (T4) ; -20 °C ≤ Tp ≤ +70 °C (T6)
Indumax	CLS50D-***D		-20 °C ≤ Tp ≤ +110 °C (T4) ; -20 °C ≤ Tp ≤ +70 °C (T6)
Measuring Cable	xYK10		-15 °C ≤ Tp ≤ +120 °C (T4) ; -15 °C ≤ Tp ≤ +70 °C (T6)
Measuring Cable	xYK20		-10 °C ≤ Tp ≤ +50 °C (T6)

Note:

where applicable, prefix “x” = C or O or OC (not Ex relevant)

Ex ia IIC T6 Gb

Class I, Zone 0 AEx ia IIC T6 Gb

IS Class I, Division 1, Groups A, B, C and D T6

Memocheck xYP02D in connection with the measuring cable xYK10 serves as a test tool for qualification or checking of transmitters providing Memosens capabilities. The connection between sensor simulator and measuring cable is galvanically isolated via a completely isolated connection system. These simulators are not permanently installed in the field and not in contact with process media. Install per



Certificate: 80021719

Master Contract: 205557

Project: 80238458

Date Issued: 2025-08-26

control drawing XA01687C.

The Sensor simulator types are:

- Memocheck **xYP##D-aabcdfff+g**

Order codes:

= 02

aa = parameter (no Ex-relevance)

b = Version (no Ex-relevance)

c = certificate (no Ex-relevance); Only xYP01D

d = Approval (no Ex-relevance)

fff = three characters determining customer version; Only if x = O, OC (no Ex-relevance)

+g = 1 or more characters for optional features (not relevant for safety)

Name	Type	Ambient Temperature
Memocheck	xYP02D	-15 °C ≤ Ta ≤ +70 °C (T6)

Note:

where applicable, prefix “x” = C or O or OC (not Ex relevant)

Conditions of Acceptability:

1. The measuring cable type xYK10 or type xYK20 and its connecting head must be protected from electrostatic charging, if installed through areas of EPL Ga (Zone 0).
2. For the sensors type xPS16D, xPS76D, xPS96D, xYP02D, xPS171D, the sensors may not be operated in electrostatically critical processing conditions. Intense vapor or dust flows directly impacting on the connection system must be avoided.
3. For the sensors type xPS441D, xPS471D and xPS491D, the sensors may not be operated on processing conditions, in which an electrostatic loading of the sensor and the connecting system is to be counted. Operation in product application intended fluid media providing conductivity of at least 10 nS/cm can be assumed as electrostatic noncritical.
4. For the sensors type CLS16D, metallic process connection parts should be grounded at a mounting location with an impedance of <1MΩ.
5. The sensors type CLS50D-*****-** may only be used in liquid media with a conductivity of at least 10 nS/cm. Metallic process connection parts should be grounded at a mounting location with an impedance of <1MΩ. Non-metallic process connection parts have to be protected from electrostatic charging. The connection cable shall be protected from electrostatic charging where necessary.
6. Only sensors, intended to be used according to the user instructions, must be connected. The rated values of input and output circuits must be followed.
7. To be supplied by a Class 2 or Limited Energy Source in accordance with CSA 61010-1-12.

APPLICABLE REQUIREMENTS

CAN/CSA C22.2 No. 61010-1-12 - Safety requirements for electrical equipment for measurement, control, and laboratory use — Part 1: General requirements

CAN/CSA C22.2 No. 60079-0:15 - Electrical apparatus for explosive gas atmospheres - Part 0: General requirements

CAN/CSA C22.2 No. 60079-11:14 - Second Edition - Explosive atmospheres - Part 11: Equipment protection by intrinsic safety “i”



Certificate: 80021719

Master Contract: 205557

Project: 80238458

Date Issued: 2025-08-26

UL 61010-1, 3rd Edition (Rev. Apr 29, 2016) - UL Standard for Safety Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General Requirements - Third Edition; Including Revisions through April 29, 2016

ANSI/UL 60079-0:2013 - Sixth Edition - UL Standard for Safety - Explosive Atmospheres - Part 0: Equipment - General Requirements

ANSI/UL 60079-11 (Sixth Edition) - UL Standard for Safety Explosive Atmospheres – Part 11: Equipment Protection by Intrinsic Safety "i"

Markings

The manufacturer is required to apply the following markings:

- Products shall be marked with the markings specified by the particular product standard.
- Products certified for Canada shall have all Caution and Warning markings in both English and French.

Additional bilingual markings not covered by the product standard(s) may be required by the Authorities Having Jurisdiction. It is the responsibility of the manufacturer to provide and apply these additional markings, where applicable, in accordance with the requirements of those authorities.

The products listed are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US (indicating that products have been manufactured to the requirements of both Canadian and U.S. Standards) or with adjacent indicator 'US' for US only or without either indicator for Canada only.

Nameplate adhesive label material approval information:

N/A. No adhesive label used.

Markings are etched directly onto the housing using laser printing similar to other sensors approved under CSA report 70157089 for the same manufacturer.

The cable marking will be applied using a non-metallic adhesive shrinking sleeve (HXCT-9.5-9-CS-0024) manufactured by TE Connectivity at a distance of 30 cm from the cable head.

Refer to drawing # 201622 for the sensors and cable generic name plate example.

The following details shall be provided by manufacturer on nameplate:

- Manufacturer's name "Endress + Hauser" or CSA Master Contract Number "205557", adjacent to the CSA Mark in lieu of manufacturer's name.
- The designation "CSA 20CA80021719".
- The CSA Mark, as shown on the Certificate of Conformity.
- Model designation: As specified in the PRODUCTS section, above.
- Electrical ratings: As specified in the PRODUCTS section, above.
- Ambient temperature rating: As specified in the PRODUCTS section, above or control drawings.
- Manufacturing date in MMY format, or serial number, traceable to year and month of manufacture.
- Hazardous Location designation: As specified in the PRODUCTS section, above.
- Temperature code: As specified in the PRODUCTS section, above.
- The words: "Install per Control Drawing XA01687C", or equivalent.
- ISO 3864 Symbol B.3.1  or ISO 7000 symbol 0434  (triangle with exclamation point)
- Warning as below both in English and French as applicable for each type of protection method:



Certificate: 80021719

Master Contract: 205557

Project: 80238458

Date Issued: 2025-08-26

-
- “WARNING: Substitution of components may impair suitability for hazardous locations.”

“AVERTISSEMENT: La substitution de composants peut compromettre l’adaptabilité aux emplacements dangereux.”



Certificate: 80021719


Project: 80238458

Master Contract: 205557

Date Issued: 2025-08-26

Notes:

Products certified under Class(es) C225804, C225884 have been certified under CSA's ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC). www.scc.ca





Supplement to Certificate of Compliance

Certificate: 80021719

Master Contract: 205557

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description
80238458	2025-08-26	Update Report 80021719 to accomplish the following: • Follow-up on FIR and update Report 80021719 regarding the non-conformance issues noted in FIR (FC# 269534) dated October 21, 2024 • Revise drawings • Add missing details for cable marking • Include safety instructions for Memosens CYK10 • Delete sensors that are no longer manufactured • Revise the electronics drawing (KLSK2) for CYK10 • Add the alternate transmitters CM42B, CM44x
80169522	2023-08-30	Update to report 80021719 to introduce the following variations: i. Clarification of Sensor model codes ii. Updating of the document CLS5XD
80063052	2021-01-21	Update of cCSAus report 80021719 for intrinsically safe digital sensor models used with CM42 transmitter to update product nameplates to address FIR (Factory ID 4925117, Trip Number DEU09Q2, date Aug.11, 2020) finding. Certificate number CSA 20CA80021719 and reference for installation drawing “XA01687C” missing from Nameplate.
80021719	2020-03-23	Issue a separate cCSAus prime report for digital sensor models used with CM42 transmitter, previously certified under CSA report 1718339. The I.S. Assessment is primarily based on IECEx issued by Dekra. The digital sensors protection method is Ex ia T4/T6 Ga, and the sensor simulators CYP01D, CYP02D are Ex ia T6 Gb.