



中国国家强制性产品认证证书

证书编号: 2020322309000858

认证委托人名称及地址

Endress+Hauser SE+Co. KG
Hauptstrasse 1, 79689 Maulburg, Germany

生产者名称及地址

Endress+Hauser SE+Co. KG
Hauptstrasse 1, 79689 Maulburg, Germany

生产企业名称及地址

Endress+Hauser SE+Co. KG
Hauptstrasse 1, 79689 Maulburg, Germany

产品名称和系列、型号、规格

显示单元
FHX40 系列

产品标准和技术要求

GB/T 3836.1-2021、GB/T 3836.4-2021

上述产品符合《强制性产品认证实施规则 防爆电气》
(CNCA-C23-01:2024)的要求, 特发此证。

发证日期:2025 年 06 月 19 日 有效期至:2030 年 06 月 18 日

首次发证日期:2020 年 08 月 30 日

认证模式:型式试验+初始工厂检查+获证后监督

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,
也可在认监委网站 (www.cnca.gov.cn) 查询。



批 准:

邵毅华

上海仪器仪表自控系统检验测试所有限公司





中国国家强制性产品认证证书

证书编号: 2020322309000858

证书附页: 第 1 页共 1 页

产品名称:

显示单元

型号规格:

FHX40-C *a b c*

其中, *a* 表示连接电缆长度, 可为 1 = 20m/65ft (HART)

5 = 20m/65ft (PROFIBUS PA /

FOUNDATION Fieldbus)

9 = 与安全无关的特殊版本

b 表示附加信息, 可为 A = 基本型

B = 安装支架, 管 1" / 2"

Y = 与安全无关的特殊版本

c 表示标签信息 (可选), 可为 1 (与安全无关)。

防爆标志:

Ex ia II C T6...T5 Gb

电气参数:

Ui = 5.6 V; Ii = 47 mA; Pi = 66 mW; Ci = 11 μ F; Li = 30 μ H.

相关报告编号:

2022S17402-007279

使用条件:

1. 产品使用环境温度和温度组别的关系:

使用环境温度	温度组别
-40°C~+60°C	T6
-40°C~+75°C	T5

本页为证书附页, 应与证书主页同时使用。



SITIAS
Worldwide Access

批 准:

上海仪器仪表自控系统检验测试所有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020322309000858

NAME AND ADDRESS OF THE APPLICANT

Endress+Hauser SE+Co. KG
Hauptstrasse 1, 79689 Maulburg, Germany

NAME AND ADDRESS OF THE MANUFACTURER

Endress+Hauser SE+Co. KG
Hauptstrasse 1, 79689 Maulburg, Germany

NAME AND ADDRESS OF THE FACTORY

Endress+Hauser SE+Co. KG
Hauptstrasse 1, 79689 Maulburg, Germany

NAME, SERIES, MODEL AND SPECIFICATION

Display
FHX40 Series

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 3836.1-2021、GB/T 3836.4-2021

This is to certify that the above-mentioned product(s) complies with the requirements of implementation rules for compulsory certification (CNCA-C23-01:2024).

Issue date:2025-06-19 Valid until:2030-06-18

Date of initial issue:2020-08-30

Type of Certification: Type test + Initial inspection + Surveillance inspection


The certificate details and validity can be verified by scanning the QR code below or logging into the issuing authority's official website. It can also be inquired on the CNCA website (www.cnca.gov.cn).

(In case of dispute, the Chinese text shall prevail.)



SITIAS
Worldwide Access

APPROVAL:



Shanghai Inspection and Testing Institute of Instruments and Automation Systems Co., Ltd.



中国国家强制性产品认证证书

证书编号: 2020322309000864

认证委托人名称及地址

恩德斯豪斯(苏州)自动化仪表有限公司
江苏省苏州市苏州工业园区苏虹中路491号

生产者名称及地址

恩德斯豪斯(苏州)自动化仪表有限公司
江苏省苏州市苏州工业园区苏虹中路491号

生产企业名称及地址

恩德斯豪斯(苏州)自动化仪表有限公司
江苏省苏州市苏州工业园区苏虹中路491号

产品名称和系列、型号、规格

显示单元
FHX40系列

产品标准和技术要求

GB/T 3836.1-2021、GB/T 3836.4-2021

上述产品符合《强制性产品认证实施规则 防爆电气》
(CNCA-C23-01:2024)的要求, 特发此证。

发证日期:2025年06月20日 有效期至:2030年06月19日

首次发证日期:2020年08月30日

认证模式:型式试验+初始工厂检查+获证后监督

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,
也可在认监委网站(www.cnca.gov.cn)查询。



批准:

邵毅华

上海仪器仪表自控系统检验测试所有限公司





中国国家强制性产品认证证书

证书编号: 2020322309000864

证书附页: 第 1 页共 1 页

产品名称:

显示单元

型号规格:

FHX40-C *a b c*

其中, *a* 表示连接电缆长度, 可为 1 = 20m/65ft (HART)

5 = 20m/65ft (PROFIBUS PA /
FOUNDATION Fieldbus)

9 = 与安全无关的特殊版本

b 表示附加信息, 可为 A = 基本型

B = 安装支架, 管 1" / 2"

Y = 与安全无关的特殊版本

c 表示标签信息 (可选), 可为 1 (与安全无关)。

防爆标志:

Ex ia II C T6...T5 Gb

电气参数:

Ui = 5.6 V; Ii = 47 mA; Pi = 66 mW; Ci = 11 μ F; Li = 30 μ H.

相关报告编号:

2022S17402-007279

使用条件:

1. 产品使用环境温度和温度组别的关系:

使用环境温度	温度组别
-40°C~+60°C	T6
-40°C~+75°C	T5

本页为证书附页, 应与证书主页同时使用。



SITIAS
Worldwide Access

批 准:

上海仪器仪表自控系统检验测试所有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020322309000864

NAME AND ADDRESS OF THE APPLICANT

Endress+Hauser (Suzhou) Automation Instrumentation Co., Ltd.
No. 491 Su Hong Zhong Road, SIP , Suzhou 215021 , China

NAME AND ADDRESS OF THE MANUFACTURER

Endress+Hauser (Suzhou) Automation Instrumentation Co., Ltd.
No. 491 Su Hong Zhong Road, SIP , Suzhou 215021 , China

NAME AND ADDRESS OF THE FACTORY

Endress+Hauser (Suzhou) Automation Instrumentation Co., Ltd.
No. 491 Su Hong Zhong Road, SIP , Suzhou 215021 , China

NAME, SERIES, MODEL AND SPECIFICATION

Display
FHX40 series

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 3836.1-2021、GB/T 3836.4-2021

This is to certify that the above-mentioned product(s) complies with the requirements of implementation rules for compulsory certification (CNCA-C23-01:2024).

Issue date:2025-06-20 Valid until:2030-06-19

Date of initial issue:2020-08-30

Type of Certification: Type test + Initial inspection + Surveillance inspection

The certificate details and validity can be verified by scanning the QR code below or logging into the issuing authority's official website. It can also be inquired on the CNCA website (www.cnca.gov.cn).

(In case of dispute, the Chinese text shall prevail.)



SITILAS
Worldwide Access

APPROVAL:



Shanghai Inspection and Testing Institute of Instruments and Automation Systems Co., Ltd.