

Safety Instructions

Cerabar PMC51B, PMP51B

Ex ia IIC T6...T1 Ga



Cerabar PMC51B, PMP51B

Table of contents

About this document	4
Associated documentation	4
Supplementary documentation	4
Certificates and declarations	4
Manufacturer address	4
Extended order code	5
Safety instructions: General	7
Safety instructions: Specific conditions of use	8
Safety instructions: Installation	8
Temperature tables	9
Connection data	11

About this document

The document number of these Safety Instructions (XA) must match the information on the nameplate.

Associated documentation

All documentation is available on the Internet:

www.endress.com/Deviceviewer

(enter the serial number from the nameplate).

To commission the device, please observe the Operating Instructions pertaining to the device:

PMC51B

HART

BA02009P, TI01506P

PROFINET

BA02226P, TI01506P

PMP51B

HART

BA02011P, TI01508P

PROFINET

BA02228P, TI01508P

Supplementary documentation

Explosion protection brochure: CP00021Z

The explosion protection brochure is available on the Internet:

www.endress.com/Downloads

Certificates and declarations**NEPSI Declaration of Conformity**

Certificate number:

GYJ25.1371X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- GB/T 3836.1-2021
- GB/T 3836.4-2021
- GB 3836.20-2010

Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

PMx51B	–	*****	+	A*B*C*D*E*F*G*..
<i>(Device type)</i>		<i>(Basic specifications)</i>		<i>(Optional specifications)</i>

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Cerabar



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

PMC51B, PMP51B

Basic specifications

Position 1, 2 (Approval)		
Selected option		Description
PMC51B	NA	NEPSI Ex ia IIC T6...T1 Ga
PMP51B		

Position 3, 4 (Output)		
Selected option		Description
PMC51B	BA	2-wire, 4-20 mA HART
PMP51B	Fx	2-wire, Ethernet-APL, 10 Mbit/s

Position 6 (Housing, Material)		
Selected option		Description
PMC51B	B	Single compartment; Alu, coated
PMP51B	J	Dual compartment; Alu, coated

Position 10 (Diaphragm Seal Type)		
Selected option		Description
PMP51B	A	W/o
	D	Compact
	G	Temperature isolator
	M m capillary, 316L
	N m capillary, PVC>316L
	O m capillary, PTFE>316L
	R ft capillary, 316L
	S ft capillary, PVC>316L
	T ft capillary, PTFE>316L

Optional specifications

ID Px, Rx (Accessory Enclosed)		
Selected option		Description
PMC51B	PA	Weather protection cover, 316L ¹⁾
PMP51B	PB	Weather protection cover, plastic ²⁾

1) Only in connection with Position 6 = J

2) Only in connection with Position 6 = B

Safety instructions: General

- The device is intended to be used in explosive atmospheres as defined in the scope of IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Comply with the installation and safety instructions in the Operating Instructions.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- For installation, use and maintenance of the device, users must also observe the requirements stated in the Operating Instructions and the standards:
 - GB 50257-2014: "Code for construction and acceptance of electric device for explosion atmospheres and fire hazard electrical equipment installation engineering".
 - GB/T 3836.13-2021: "Explosive atmospheres, Part 13: Equipment repair, overhaul, reclamation and modification".
 - GB 3836.15-2024: "Explosive atmospheres, Part 15: Specification of electrical installations design, selection and erection".
 - GB 3836.16-2024: "Explosive atmospheres, Part 16: Specification of electrical installations inspection and maintenance".
 - GB/T 3836.18-2024: "Explosive atmospheres, Part 18: Intrinsically safe electrical systems".
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.

- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ...)
 - Of isolated capacities (e.g. isolated metallic plates)
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.


Safety instructions:
Specific conditions of use

- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
 - Observe the danger of electrostatic charging and discharge.
 - Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges.
- Avoid sparks caused by impact and friction.

Optional specification, ID Px, Rx = PA

Connect the weather protection cover to the local potential equalization.

Safety instructions:
Installation



A0041997

- A Zone 0, Electronic
- B Zone 0, Process
- 1 Associated intrinsically safe power supply units
- 2 PMC51B, PMP51B

- After aligning (rotating) the enclosure, retighten the fixing screw.
- Continuous service temperature of the connecting cable: $\geq T_a + 20 \text{ K}$.
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- Observe the maximum process conditions according to the manufacturer's Operating Instructions.
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.

Intrinsic safety

- The device is only suitable for connection to certified, intrinsically safe equipment with explosion protection Ex ia.
- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least $500 V_{\text{rms}}$.

Potential equalization

Integrate the device into the local potential equalization.

Temperature tables



- The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
- Do not exceed the max. ambient temperature at the enclosure.
- The process temperatures refer to the temperature at the separation membrane.



Optional specification, ID Px, Rx = PB

When using the weather protection cover: Reduce the admissible ambient temperature by 10 K.

Device Type PMC51B

Temperature class	Process temperature T_p (process)	Ambient temperature T_a (ambient)
T6	+40 °C	-40 to +60 °C
	+80 °C	-40 to +55 °C
T4...T1	+60 °C	-40 to +60 °C
	+80 °C	-40 to +60 °C
	+100 °C	-40 to +55 °C
	+125 °C	-40 to +45 °C

Device Type PMP51B

Basic specification, Position 10 = A, D

Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
T6	+60 °C	-40 to +60 °C
	+70 °C	-40 to +55 °C
	+80 °C	-40 to +55 °C
T4...T1	+70 °C	-40 to +65 °C
	+80 °C	-40 to +60 °C
	+100 °C	-40 to +55 °C
	+125 °C	-40 to +45 °C

Basic specification, Position 10 = G

Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
T6	+80 °C	-40 to +60 °C
T4	+130 °C	-40 to +60 °C
T3	+190 °C	-40 to +60 °C
T2	+290 °C	-40 to +55 °C
T1	+300 °C	-40 to +55 °C
	+400 °C	-40 to +50 °C

Basic specification, Position 10 = M, N, O, R, S, T

Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
T6	+80 °C	-40 to +60 °C
T4	+130 °C	-40 to +65 °C
T3	+190 °C	-40 to +65 °C
T2	+290 °C	-40 to +65 °C
T1	+400 °C	-40 to +65 °C

Version with separate enclosure

Temperature class	Process temperature T_p (process)	Ambient temperature T_a (ambient)
T6	+80 °C	-20 to +60 °C
T4...T1	+100 °C	-20 to +60 °C

Connection data

Basic specification, Position 3, 4 = BA

Power supply
$U_i \leq 30 V_{DC}$ $I_i \leq 300 \text{ mA}$ $P_i \leq 1 \text{ W}$ $C_i \leq 10 \text{ nF}$ $L_i = 0$

Basic specification, Position 3, 4 = Fx

Power supply	
2-WISE $U_i \leq 17.5 V_{DC}$ $I_i \leq 380 \text{ mA}$ $P_i \leq 5.32 \text{ W}$ $C_i \leq 5 \text{ nF}$ $L_i = 0$	Entity $U_i \leq 17.5 V_{DC}$ $I_i \leq 300 \text{ mA}$ $P_i \leq 1.2 \text{ W}$ $C_i \leq 5 \text{ nF}$ $L_i = 0$



71769402

www.addresses.endress.com
