


# O-Ring set: Kit 51518483: EPDM, Kit 51518484: FKM, Kit 51518485: FFKM



| Kit Content                                                                                   | Pcs. | Pos.  |
|-----------------------------------------------------------------------------------------------|------|-------|
| Scraper PEEK with<br>1x O-Ring ID 19.00 W 3.00 AD 25.00<br>1x O-Ring ID 26.70 W 1.78 AD 30.26 | 1    | a/ 20 |
| O-Ring ID 55.00 W 3.00 AD 61.00                                                               | 1    | b/ 70 |
| O-Ring ID 44.00 W 3.00 AD 50.00                                                               | 1    | c/ 40 |
| O-Ring ID 28.17 W 3.53 AD 35.23                                                               | 2    | d/ 90 |
| O-Ring ID 19.00 W 3.00 AD 25.00                                                               | 2    | e/ 50 |
| Scraper ID 19 mm                                                                              | 1    | f/ 60 |
| O-Ring ID 13.00 W 1.50 AD 16.00                                                               | 2    | g/ 80 |
| O-Ring ID 11.00 W 2.00 AD 15.00                                                               | 1    | h/ 10 |
| Grease Klueber Unisilikon L 2 g                                                               | 1    | i     |

A Seals at the process connection flange  
B Seals at the process connection dairy fitting DN65  
C Seals at the rinsing connections

