



IECEx Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.:	IECEx KEM 10.0058X	Page 1 of 4	<u>Certificate history:</u>
Status:	Current	Issue No: 8	Issue 7 (2023-01-19)
Date of Issue:	2024-09-12		Issue 6 (2021-12-02)
Applicant:	Endress+Hauser Yamanashi Co., Ltd. 862-1 Mitsukunugi Sakaigawa-cho Fuefuki-shi Yamanashi Pref. 406-0846 Japan		Issue 5 (2018-10-09)
Equipment:	Transmitters Prothermo Types NMT539-F and NMT532-F		Issue 4 (2016-07-27)
Optional accessory:			Issue 3 (2015-07-29)
Type of Protection:	Ex i		Issue 2 (2014-09-11)
Marking:	Ex ia IIB T6...T2 Ga/Gb or Ex ia IIB T6...T2 Gb		Issue 1 (2013-11-04)
			Issue 0 (2010-07-27)

Approved for issue on behalf of the IECEx
Certification Body:

R. Schuller

Position:

Certification Manager

Signature:
(for printed version)

Date:
(for printed version)

2024-09-12

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.



Certificate issued by:

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands





IECEX Certificate of Conformity

Certificate No.: **IECEX KEM 10.0058X**

Page 2 of 4

Date of issue: 2024-09-12

Issue No: 8

Manufacturer: **Endress+Hauser Yamanashi Co., Ltd.**
862-1 Mitsukunugi Sakaigawa-cho
Fuefuki-shi Yamanashi Pref. 406-0846
Japan

Manufacturing locations: **Endress+Hauser Yamanashi Co., Ltd.**
862-1 Mitsukunugi Sakaigawa-cho
Fuefuki-shi Yamanashi Pref. 406-0846
Japan

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended

STANDARDS :

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

[IEC 60079-0:2017](#) Explosive atmospheres - Part 0: Equipment - General requirements
Edition:7.0

[IEC 60079-11:2011](#) Explosive atmospheres - Part 11: Equipment protection by intrinsic safety "i"
Edition:6.0

[IEC 60079-26:2014](#) Explosive atmospheres – Part 26: Equipment with Equipment Protection Level (EPL) Ga
Edition:3.0

This Certificate **does not** indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

[NL/KEM/ExTR10.0061/07](#)

Quality Assessment Report:

[DE/TUN/QAR06.0003/11](#)



IECEX Certificate of Conformity

Certificate No.: **IECEX KEM 10.0058X**

Page 3 of 4

Date of issue: 2024-09-12

Issue No: 8

EQUIPMENT:

Equipment and systems covered by this Certificate are as follows:

Prothermo NMT 539-F Series Converters, Temperature and Water Level Detectors and Prothermo NMT 532-F Series Average Temperature Transmitters are used either for average temperature measurement, using a separate or an integral temperature probe, or for the measurement of the water interface level at the bottom of a tank, or for combinations of these measurements. The maximum lengths of measurement probes are 99999 mm for NMT 539-F series, and 40000 mm for NMT 532-F series, respectively. The output signal is a 4 - 20 mA current with digital communication (HART).

For temperature range and electrical data, see Annex 1 to this certificate.

SPECIFIC CONDITIONS OF USE: YES as shown below:

In order to exclude ignition sources due to impact and friction sparks, even in the event of rare incidents, the temperature sensor tube shall not be subject to environmental stress, such as impact from moving parts, and the bottom part shall be secured.



IECEX Certificate of Conformity

Certificate No.: **IECEX KEM 10.0058X**

Page 4 of 4

Date of issue: 2024-09-12

Issue No: 8

DETAILS OF CERTIFICATE CHANGES (for issues 1 and above)

Minor change in the construction.

Annex:

[420404700-Annex1.pdf](#)

Description

Prothermo NMT 539-F Series Converters, Temperature and Water Level Detectors and Prothermo NMT 532-F Series Average Temperature Transmitters are used either for average temperature measurement, using a separate or an integral temperature probe, or for the measurement of the water interface level at the bottom of a tank, or for combinations of these measurements.

The maximum lengths of measurement probes are 99999 mm for NMT 539-F series, and 40000 mm for NMT 532-F series, respectively.

The output signal is a 4 - 20 mA current with digital communication (HART).

Ambient temperature range -40 °C to +85 °C.

The relation between the ambient temperature, the process temperature and the temperature class is shown in the following table:

Temperature class	Ambient temperature	Process temperature (sensor)	
		Temperature measurement only	Temperature measurement and water level or water level only
T6	≤ 60 °C	≤ 60 °C	≤ 60 °C
T5	≤ 85 °C	≤ 80 °C	≤ 80 °C
T4	≤ 85 °C	≤ 100 °C	≤ 100 °C
T3*	≤ 85 °C	≤ 175 °C	≤ 125 °C
T2*	≤ 85 °C	≤ 235 °C	---

Note: * is applicable to Prothermo NMT 539 only.

Electrical data

All versions:

Supply and output circuit (terminals H1+ and H1-):

in type of protection intrinsic safety Ex ia IIB, only for connection to a certified intrinsically safe circuit, with the following maximum values:

$U_i = 30 \text{ V}$; $I_i = 120 \text{ mA}$; $P_i = 1 \text{ W}$; $C_i = 7.9 \text{ nF}$; $L_i = 48 \text{ }\mu\text{H}$.

Converter only:

Temperature sensor circuit (connectors CN4 and CN5, module 3):

in type of protection intrinsic safety Ex ia IIB, for connection to an external temperature probe, with following maximum values (trapezoidal characteristic):

$U_o = 8.6 \text{ V}$; $I_o = 71 \text{ mA}$; $P_o = 153 \text{ mW}$; $C_o = 9.5 \text{ }\mu\text{F}$; $L_o = 7.5 \text{ mH}$.

The level sensor circuit is connected to ground and is infallibly galvanically isolated from the supply and output circuit and from the temperature measurement circuit.