



1. EU-TYPE EXAMINATION CERTIFICATE

2. Equipment or Protective systems intended for use in Potentially Explosive Atmospheres - Directive 2014/34/EU

3. EU-Type Examination Certificate No: FM25ATEX0018X

4. Equipment or protective system:
(Type Reference and Name) FMR20B/30B Radar Level Device

5. Name of Applicant: Endress+Hauser SE+Co. KG

6. Address of Applicant Hauptstraße 1, Maulburg D-79689, Germany

7. This equipment or protective system and any acceptable variation thereto is specified in the schedule to this certificate and documents therein referred to.

8. FM Approvals Europe Ltd, notified body number 2809 in accordance with Article 17 of Directive 2014/34/EU of 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in confidential report number:

PR471167 dated 7th July 2025

9. Compliance with the Essential Health and Safety Requirements, with the exception of those identified in item 15 of the schedule to this certificate, has been assessed by compliance with the following documents:

EN IEC 60079-0:2018, EN 60079-11:2012, EN 60079-31:2014, EN 60529:1991+A1:2000+A2:2013

10. If the sign 'X' is placed after the certificate number, it indicates that the equipment is subject to specific conditions of use specified in the schedule to this certificate.

11. This EU-Type Examination certificate relates only to the design, examination and tests of the specified equipment or protective system in accordance to the directive 2014/34/EU. Further requirements of the Directive apply to the manufacturing process and supply of this equipment or protective system. These are not covered by this certificate.

12. The marking of the equipment or protective system shall include:



See Annex

Certificate issued by:

 FM Approvals

7 May 2026

Certification Manager, FM Approvals Europe Ltd.

Date

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals Europe Ltd. One Georges Quay Plaza, Dublin. Ireland. D02 E440
T: +353 (0) 1761 4200 E-mail: atex@fmaprovals.com www.fmaprovals.com

F ATEX 020 (Jul/2024)



Page 1 of 8


SCHEDULE

EU-Type Examination Certificate No. FM25ATEX0018X


13. Description of Equipment or Protective System:

General - The FMR 20B/30B is a radar level device which converts a time-of-flight wave signal into an electrical output signal. The environment can be a hazardous area with gas or dust atmosphere. The FMR20B/30B has an 80GHz radar sensor, which transmits the wave signal direct into air. The electronic transforms the time difference between the propagated wave and the received wave into an electrical signal which is evaluated and put out as a digital (HART) measurement value.

The Block diagram below describes the FMR20B. The Compact Platform components are shown below in blue color (Main Electronic), in orange color (Terminal Electronic) and Radar Sensor modules (Sensor Power Board and Sensor Board).



The Block diagram below describes the FMR30B. The Compact Platform components are shown in blue color (Main Electronic), in orange color (Terminal Electronic) and Radar Sensor modules (Sensor Power Board and Sensor Board).



For additional information on the electronics see the following:

Component	Component Certificates
Electronic Modules (Main electronic and Visualization Unit)	CSANe 24ATEX1149U
Radar Sensor Modules (Sensor Power Board and Sensor Board)	CSANe 24ATEX1175U

Construction - For details on enclosure options for Variant 1, Variant 2 and Variant 3, see document no. 961008308-C.

The FMR20B has an Ingress Protection rating of IP66, IP68.

The FMR30B has an Ingress Protection rating of IP66, IP67.

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

SCHEDULE

EU-Type Examination Certificate No. FM25ATEX0018X

Thermal Ratings -

Protection Type	Model Type	Permitted ambient and Process Temperature
Ex ia IIC	FMR20B / FMR30B	-40°C to +70°C
Ex ia IIIB	FMR20B (Variant 2) / FMR30B	-40°C to +55°C
Ex ia IIIC	FMR20B (Variant 2)	-20°C to +55°C
Ex ta IIIC	FMR20B (Variant 2)	-20°C to +55°C

Electrical Ratings -

The device is DC supplied.

The following values for cables are relevant for the FMR30B (all variants) and FMR20B (all variants) for protection type “intrinsically safe”. For FMR30B the cable must be connected by the customer himself. The FMR20B is supplied with a pre-installed cable (length can be ordered up to a maximum of 300m):

Cable Inductance $L_{\text{cable}} = 1 \mu\text{H/m}$

Cable Capacitance $C_{\text{cable}} = 200 \text{ pF/m}$

Designation	4...20mA HART (X100) L+ / L-
Ex ia IIC	$U_i \leq 30\text{V}$ $I_i \leq 100\text{mA}$ $P_i \leq 700\text{mW}$ $C_i = 18\text{nF}$ $L_i = 0\text{H}$
Ex ia IIIB / Ex ia IIIC	$U_i \leq 30\text{V}$ $I_i \leq 100\text{mA}$ $P_i \leq 650\text{mW}$ $C_i = 18\text{nF}$ $L_i = 0\text{H}$
Ex ta IIIC	$U = 12 \text{ to } 30\text{V}$ $I = 3.4 \text{ to } 22.5\text{mA}$ $P \leq 650\text{mW}$

See Annex for Model Codes

14. Specific Conditions of Use:

See Annex

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

SCHEDULE

EU-Type Examination Certificate No. FM25ATEX0018X

15. Essential Health and Safety Requirements:

The relevant EHSRs that have not been addressed by the standards listed in this certificate have been identified and assessed in the confidential report identified in item 8.

16. Test and Assessment Procedure and Conditions:

This EU-Type Examination Certificate is the result of testing of a sample of the product submitted, in accordance with the provisions of the relevant specific standard(s), and assessment of supporting documentation. It does not imply an assessment of the whole production.

Whilst this certificate may be used in support of a manufacturer's claim for CE Marking, FM Approvals Europe Ltd accepts no responsibility for the compliance of the equipment against all applicable Directives in all applications.

This Certificate has been issued in accordance with FM Approvals Europe Ltd's ATEX Certification Scheme.

17. Schedule Drawings

A list of the significant parts of the technical documentation is annexed to this certificate and a copy has been kept by the Notified Body.

18. Certificate History

Details of the supplements to this certificate are described below:

Date	Description
8 July 2025	Original Issue.
12 January 2026	<u>Supplement 1:</u> Report Reference: PR473554 dated 9 th January 2026. Description of the Change(s): 1. Addition of model type 'BH' for FMR20B with protection type ia IIIC T135°C Da 2. Addition of model type 'BN' for FMR20B with protection type ta IIIC T₂₀₀ 94°C Da 3. EN 60079-31:2014 added to Standards List
7 May 2026	<u>Supplement 2:</u> Report Reference: RR250705 dated 1 May 2026. Description of the Changes: 1. Terminal Board [TA30-0x] layout updated 2. Document updates 3. Document reference update in Description (Section 13)

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

SCHEDULE

EU-Type Examination Certificate No. FM25ATEX0018X

ANNEX**FMR20B - aa bb c d ee fff ggg h+(options) Radar Level Device****Markings:**

II 1 G Ex ia IIC T4 Ga
II 1 D Ex ia IIIB T135°C Da
II 1 D Ex ia IIIC T135°C Da
II 1 D Ex ta IIIC T₂₀₀ 94°C Da

Description of Equipment:

aa	Approval: BA: ATEX/IEC II 1 G Ex ia IIC T4 Ga BH: ATEX/IEC II 1 D Ex ia IIIC T135°C Da BK: ATEX/IEC II 1 D Ex ia IIIB T135°C Da BN: ATEX/IEC II 1 D Ex ta IIIC T ₂₀₀ 94°C Da
bb	Output: BA: 2-wire 4-20mA HART 9Y: Changes not explosion protection relevant
c	Display; Operation: B: LED D: LED + Bluetooth Y: Changes not explosion protection relevant
d	Electrical Connection: T: Pre-installed cable Y: Changes not explosion protection relevant
ee	Antenna: BM: PVDF encapsulated, 40mm / 1-1/2" BN: PVDF encapsulated, 80mm / 3" 99: Changes not explosion protection relevant
fff	Process Connection, cable entry: VCG: Thread ASME MNPT1 WDG: Thread G1 ISO228 XQ0: Without, cable entry lateral YYY: Changes not explosion protection relevant
ggg	Process Connection, antenna end: VEE: Thread ASME MNPT1-1/2, PVDF WEE: Thread ISO228 G1-1/2, PVDF XR0: Without, prepared for UNI throw flange > accessories 9YY: Changes not explosion protection relevant

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

SCHEDULE

EU-Type Examination Certificate No. FM25ATEX0018X

FM Approvals

h	Cable Length: A: 5m/16ft B: 10m/32ft C: 15m/49ft D: 20m/65ft E: 30m/98ft F: 50m/164ft 1:...m 2:...ft 9: Changes not explosion protection relevant
(options)	Options: Not relevant for safety

Specific Conditions of Use:

1. To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
2. In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
 - Observe the danger of electrostatic charging and discharge.
 - Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges.
3. Avoid sparks caused by impact and friction.
4. In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic surfaces.
5. The process connection of the device must be installed in such a way that guarantees a sufficiently tight joint (IP66/67).
6. Applications in which the process temperature exceeds the maximum surface temperature limits of the required maximum surface temperature: The ignition hazard posed by hot surfaces on the process connecting parts of the device must be taken into account
7. It is essential for the device to use a power supply that is galvanically isolated from earth.
8. When using an intrinsically safe barrier, the barrier must be connected to the same earth as the device.
9. Refer to the temperature tables for various ambient and process temperature ranges.
10. For Ex ia IIIC and Ex ta IIIC: The device corresponds to a low risk of mechanical danger
11. For Ex ta IIIC: The user is required to protect the device with an external fuse with a breaking capacity of 1.5kA
12. For Ex ta IIIC: The internal fuse has a breaking capacity of 100A

FMR30B - aa bb c d ee fff ggg h+(options) Radar Level Device

Markings:



II 1 G Ex ia IIC T4 Ga
II 1 D Ex ia IIIB T135°C Da

Description of Equipment:

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals Europe Ltd. One Georges Quay Plaza, Dublin. Ireland. D02 E440
T: +353 (0) 1761 4200 E-mail: atex@fmaprovals.com www.fmaprovals.com

SCHEDULE

EU-Type Examination Certificate No. FM25ATEX0018X

aa	Approval: BA: ATEX/IEC II 1 G Ex ia IIC T4 Ga BK: ATEX/IEC II 1 D Ex ia IIIB T135°C Da
bb	Output: BA: 2-wire 4-20mA HART 9Y: Changes not explosion protection relevant
c	Display; Operation: J: Color Display with Touch Control K: Color Display with Touch Control + Bluetooth Y: Changes not explosion protection relevant
d	Electrical Connection: A: Cable gland M20, plastic, IP66/67 H: Thread NPT1/2, IP66/67 J: Cable gland M20, plastic blue, IP66/67 Y: Changes not explosion protection relevant
ee	Antenna: BM: PVDF encapsulated, 40mm / 1-1/2" BN: PVDF encapsulated, 80mm / 3" 99: Changes not explosion protection relevant
fff	Process Connection, cable entry: XQ0: Without, cable entry on the side YYY: Changes not explosion protection relevant
ggg	Process Connection, antenna end: VEE: Thread ASME MNPT1-1/2, PVDF WEE: Thread ISO228 G1-1/2, PVDF XR0: Without, prepared for UNI throw flange > accessories 9YY: Changes not explosion protection relevant
h	Cable Length: 3: Without, customer side
(options)	Options: Not relevant for safety

Specific Conditions of Use:

1. To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
2. In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
 - Observe the danger of electrostatic charging and discharge.
 - Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges.
3. Avoid sparks caused by impact and friction.
4. In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic surfaces.

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

SCHEDULE

EU-Type Examination Certificate No. FM25ATEX0018X

FM Approvals

5. The process connection of the device must be installed in such a way that guarantees a sufficiently tight joint (IP66/67).
6. Applications in which the process temperature exceeds the maximum surface temperature limits of the required maximum surface temperature: The ignition hazard posed by hot surfaces on the process connecting parts of the device must be taken into account
7. It is essential for the device to use a power supply that is galvanically isolated from earth.
8. When using an intrinsically safe barrier, the barrier must be connected to the same earth as the device.
9. Refer to the temperature tables for various ambient and process temperature ranges.



THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals Europe Ltd. One Georges Quay Plaza, Dublin. Ireland. D02 E440
T: +353 (0) 1761 4200 E-mail: atex@fmaprovals.com www.fmaprovals.com

Blueprint Report

Endress+Hauser SE+Co KG 1000001123

Class No. 3610

Original Project I.D. 471167

Certificate I.D. FM25ATEX0018X

<u>Drawing No.</u>	<u>Revision Level</u>	<u>Drawing Title</u>	<u>Last Report</u>
961005638	B	Electronic Modules	PR473554
961006632	B	Compact Platform AIC Electronic Module	PR473554
961006634	C	Addendum AIC MA20-01A IECEx+ CH-Platform	PR473554
961006636	B	Addendum AIC VA20-0XA IECEx+ CH-Platform	PR473554
961006639	A	Addendum AIC EA20-01A IECEx+ Compact Platform	471167
961006853	B	Compact Platform AIC FMR43 Sensors	471167
961007205	B	Radar Sensor Modules	PR473554
961007619	A	Overview FMR10/20/30B	471167
961007620	A	FMR10B Sensor DN40 nonEx	471167
961007621	A	FMR20B BV DN40/DN80	471167
961007622	A	FMR30B BV DN40/DN80	471167
961007623	A	Visualization unit FMR30B	471167
961007624	A	FMR10/20/30B electronic	471167
961007967	A	Addendum AIC SR20-XXXA IECEx+ Compact Platform	471167
961008340	A	Namepl. IECEx_ATEX FMR30B-BK_Ex ia Da	471167
961008341	A	Namepl. IECEx_ATEX FMR20B-BK_Ex ia Da	471167
961008342	A	Namepl. IECEx_ATEX FMR20B-BA_Ex ia Ga	471167
961008343	A	Namepl. IECEx_ATEX FMR30B-BA_Ex ia Ga	471167
961008702	A	Namepl. IECEx_ATEX FMR20B-BH_Ex ia Da	PR473554
961008703	A	Namepl. IECEx_ATEX FMR20B-BN_Ex ta Da	PR473554
961009089	A	Printed Circuit Board (APP) Compact Hygiene FMRx0_B_TE	RR250705
961009090	A	Conductive Pattern (APP) A1 Compact Hygiene FMRx0_B_TE	RR250705
961009091	A	Conductive Pattern (APP) A2 Compact Hygiene FMRx0_B_TE	RR250705
961009092	A	Conductive Pattern (APP) B2 Compact Hygiene FMRx0_B_TE	RR250705
961009093	A	Conductive Pattern (APP) B1 Compact Hygiene FMRx0_B_TE	RR250705
961009094	A	Circuit Diagram (APP) Compact Hygiene FMRx0_B_TE CPU	RR250705
961009095	A	Circuit Diagram (APP) Compact Hygiene FMRx0_B_TE CPU	RR250705
961009096	A	Circuit Diagram (APP) Compact Hygiene FMRx0_B_TE CPU	RR250705
961009097	A	Assembly Plan (APP) A Compact Hygiene FMRx0_B_TE	RR250705
961009098	A	Assembly Plan (APP) A Compact Hygiene FMRx0_B_TE	RR250705
961009099	A	Assembly Plan (APP) A Compact Hygiene FMRx0_B_TE	RR250705
961009100	A	Assembly Plan (APP) B Compact Hygiene FMRx0_B_TE	RR250705
961009101	A	Assembly Plan (APP) B Compact Hygiene FMRx0_B_TE	RR250705
961009102	A	Assembly Plan (APP) B Compact Hygiene FMRx0_B_TE	RR250705
XA03510F	B	Safety Instructions FMR20B ATEX/IECEx	PR473554
XA03511F	A	Safety Instructions FMR20B ATEX/IECEx	PR473554
XA03512F	A	Safety Instructions FMR30B ATEX/IECEx	471167
XA03648F	A	Safety Instructions FMR20B ATEX/IECEx	PR473554