

# Safety Instructions

## Liquiline M CM42

Two-wire transmitter for hazardous areas

EAC 1Ex ib [ia Ga] IIC T6/T4 Gb X



# Liquiline M CM42

Two-wire transmitter for hazardous areas

## Table of contents

Associated documentation ..... 3

Supplementary documentation ..... 3

Certificate ..... 3

Identification ..... 3

Safety instructions ..... 3

Temperature tables ..... 4

Connection data ..... 4

**Associated documentation** This document is an integral part of Operating Instructions BA00381C and BA00382C.

**Supplementary documentation**



- Competence Brochure CP00021Z
- Explosion Protection: Guidelines and General Principles
  - [www.endress.com](http://www.endress.com)

**Certificate**

EA3C KZ 7500525.01.01.01922

**Identification**

The nameplate provides you with the following information on your device:

- Manufacturer identification
- Extended order code
- Serial number
- Safety information and warnings
- Ex marking on hazardous area versions

► Compare the information on the nameplate with the order.

**Type code**

Type	Version									
CM42 -	*	K	*	*	*	*	**	*	*	*
	No Ex relevance	1Ex ib [ia Ga] IIC T6/T4 Gb X	No Ex relevance							

**Certification Body**

ТОО/ЖШС "Т-Стандарт"

**Safety instructions**

The transmitter meets the fundamental requirements of the applicable standards and is suitable for use in hazardous areas.

- The transmitter is an intrinsically safe electrical apparatus for use in Zone 1 with Gb instrument protection rating.
- You may only connect suitable sensors and must use them as designated according to the Operating Instructions.
- Suitable sensors, which may be arranged in Zone 0, can be connected to the sensor circuits. Suitable sensors bear a red ring.
- The transmitter may only be connected to suitable transmitter power supply units or fieldbus systems according to the FISCO model.
- Pay attention to the information in the Operating Instructions regarding the characteristic values of the input and output circuits.
- Devices with a stainless steel housing must be connected to the local potential equalization system of the place of installation.
- Only genuine spare parts may be used for maintenance or repair measures on the device. These measures may only be performed by service staff or properly trained and authorized technical staff.
- Installation, electrical connection, commissioning, inspection, maintenance and repair may only be performed by qualified specialists trained to work on explosion protected devices in accordance with the applicable standards, e.g. EN 60079-14, -17, -19. Comply with the instructions in the Operating Instructions.
- To avoid electrostatic charge, the device is fitted with a warning label bearing the following information: "Protect against electrostatic charge. Clean the device with a damp cloth only."

## Temperature tables

	Temperature class	
	T4	T6
Ambient temperature $T_a$	-20 to +55 °C	-20 to +50 °C

If the specified process temperatures are complied with, temperatures that are not permitted for the respective temperature class will not occur on the equipment.

## Connection data

## Ex-specification, current output

Intrinsically safe power supply and signal circuits, passive	
Max. input voltage $U_i$	30 V
Max. input current $I_i$	100 mA
Max. input power $P_i$	800 mW
Max. internal inductance $L_i$	29 $\mu$ H (output 1) 24 $\mu$ H (output 2)
Max. internal capacitance $C_i$	1.2 nF (output 1) 0.2 nF (output 2)

## Ex-specification PROFIBUS and FOUNDATION Fieldbus

Suitable for use as a field device in a FISCO system according to EN/IEC 60079-27	
Max. input voltage $U_i$	17.5 V
Max. input current $I_i$	380 mA
Max. input power $P_i$	5.32 W
Max. internal inductance $L_i$	< 10 $\mu$ H
Max. internal capacitance $C_i$	< 5 nF

## Connecting Memosens sensors

Intrinsically safe sensor circuit with type of protection: 0Ex ia IIC	
Max. output voltage $U_o$	5.04 V
Max. output current $I_o$	80 mA
Max. output power $P_o$	112 mW

## Connecting analog pH/ORP sensors

Intrinsically safe sensor circuit with type of protection: 0Ex ia IIC		
	<b>Glass</b>	<b>ISFET</b>
Max. output voltage $U_o$	10.08 V	10.08 V
Max. output current $I_o$	4.1 mA	50.7 mA
Max. output power $P_o$	10.2 mW	128 mW
Max. external inductance $L_o$	1 mH	1 mH
Max. external capacitance $C_o$	250 nF	250 nF

**Connecting analog conductivity sensors with conductive measurement of conductivity**

Intrinsically safe sensor circuit with type of protection: 0Ex ia IIC	
Max. output voltage $U_o$	10.08 V
Max. output current $I_o$	23 mA
Max. output power $P_o$	57 mW
Max. external inductance $L_o$	300 $\mu$ H
Max. external capacitance $C_o$	50 nF

**Connecting analog conductivity sensors with inductive measurement of conductivity**

Intrinsically safe sensor circuit with type of protection: 0Ex ia IIC	
Max. output voltage $U_o$	10.08 V
Max. output current $I_o$	64 mA
Max. output power $P_o$	128 mW
Max. external inductance $L_o$	0.1 mH
Max. external capacitance $C_o$	1.8 $\mu$ F

---

---



[www.addresses.endress.com](http://www.addresses.endress.com)

---