Safety Instructions Cerabar PMC21, PMP21, PMP23

Solutions

Ex ia IIC T4 Ga/Gb Ex ia IIC T4 Gb



71500748 2020-11-23

Document: XA01363P-B Safety instructions for electrical apparatus for explosion-hazardous areas $\rightarrow \cong$ 3



Cerabar PMC21, PMP21, PMP23

Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Extended order code	4
Safety instructions: General	6
Safety instructions: Special conditions	6
Safety instructions: Installation	6
Safety instructions: Zone 0	7
Temperature tables	7
Connection data	7

Associated documentation	This document is an integral part of the following Operating Instructions: BA01271P/00
Supplementary documentation	 Explosion-protection brochure: CP00021Z/11 The Explosion-protection brochure is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Media Type: Documentation -> Documentation Type: Brochures and catalogs -> Text Search: CP00021Z On the CD for devices with CD-based documentation
Manufacturer's certificates	NEPSI Declaration of Conformity
	Certificate number: GYJ20.1351
	Affixing the certificate number certifies conformity with the following standards (depending on the device version):
	 GB3836.1-2010 GB3836.4-2010 GB3836.20-2010
Manufacturer address	Endress+Hauser SE+Co. KG Hauptstraße 1 79689 Maulburg, Germany Address of the manufacturing plant: See nameplate.
Extended order code	The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.
	Structure of the extended order code
	PMC21, PMP2x – ********* + A*B*C*D*E*F*G*
	(Device type) (Basic specifications) (Optional specifications)
	* = Placeholder At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.
	Basic specifications
	The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.
	Optional specifications
	The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit

The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Cerabar

The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

PMC21, PMP21, PMP23

Basic specifications

Position 1, 2 (Approval)		
Selected option		Description
PMC21 NA PMP2x		NEPSI Ex ia IIC T4 Ga/Gb NEPSI Ex ia IIC T4 Gb

Position 3 (Output)			
Selected option		Description	
PMC21 PMP2x	1	4 to 20 mA	

Position 4 (Electrical Connection)			
Selected option		Description	
PMC21	А	Cable 5 m, IP66/68 NEMA Type 4X/6P Encl.	
PMP2x	В	Cable 10 m, IP66/68 NEMA Type 4X/6P Encl.	
	С	Cable 25 m, IP66/68 NEMA Type 4X/6P Encl.	
	М	Plug M12, IP65/67 NEMA Type 4X Encl.	
	U	Valve plug ISO4400 M16, IP65 NEMA Type 4X Encl.	
	V	Valve plug ISO4400 NPT1/2, IP65 NEMA Type 4X Encl.	
PMP23	N	Plug M12, IP66/69 NEMA Type 4X Encl.	

Optional specifications

No options specific to hazardous locations are available.


Safety instructions: General

• Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:


- Be suitably qualified for their role and the tasks they perform
- Be trained in explosion protection
- Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- For installation, use and maintenance of the device, users must also observe the requirements stated in the Operating Instructions and the standards:
 - GB 50257-2014: "Code for construction and acceptance of electric device for explosion atmospheres and fire hazard electrical equipment installation engineering".
 - GB 3836.13-2013: "Explosive atmospheres, Part 13: Equipment repair, overhaul and reclamation".
 - GB/T 3836.15-2017: "Explosive atmospheres, Part 15: Electrical installations design, selection and erection".
 - GB/T 3836.16-2017: "Explosive atmospheres, Part 16: Electrical installations inspection and maintenance".
 - GB/T 3836.18-2017: "Explosive atmospheres, Part 18: Intrinsically safe electrical systems".
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. housing, sensor element, special varnishing, attached additional plates, ..)
 - Of isolated capacities (e.g. isolated metallic plates)

Safety instructions: Special conditions

Safety instructions: Installation



- Observe the danger of electrostatic charging and discharge.
 - Do not rub surfaces with a dry cloth.



🛃 1

- A Zone 1
- 1 Tank; Zone 0
- 2 Certified associated apparatus
- 3 Transmitter housing
- 4 Potential equalization line
- 5 Potential equalization

Intrinsic safety

- When the device is connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC and IIB, the type of protection changes to Ex ib IIC and Ex ib IIB. Do not operate the sensor in Zone 0 if connecting to an intrinsically safe circuit of Category Ex ib.
- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least 500 V_{rms}.

Potential equalization

If the potential equalization cannot be guaranteed by the installation: In order to avoid electrostatic charging, integrate metallic parts of the housing into the potential equalization.

- Safety instructions: Zone 0 In the event of potentially explosive vapor/air mixtures, only operate the device under atmospheric conditions.
 - Temperature: -20 to +60 °C
 - Pressure: 80 to 110 kPa (0.8 to 1.1 bar)
 - Air with normal oxygen content, usually 21 % (V/V)
 - If no potentially explosive mixtures are present, or if additional protective measures have been taken, the device may also be operated under non-atmospheric conditions in accordance with the manufacturer's specifications.
 - Associated devices with galvanic isolation between the intrinsically safe and non-intrinsically safe circuits are preferred.

Temperature tables	Temperature class	Process temperature T _p (process)	Ambient temperature T_a (ambient): housing
	Τ4	≤ 100 °C	-40 °C $\leq T_a \leq +70$ °C

Connection data

Electrical data	
$U_i \le 30 \text{ V}$	
$I_i \le 100 \text{ mA}$ $P_i \le 0.8 \text{ W}$	
$C_i \le 11.6 \text{ nF}$	
$L_i = 0$	



www.addresses.endress.com

