XA02015F-A/00/EN/ 01.20 71503752 2020-05-04

Safety Instructions Gammapilot FMG50

4-20 mA HART

Ex db ia IIC T6...T1 Gb

Document: XA02015F-A Safety instructions for electrical apparatus for explosion-hazardous areas $\rightarrow \boxdot 3$



Gammapilot FMG50

4-20 mA HART

Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Extended order code	4
Safety instructions: General	7
Safety instructions: Special conditions	7
Safety instructions: Installation	8
Safety instructions: Ex d joints	9
Temperature tables	9
Connection data	9

Associated documentation	This document is an integral part of the following Operating Instructions: BA01966F/00
Supplementary	Explosion-protection brochure: CP00021Z/11
documentation	 The Explosion-protection brochure: CP000212711 The Explosion-protection brochure is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Media Type: Documentation -> Documentation Type: Brochures and catalogs -> Text Search: CP00021Z On the CD for devices with CD-based documentation
Manufacturer's certificates	Certificate of Conformity
certificates	Certificate number: CML 20JPN1125X
	Affixing the certificate number certifies conformity with the following standards (depending on the device version):
	 JNIOSH-TR-46-1:2015 JNIOSH-TR-46-2:2018 JNIOSH-TR-46-6:2015
Manufacturer address	Endress+Hauser SE+Co. KG Hauptstraße 1 79689 Maulburg, Germany Address of the manufacturing plant: See nameplate.
Extended order code	The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FMG50	-	*****	+	A*B*C*D*E*F*G*
(Device		(Basic		(Optional
type)		specifications)		specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Gammapilot



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type FMG50

Basic specifications

Position 1, 2 (Approval)		
Selected option	Description	
FMG50 JP	JPN Ex db ia IIC T6T1 Gb ¹⁾	

1) Protection type "Ex db" only available inside the detector pipe

Position 8 (Application)		
Selected option		Description
FMG50 A		Ambient temperature -4060°C/ -40140°F (PVT)
	В	Ambient temperature -2080°C/ -4176°F (PVT HT)
	С	Ambient temperature -4080°C/ -40176°F (NaI)


Position 9 (Sensor Length, Material)		
Selected op	tion	Description
FMG50	A, B, C	mm; NaI crystal
	G, H, I, J, K, L, M, N	mm; PVT

Optional specifications


ID Nx (Accessory Mounted)		
Selected option		Description
FMG50	NA	Overvoltage protection

Safety instructions: General	 Comply with the installation and safety instructions in the Operating Instructions. Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device: Be suitably qualified for their role and the tasks they perform Be trained in explosion protection Be familiar with national regulations Install the device according to the manufacturer's instructions and national regulations. Do not operate the device outside the specified electrical, thermal and mechanical parameters. Avoid electrostatic charging: Of plastic surfaces (e.g. housing, sensor element, special varnishing, attached additional plates,) Of isolated capacities (e.g. isolated metallic plates)
Safety instructions: Special conditions	 In the event of additional or alternative special varnishing on the housing or other metal parts: Observe the danger of electrostatic charging and discharge. Do not rub surfaces with a dry cloth. Do not install in the vicinity of processes generating strong electrostatic charges.

Safety instructions: Installation



- A Zone 1, Zone 2
- B Zone 0, Zone 1, Zone 2
- 1 Detector pipe (in Ex d)
- 2 Housing
- 3 Certified associated apparatus
- 4 Local potential equalization
- After aligning (rotating) the housing, retighten the fixing screw.
- The safety screws at the pipe housing must not be loosened:



Continuous service temperature of the connecting cable: $\ge T_a+20$ K.

Intrinsic safety

- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least 500 $V_{\rm rms}$.
- When the device is connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC and IIB, the type of protection changes to Ex ib IIC and Ex ib IIB.
- Associated devices with galvanic isolation between the intrinsically safe and non-intrinsically safe circuits are preferred.

Potential equalization

Integrate the device into the local potential equalization.

Overvoltage protection

Optional specification, ID Nx (Accessory Mounted) = NA The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least 290 V_{rms} .

• If required or if in doubt: ask manufacturer for specifications.

Safety instructions: Ex d joints

Flameproof joints are not intended to be repaired.

 $-40 \ ^\circ C \le T_a \le +60 \ ^\circ C$

Temperature
tablesBasic specification, Position 8 (Application) = ATemperature classAmbient temperature T_a (ambient)

T6...T1

Basic specification, Position 8 (Application) = B

Temperature class	Ambient temperature T _a (ambient)
T6	$-20 ^{\circ}\text{C} \le \text{T}_{a} \le +60 ^{\circ}\text{C}$
T4T1	$-20 ^{\circ}\text{C} \le \text{T}_{a} \le +70 ^{\circ}\text{C}$

Basic specification, Position 8 (Application) = C

Temperature class	Ambient temperature T _a (ambient)
Т6	$-40 ^{\circ}\text{C} \le \text{T}_{a} \le +60 ^{\circ}\text{C}$
T4T1	-40 °C $\leq T_a \leq +70$ °C

Connection data

Power	supply
-------	--------

	1
\leq 30 V _{DC}	
≤ 300 mÅ	
≤1W	
≤ 10 nF	
= 0	



71503752

www.addresses.endress.com

