

## IECEx Certificate of Conformity

### INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.cor

Certificate No.:	IECEx IBE 20.0031X	Page 1 of 3	Certificate history:				
Status:	Current	Issue No: 0					
Date of Issue:	2021-06-08						
Applicant:	Endress + Hauser Wetzer GmbH & Co. KG Obere Wank 1 87484 Nesselwang Germany						
Equipment:	NAMUR Switch Isolating Amplifier type RLN	22-xx**					
Optional accessory:							
Type of Protection:	ype of Protection: intrinsic safety in combination with increased safety and sealed device						
Marking:	[Ex ia Ga] IIC						
	[Ex ia Da] IIIC						
	Ex ec nC [ia Ga] IIC T4 Gc						
	$-40 \text{ °C} \le \text{T}_{amb} \le +60 \text{ °C}$						
Approved for issue of Certification Body:	on behalf of the IECEx	Alexander Henker					
Position:		Deputy Head of department Certification Body					
Signature:		1100					
(for printed version)		A. Flewser					
Date:		2021-06-08					
<ol> <li>This certificate and schedule may only be reproduced in full.</li> <li>This certificate is not transferable and remains the property of the issuing body.</li> <li>The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.</li> </ol>							
Certificate issue	Certificate issued by:						
IBExU Institut für Sicherheitstechnik GmbH Fuchsmühlenweg 7 09599 Freiberg Germany							



## IECEx Certificate of Conformity

Certificate No .:	IECEx IBE 20.0031X	Page 2 of 3				
Date of issue:	2021-06-08	Issue No: 0				
Manufacturer:	Endress + Hauser Wetzer GmbH & Co. KG Obere Wank 1 87484 Nesselwang Germany					
Additional manufacturing locations:						
This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended						
STANDARDS : The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards						
IEC 60079-0:2017 Edition:7.0	Explosive atmospheres - Part 0: Equipment - General requirement	nts				
IEC 60079-11:2011 Edition:6.0	Explosive atmospheres - Part 11: Equipment protection by intrinsi	ic safety "i"				
IEC 60079-15:2017 Edition:5.0	Explosive atmospheres - Part 15: Equipment protection by type o	f protection "n"				
IEC 60079-7:2017 Edition:5.1	Explosive atmospheres - Part 7: Equipment protection by increase	ed safety "e"				
	This Certificate <b>does not</b> indicate compliance with safety and other than those expressly included in the Standa	performance requirements rds listed above.				

#### **TEST & ASSESSMENT REPORTS:**

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

DE/IBE/ExTR21.0025/00

Quality Assessment Report:

DE/TUN/QAR06.0009/09



## **IECEx Certificate** of Conformity

Certificate No .: IECEx IBE 20.0031X

Date of issue:

Page 3 of 3

Issue No: 0

#### EQUIPMENT:

Equipment and systems covered by this Certificate are as follows:

2021-06-08

The NAMUR Switch Isolating Amplifiers Type RLN22-xx\*\* are used for the intrinsically safe and galvanically isolated operation of proximity switches with NAMUR behaviour or potential-free switches and resistance-connected switches. They are equipped with a 24 V voltage supply. The equipment is provided for installation in zone 2 or in the safe area as associated apparatus. The intrinsically safe signal circuits may be routed into areas that require EPL Ga (Zone 0) or Da (Zone 20).

The voltage difference between input and output circuit or supply can be up to 375 V peak. The modules are equipped with a circuit for the detection of line faults.

The technical data are mentioned in the Annex.

#### SPECIFIC CONDITIONS OF USE: YES as shown below:

- The NAMUR Switch Isolating Amplifiers have to be installed in a suitable housing fulfilling the requirements of IEC 60079-7 or another recognized type of protection. The housing has to maintain a degree of protection of at least IP54 according to IEC 60529 for operation in zone 2.
- Connecting and disconnecting of non-intrinsically safe circuits are not allowed in energized state of the NAMUR Switch Isolating Amplifier. The DIP switches may only be operated when no explosive atmosphere is present.

#### Annex:

Annex\_IBE20.0031\_00.pdf



# IECEx Certificate of Conformity - Annex



Certificate No: IECEx IBE 20.0031X Date of Issue: 2021-06-08 Issue No: 0

Page 1 of 2

### Technical data:

Environmental data	
Ambient temperature range	-40 °C up to +60 °C
Degree of protection of the enclosure	≥ IP20

Elect	rical data					
1.	Power Supply (1.1 and 1.2) and TBUS					
	rated voltage range	Un	24 V DC (19.2 30 V DC)			
	supply current	I <sub>n</sub>	< 35 mA (24 V)			
	power consumption	Pn	< 1 W			
	maximum direct voltage	U <sub>m</sub>	125 V DC			
	maximum effective value of alternating voltage	Um	253 V DC			
	galvanically separated up to a peak voltage	Up	375 V			
2.	Intrinsically safe sensor circuit					
	(4.1 and 4.2/ 5.1 and 5.2)					
	maximum output voltage	Uo	9.6 V			
	maximum output current	Ι <sub>ο</sub>	10 mA			
	maximum output power	Po	25 mW			
	effective internal capacity	Ci	11 nF			
	effective internal inductivity	Li	negligible			
3.	Relay output (2.1 and 2.2 / 3.1 and 3.2)					
	maximum Switching voltage	Us	250 V AC (2 A) /			
			120 V DC (0,2 A) /			
			30 V DC (2 A)			
	maximum switching power	Ps	500 VA			

For circuits including inductances and capacitances the following has to be observed: The values for  $L_0$  and  $C_0$ , mentioned in this certificate are allowed for:

- distributed inductances and capacitances, e.g. as in a cable or
- if the total Li of the external circuit (excluding the cable) is < 1 % of the Lo value or
- if the total Ci of the external circuit (excluding the cable) is < 1 % of the Co value.

	Ex ia IIC	Ex ia IIB/IIIC	Ex ia IIA, Ex ia I
Co	3.6 µF	26 µF	210 µF
Lo	300 mH	1000 mH	1000 mH



# IECEx Certificate of Conformity - Annex



Certificate No:

IECEx IBE 20.0031X

Issue No: 0

Date of Issue:

2021-06-08

Page 2 of 2

The values of  $L_0$  and  $C_0$ , mentioned in this certificate shall be reduced to 50 % or taken from the following table if both of the following conditions are met:

- the total Li of the external circuit (excluding the cable) is ≥ 1 % of the Lo value and
- the total Ci of the external circuit (excluding the cable) is  $\geq$  1 % of the Co value.

	Ex ia IIC			Ex ia I, Ex ia IIB/IIA, Ex ia					
Co	500 nF	570 nF	590 nF	590 nF	600 nF	1 µF	1 μF	1 µF	1μF
Lo	100 mH	50 mH	5 mH	1 mH	10 µH	100 mH	5 mH	1 mH	10 µH

The reduced capacitance of the external circuit (including cable) shall not be greater than 1  $\mu$ F for Groups I, IIA and IIB and 600 nF for Group IIC.