# Safety Instructions Liquiline M CM42

Supplement to: BA00381C and BA00382C

Safety instructions for electrical apparatus in explosionhazardous areas





XA01504C Liquiline M CM42

## Liquiline M CM42

Supplement to: BA00381C and BA00382C

#### Table of contents

Associated documentation	3
Supplementary documentation	3
Identification	3
Safety instructions	3
Temperature tables	4
Connection data	4
Connection diagram	6

Liquiline M CM42 XA01504C

#### Associated documentation

This document is an integral part of Operating Instructions BA00381C and BA00382C.

### Supplementary documentation



Competence Brochure CP00021Z

- Explosion Protection: Guidelines and General Principles
- www.endress.com

#### Identification

The nameplate provides you with the following information on your device:

- Manufacturer identification
- Extended order code
- Serial number
- Firmware version
- Safety information and warnings
- Ex labeling on hazardous area versions
- Certificate information
- ► Compare the information on the nameplate with the order.

#### Type code

Туре	Version			
CM42-	*	K	*	(+*)
	No Ex relevance	1Ex ib [ia Ga] IIC T6/T4 Gb X	No Ex relevar	nce

#### Certificates and approvals

Ex approval

The product has been certified in accordance with Directive TR CU 012/2011 valid within the Eurasian Economic Area (EAEU). The EAC conformity mark has been affixed to the product.

EAC Ex, 1Ex ib [ia Ga] IIC T6/T4 Gb X

Zone 1, connected sensors in Zone 0

Certificate number: TC RU C-DE.AA87.B.00566/20

Certification body

#### 000 "НАНИО ЦСВЭ"

Russian Federation

#### Safety instructions

The transmitter meets the fundamental requirements of the applicable standards and is suitable for use in hazardous areas.

- The transmitter is an intrinsically safe electrical apparatus for use in Zone 1 with Gb instrument protection rating.
- You may only connect suitable sensors and must use them as designated according to the Operating Instructions.
- Suitable sensors, which may be arranged in Zone 0, can be connected to the sensor circuits.
   Suitable sensors bear a red ring.
- The transmitter may only be connected to suitable transmitter power supply units or fieldbus systems according to the FISCO model.
- Pay attention to the information in the Operating Instructions regarding the characteristic values
  of the input and output circuits.
- Devices with a stainless steel housing must be connected to the local potential equalization system
  of the place of installation.

XA01504C Liquiline M CM42

Only genuine spare parts may be used for maintenance or repair measures on the device. These
measures may only be performed by service staff or properly trained and authorized technical
staff.

- Installation, electrical connection, commissioning, inspection, maintenance and repair may only be performed by qualified specialists trained to work on explosion protected devices in accordance with the applicable standards, e.g. EN 60079-14, -17, -19. Comply with the instructions in the Operating Instructions.
- To avoid electrostatic charge, the device is fitted with a warning label bearing the following information: "Protect against electrostatic charge. Clean the device with a damp cloth only."

#### Temperature tables

	Temperature class	
	T4	Т6
Ambient temperature T <sub>a</sub>	−20 to +55 °C	−20 to +50 °C

If the specified process temperatures are complied with, temperatures that are not permitted for the respective temperature class will not occur on the equipment.

#### Connection data

#### Ex-specification, current output

Intrinsically safe power supply and signal circuits, passive		
Max. input voltage U <sub>i</sub>	30 V	
Max. input current I <sub>i</sub>	100 mA	
Max. input power P <sub>i</sub>	800 mW	
Max. internal inductance $L_{\rm i}$	29 μH (output 1) 24 μH (output 2)	
Max. internal capacitance $C_{\rm i}$	1.2 nF (output 1) 0.2 nF (output 2)	

#### Ex-specification PROFIBUS and FOUNDATION Fieldbus

Suitable for use as a field device in a FISCO system according to EN/IEC 60079-27		
Max. input voltage U <sub>i</sub>	17.5 V	
Max. input current I <sub>i</sub>	380 mA	
Max. input power P <sub>i</sub>	5.32 W	
Max. internal inductance L <sub>i</sub>	< 10 µН	
Max. internal capacitance C <sub>i</sub>	< 5 nF	

#### **Connecting Memosens sensors**

Intrinsically safe sensor circuit with type of protection: 0Ex ia IIC	
Max. output voltage U <sub>o</sub> 5.04 V	
Max. output current I <sub>o</sub>	80 mA
Max. output power P <sub>o</sub> 112 mW	

Liquiline M CM42 XA01504C

#### Connecting analog pH/ORP sensors


Intrinsically safe sensor circuit with type of protection: OEx ia IIC		
	Glass	ISFET
Max. output voltage $\mathrm{U_o}$	10.08 V	10.08 V
Max. output current I <sub>o</sub>	4.1 mA	50.7 mA
Max. output power P <sub>o</sub>	10.2 mW	128 mW
Max. external inductance $L_0$	1 mH	1 mH
Max. external capacitance C <sub>o</sub>	250 nF	250 nF

#### Connecting analog conductivity sensors with inductive measurement of conductivity

Intrinsically safe sensor circuit with type of protection: OEx ia IIC		
Max. output voltage $\mathrm{U_o}$	10.08 V	
Max. output current I <sub>o</sub>	64 mA	
Max. output power P <sub>o</sub>	128 mW	
Max. external inductance $L_o$	0.1 mH	
Max. external capacitance C <sub>o</sub>	1.8 μF	


XA01504C Liquiline M CM42

#### Connection diagram



■ 1 Memosens sensors

Liquiline M CM42 XA01504C



■ 2 Analog sensors



www.addresses.endress.com

