[1]	EU-TYPE EXAMINATION CERTIFICATE					
					\overline{C}	
					(CX/	
2]	Equipment or Protective System intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU					
-01						
3]	Ma Ma Ma Ma Ma	EU-Type Examination Certificate Number: DEMKO 16 ATEX 1803 Rev. 1				
4]		Product: Tablet Computer, Agile X IS, Type 17-A1B*-****/*******				
5]	Manufacturer: BARTEC GmbH					
6]	Address: Max-Eyth-Straße 16, 97980 Bad Mergentheim, Germany					
7]	This product and any acceptable variation thereto are specified in the schedule to this certificate and the documents therein referred to.					
[8]	UL International Demko A/S, notified body number 0539 in accordance with Article 17 of the Council Directive 2014/34/EU of 26 February 2014, certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to design and construction of products intended for use in potentially explosive atmospheres given in Annex II to the Directive. The examination and test results are recorded in confidential report no. 4788664284.3.1					
[9]	Compliance with the Essential Health and Safety R	equirements has	been assured by c	ompliance with:		
	EN 60079-0:2012+A11:2013 EN 60079-28:2015	EN 60079 EN 50303				
[10]	If the sign "X" is placed after the certificate number, it indicates that the product is subject to special conditions for safe use specified in th schedule to this certificate.					
11]	This EU-Type Examination Certificate relates only to the design and construction of the specified product. Further requirements of the Directive apply to the manufacturing process and supply of this product. These are not covered by the certificate.					
12]	The marking of the product shall include the followi	ng:				
	$\langle \widehat{\mathbf{E}} \mathbf{x} \rangle$ II 1 G Ex ia op is IIC			Ex ia op is I Ma		
	$\langle \widehat{\mathbf{E}} \mathbf{x} \rangle$ II 2 G Ex ia op is IIC	; T4 Gb	⟨ [€] x⟩ I M2	Ex ia op is I Mb		
կ	ть	is is to certify that the	sample(s) of the Product of	escribed herein ("Certified Product") h	as been investigated	
	Certification Manager Certification Manager Jan-Erik Storgaard	Ind found in compliance ertification Program Req imple(s) submitted by the ovided were representar inveillance of the produce oplicable Standards, spe	with the Standard(s) indic quirements. This certifica ne Manufacturer. UL did r ative of other manufacture ct. The Manufacturer is so	ated on this Certificate, in accordance te and test results obtained apply only ot select the sample(s) or determine 1 d product. UL has not established Fol lely and fully responsible for conformit or Directives. The test results may no	with the ATEX Product to the product whether the sample(s) low-Up Service or other y of all product to all	
	Jan but Stepand D	ate of issue: Re-issued:				
					(Ψ_)	
	Notified Body	\sim	\sim	orupyang 54, 2750 Ba	\sim	

Notified Body

UL International Demko A/S, Borupvang 5A, 2750 Ballerup, Denmark Tel. +45 44 85 65 65, <u>info.dk@ul.com</u>, <u>www.ul.com</u> [14]

Schedule EU-TYPE EXAMINATION CERTIFICATE No. DEMKO 16 ATEX 1803 Rev. 1

[15]

Description of Product

The device covered by this certificate is a handheld tablet computer with touch screen. It is powered by a non-replaceable, rechargeable, internal battery and an optional, replaceable external battery pack. Connection facilities are provided for a USB stick, an SD card, a SIM card, and other external accessories. The device may be configured with a RFID/NFC reader and/or a laser barcode scanner.

Type 17- A1B *-****/******** (Certification)

- 3 or 4 or A Group II, Zone 1 Certified 🖾 II 2 G Ex ia op is IIC T4 Gb
- 5 or 6 or B Group II, Zone 0 Certified- 🐼 II 1 G Ex ia op is IIC T4 Ga
- C Groups I and II, Zone 1 Certified 🐼 II 2 G Ex ia op is IIC T4 Gb, 🐼 I M2 Ex ia op is I Mb
- D Groups I and II, Zone 0 Certified 🐼 II 1 G Ex ia op is IIC T4 Ga, 🕼 I M1 Ex ia op is I Ma
- E Group I, Zone 1 Certified 🔄 I M2 Ex ia op is I Mb
- F Group I, Zone 0 Certified 🔄 I M1 Ex ia op is I Ma

Type 17- A1B *-<u>****/********</u> (Display) 1 – 10" Capacitive

- Type 17- A1B *-****/******* (WAN Carriers) 0 - None 1 or 2 - 4G/LTE
- Type 17- A1B *-***/******** (Operating System) 0-9 – Functions not affecting construction

Type 17- A1B *-****/******** (Processor) 0-9 – Functions not affecting construction

Type 17- A1B *-****/<u>*</u>******* (Memory) 0-9 – Functions not affecting construction

Type 17- A1B *-****/******** (Memory) 0-9 – Functions not affecting construction

Type 17- A1B *-****/************************** (Camera)

0 - None

1 – 5MP Rear, 2MP Front

Type 17- A1B *-****/************************* (External Battery)

- 0 None 1 – 7.4V / 4200mAh
- 1 7.4V / 4200MAN
- Type 17- A1B *-****/************************* (Data Acquisition)
 - 0 None
 - 1 RFID HF/NFC
- - 0 None
 - 1 1D/2D-Imager SE4500

Temperature range:

The ambient temperature range is $-20^{\circ}C \le Ta \le to +50^{\circ}C$.

Electrical data:

Powered by internal battery rated 7.4V, 4200mAh, and optional external battery pack, BARTEC Type 17-A1Z0-0006 rated 7.4V, 4200mAh. The external battery pack may be replaced in a hazardous location.

U_m: 25V for the DCin jack and Docking Connector, which may not be used in a hazardous location.

Accessories:

[13]

[14]

The device may be used with the following BARTEC accessories, which are included as part of this certification:

• Type 17-A1Z0-0007 USB Memory Stick. Alternatively, the USB Port has the following intrinsic safety entity parameters:

USB Port:	Uo = 6.07V						
	lo = 4.46A						
	し人。し人	「人」「人」					
	Co = 28µF	Co = 12µF	Co = 9µF	Co = 6.9µF			
	Lo = 2µH	Lo = 5µH	Lo = 7µH	Lo = 9µH			

• Type 17-A1Z0-00** SD Memory Card, where ** is 08, 09, or 10. Alternatively, the SD Card Port has the following intrinsic safety entity parameters:

SD Card Port:	Uo = 4.63V	
	lo = 2.76A	
	Po = 1.18W	
ULXUL	Co = 79µF	
	Lo = 2µH	

 Expansion Port – The Expansion Port has the following intrinsic safety entity parameters. Under this certificate, the Agile X IS has been subjected to additional mechanical tests with the BARTEC Model 17-A1Z0-0005 HART Module connected. The Model 17-A1Z0-0005 HART Module is certified under EPS 15 ATEX 1069X.

Expansion	Uo = 8.11V		
Port:	lo = 5.69A		
	Po = 8.04W		
	Co = 7.6µF	Co = 5.3µF	
	Lo = 2µH	Lo = 5µH	

Routine tests: None.

[16] <u>D</u>

[17]

[18]

Descriptive Documents

The scheduled drawings are listed in the report no. provided under item no. [8] on page 1 of this EU-Type Examination Certificate.

Specific conditions of use:

None.

Essential Health and Safety Requirements

The Essential Health and Safety Requirements (EHSRs) covered by the standards listed at item 9.

Additional information

The Agile X IS, Type 17-A1B*-****/****** has in addition passed the tests for Ingress Protection to IP 65 in accordance with EN60529:1991+A1:2000+A2:2013.

The manufacturer shall inform the notified body concerning all modifications to the technical documentation as described in Annex III to Directive 2014/34/EU of the European Parliament and the Council of 26 February 2014.