Safety Instructions **Gammapilot FMG50**

4-20 mA HART

1Ex d ia IIC T6...T1 Gb X







Gammapilot FMG50

4-20 mA HART

Table of contents

Associated documentation 4
Supplementary documentation
Manufacturer's certificates 4
Manufacturer address
Extended order code
Safety instructions: General
Safety instructions: Special conditions
Safety instructions: Installation
Safety instructions: Ex d joints
Temperature tables
Connection data9

XA02009F-A Gammapilot FMG50

Associated documentation

This document is an integral part of the following Operating Instructions:

BA01966F/00

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP000217.
- On the CD for devices with CD-based documentation

Manufacturer's certificates

Certificate of Conformity TP TC 012/2011

Inspection authority:

LLC NANIO CCVE (ООО «НАНИО ЦСВЭ»)

Certificate number:

EA9C RU C-DE.AA87.B.00675/21

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- GOST 31610.0-2014 (IEC 60079-0:2011)
- GOST IEC 60079-1-2011
- GOST 31610.11-2014 (IEC 60079-11:2011)

Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FMG50	_ ********	+	A*B*C*D*E*F*G*.
(Device	(Basic		(Optional
type)	specifications)		specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available.

The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Gammapilot



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

FMG50

XA02009F-A Gammapilot FMG50

Basic specifications

Position 1,	Position 1, 2 (Approval)	
Selected option		Description
FMG50	GP	EAC 1Ex d ia IIC T6T1 Gb X ¹⁾

1) Protection type "Ex d" only available inside the detector pipe

Position 8 (Application)		
Selected option Description		Description
FMG50	Α	Ambient temperature -4060°C/ -40140°F (PVT)
	В	Ambient temperature -2080°C/ -4176°F (PVT HT)
	С	Ambient temperature -4080°C/ -40176°F (NaI)

Position 9 (S	Position 9 (Sensor Length, Material)		
Selected opt	ion	Description	
FMG50	A, B, C	mm; NaI crystal	
	G, H, I, J, K, L, M, N	mm; PVT	

Optional specifications

ID Nx (Accessory Mounted)		
Selected o	ption	Description
FMG50	NA	Overvoltage protection

Safety instructions: General

 Comply with the installation and safety instructions in the Operating Instructions.

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. housing, sensor element, special varnishing, attached additional plates, ..)
 - Of isolated capacities (e.g. isolated metallic plates)


Safety instructions: Special conditions

In the event of additional or alternative special varnishing on the housing or other metal parts:

- Observe the danger of electrostatic charging and discharge.
- Do not rub surfaces with a dry cloth.
- Do not install in the vicinity of processes generating strong electrostatic charges.


XA02009F-A Gammapilot FMG50

Safety instructions: Installation



A004116

- A Zone 1, Zone 2
- B Zone 0, Zone 1, Zone 2
- 1 Detector pipe (in Ex d)
- 2 Housing
- 3 Certified associated apparatus
- 4 Local potential equalization
- After aligning (rotating) the housing, retighten the fixing screw.
- The safety screws at the pipe housing must not be loosened:



A0041226

Intrinsic safety

- \blacksquare The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least 500 $V_{\rm rms}.$
- When the device is connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC and IIB, the type of protection changes to Ex ib IIC and Ex ib IIB.
- Associated devices with galvanic isolation between the intrinsically safe and non-intrinsically safe circuits are preferred.

Potential equalization

Integrate the device into the local potential equalization.

Overvoltage protection

Optional specification, ID Nx = NA

The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least 290 $V_{\rm rms}.\,$

Safety instructions: Ex d joints

- If required or if in doubt: ask manufacturer for specifications.
- Flameproof joints are not intended to be repaired.

Temperature tables

Basic specification, Position 8 = A

Temperature class	Ambient temperature T _a (ambient)
T6T1	$-40 ^{\circ}\text{C} \le \text{T}_{\text{a}} \le +60 ^{\circ}\text{C}$

Basic specification, Position 8 = B

Temperature class	Ambient temperature T _a (ambient)
Т6	-20 °C \leq T _a \leq +60 °C
T4T1	$-20 ^{\circ}\text{C} \le \text{T}_{\text{a}} \le +70 ^{\circ}\text{C}$

Basic specification, Position 8 = C

Temperature class	Ambient temperature T _a (ambient)
T6	$-40^{\circ}\text{C} \le T_a \le +60^{\circ}\text{C}$
T4T1	$-40^{\circ}\text{C} \le \text{T}_{\text{a}} \le +70^{\circ}\text{C}$

Connection data

Power supply $U_i \leq 30 \ V_{DC} \\ I_i \leq 300 \ mA \\ P_i \leq 1 \ W \\ C_i \leq 10 \ nF \\ L_i = 0$





www.addresses.endress.com