

Temperature range

T4 -50°C ... +85°C T5 -50°C ... +70°C T6 -50°C ... +55°C

O

INTRINSICALLY SAFE NONINCENDIVE, FIELD WIRING

IS Class I / Div. 1 / Groups ABCD
NI Class I / Div. 2 / Groups ABCD


N

Sensor circuits (Terminals 1...6)

Uo or Voc or Vt = 7.6 V Io or Isc = 29.3 mA Po = 55.6 mW

Group A, B resp. IIC Co or Ca = $10.4~\mu F$ Lo or La = 40~mH Group C, D resp. IIB, IIA Co or Ca = $160~\mu F$ Lo or La = 400~mH

Installation Notes TMT162



- Use supply wires suitable for 5°C above surroundings.
- Only simple apparatus should be terminated to the sensor connection. Simple apparatus are components as defined by the NEC (1.2 V, 0.1 A, 0.25 mW or 20 μ J).
- Warning: Substitution of components may impair intrinsic safety or suitability for Class I, Division 2.

INTRINSICALLY SAFE

IS Class I / Div. 1 / Groups ABCD

 \triangleright

В

 \cap

O

- Installation should be in accordance with ANSI/ISA RP 12.6.01 "Installation of Intrinsically safe systems for Hazardous (classified) locations" and the National Electrical Code (ANSI/NFPA 70).
- FM Approved Associated Apparatus must meet the following parameters:

 $Uo \le Ui$ $Io \le Ii$ $Po \le Pi$ $Ca \ge Ci + Ccable$ $La \ge Li + Lcable$ Transmitter entity parameters are as follows:

Ui or $Vmax \le 30 \text{ V DC}$ Ci = 5.3 nF

If or Imax $\leq 300 \text{ mA}$ Li = 0

Pi ≤ 1000 mW

Voc + Voc of Handheld device < Vmax, Isc + Isc of Handheld device < Imax,

Po + Po of Handheld device < Pi, Ca > Ci + Ccable + Ci of Handheld device,

La > Li + Lcable + Li of Handheld device, when Programming Handheld device is used.

NONINCENDIVE

NI Class I / Div. 2 / Groups ABCD

 Depending on location install per National Electrical Code (NEC) using wiring methods described in article 500 through article 510.

Intrinsic safety barrier not required. Vmax \leq 40 V DC.

- Warning: Do not disconnect equipment unless power has been switched off or the area is known to be non-hazardous.
- Nonincendive field wiring installation

The Nonincendive Field Wiring Circuit Concept allows interconnection of Nonincendive Field Wiring Apparatus with Associated Nonincendive Field Wiring Apparatus or Associated Intrinsically Safe Apparatus or Associated Apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations, when $Voc \le Vmax$, $Ca \ge Ci + Ccable$, $La \ge Li + Lcable$.

Transmitter Nonincendive Field Wiring parameters are as follows:

Ui or $Vmax \le 40 VDC$ Ci = $\frac{1}{2}$

Ci = 5.3 nF Li = 0

Ii or Imax = see following note below

For these current controlled circuits, the parameter Imax is not required and need not to be aligned with parameter Isc and It of the Associated Nonincendive Field Wiring Apparatus or Associated Apparatus.

Functional ratings

These ratings do not supersede Hazardous Location values

Unom ≤ 40 DC Inom ≤ 4 to 20 mA

)	Approved	Date (yyyy-mm-dd)	Drawing No.	Dwg.rev.	Revision no.	Revision date (yyyy-mm-dd)	Name	Material 71540240	
	Pfanzelt	2003-04-23	14 12 00 111	В	-	2017-05-03	MP		Endress+Hauser 🖼 📗
Volume (mm³)	Designed	Date (yyyy-mm-dd)	Unit	Scale	Title				
	Pfanzelt	2003-04-23	iTEMP TMT162	1:1	CONTRO	DL DRAWING	9 FM	Series	
Refer to protection notice	Edge of working parts	Geometrical tolerancing	Part No.	Format	IS, NI			Objekt version Sheet	Endress + Hauser Wetzer
ISO 16016	ISO 13715	ISO 2768-mH-E	-	A4	10, 111				GmbH+Co. KG Nesselwang / Germany