



1 **EU-TYPE EXAMINATION CERTIFICATE**

2 Equipment intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU

3 Certificate Number: **CSANe 22ATEX1037X** Issue: **1**

4 Equipment: **RXN Series RAMAN Analyzers**

5 Applicant: **Endress+Hauser Optical Analysis, Inc.**

6 Address: **371 Parkland Plaza
Ann Arbor
Michigan 48103
United States of America**

7 This equipment and any acceptable variation thereto is specified in the schedule to this certificate and the documents therein referred to.

8 CSA Group Netherlands B.V., notified body number 2813 in accordance with Articles 17 and 21 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in the confidential reports listed in Section 14.2.

9 Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the schedule to this certificate, has been assured by compliance with the following documents:

EN IEC 60079-0:2018 EN 60079-11:2012 EN 60079-28:2015 EN 50495: 2010

10 If the sign 'X' is placed after the certificate number, it indicates that the equipment is subject to Specific Conditions of Use identified in the schedule to this certificate.

11 This EU-Type Examination Certificate relates only to the design and construction of the specified equipment. If applicable, further requirements of this Directive apply to the manufacture and supply of this equipment.

12 The marking of the equipment shall include the following:



II (2) (1) G
Ex [ia Ga] [op sh Gb] IIC



Signed: M Halliwell

Title: Director of Operations

Project Number 80175908

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

CSANe 22ATEX1037X
Issue 1

13 DESCRIPTION OF EQUIPMENT

RXN2 and RXN4 series of analyzers is designed to monitor, analyze, or optimize reaction chemistry in multiple vessels using the analytical technique of "Raman" spectroscopy. The equipment utilizes a computer controlled spectrometer and laser to accomplish this.

Model Similarity

The RXN2 and RXN4 models have the same internal components with only a slight difference in the enclosure. The RXN4 has a rack-mount type enclosure, while the RXN2 has a desk-top type enclosure. RXN2 IoT and RXN4 IoT utilize the same components as RXN2 and RXN4 respectively. The only difference is an added embedded controller, different mains switch and a different enclosure. The laser output is the same as on the RXN2 and RXN4.

General

The analyzer consists of a stamped aluminium enclosure which is mounted in a non-hazardous location and provides intrinsically safe and fibre-optical signals to up to 4 probes located in a hazardous area, therefore this equipment may be considered as "associated apparatus".

The power inlet is provided within the connection box so that power may be applied to the system when the enclosure is located in a non-hazardous location.

Main Enclosure Laser Output & Spectrometer Input

The laser beam within the enclosure is routed through various optical instruments before being made available at up to 4 bulkhead connectors contained within the connector box compartment. From here, fibre optic cables take the laser light to the process probe which is in contact with the process being monitored. Up to 4 probes may be connected.

Fibre Breakage Interlock

The fibre breakage interlock is also part of the analyser controls, and is formed around an IS repeater (GM Intl., D 1032 Q 4 channel switch / proximity detector repeater) with galvanic isolation of a rating of SIL2, the relay output of which is used to directly interrupt the laser electrical supply (Note: The IS barrier is not part of this work or of this certification as it has its own certification). This was considered as suitably reliable for EPL Gb, based on the SIL2 rating.

Laser Power Interlock

The input optical power to the probes is set by the analyser providing the laser source. The laser power is adjusted for each application so that the appropriate optical power level exits the probe. The power of the laser beam is variable under the control of a computer within the enclosure. A dual channel laser power monitoring circuit is provided that checks the power level produced by the laser and turns off the laser should the power exceed the pre-set maximum limit.

The output of the laser is routed through a beam splitter that divides the light between 2 photo detectors and the main output. The interlock circuitry provides 2 separate paths where the voltage generated by the current through the photo detectors is compared against a pre-set voltage. Provided that the generated voltage is lower than the pre-set voltage, and the corresponding to the laser power being lower than the limit, the power to the laser shall remain connected. Consequently, if either channel of the circuit detects that the power exceeds the limit, the laser is turned off.

Status indicators are provided to assist in the detection of failures in the interlock circuit.

Project Number 80175908

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

CSANe 22ATEX1037X
Issue 1

Calibration Switching Module

The Calibration Switching Module (CSM) provides for a method of monitoring the interlock status on up to 4 probes separately and provide shutdown of the optical power to individual probes, without shutting down the signal to the remaining probes where the interlock is not activated.

Variation 1 - This variation introduced the following changes:

- i. Addition of SAFT battery for RXN2 and RXN4.
- ii. Update drawing to add path for purge tube for RXN4 enclosure.

14 DESCRIPTIVE DOCUMENTS

14.1 Drawings

Refer to Certificate Annexe.

14.2 Associated Reports and Certificate History

Issue	Date	Report number	Comment
0	04 November 2022	R80069337A	The release of the prime certificate.
1	12 October 2023	R80175907A	The introduction of Variation 1.

15 SPECIFIC CONDITIONS OF USE (denoted by X after the certificate number)

- 15.1 The fibre optic cable linking the laser output to the pilot probe shall be installed so that the minimum bend radius specified by the cable manufacturer is not exceeded.
- 15.2 Where it is necessary to monitor the process level to ensure that the optical beam is not exposed to a potentially explosive atmosphere, the devices used to monitor the level shall be intrinsically safe or classed as simple apparatus, and be installed so as to provide a fault tolerance of 2 for Category 1 equipment or fault tolerance of 1 for Category 2 equipment. The functional safety of this arrangement has not been assessed as part of this certification and it is the responsibility of the installer / user to ensure that an appropriate mechanism is in place.
- 15.3 Where IS Galvanic Isolators are added to the main enclosure in order to produce IS signals to external apparatus not covered by this certification, the IS galvanic Isolators shall have an ambient working temperature upper limit of at least 55°C. The IS parameters pertaining to these isolators shall be conveyed to the user in an appropriate manner. The IS nature of any such circuits has not been assessed as part of this certification and this certificate is not to be taken as indication that these IS circuits comply with relevant requirements.

16 ESSENTIAL HEALTH AND SAFETY REQUIREMENTS OF ANNEX II (EHSRs)

The relevant EHSRs that are not addressed by the standards listed in this certificate have been identified and individually assessed in the reports listed in Section 14.2.

17 CONDITIONS OF MANUFACTURE

- 17.1 The use of this certificate is subject to the Regulations Applicable to Holders of CSA Group Netherlands B.V. certificates.
- 17.2 Holders of EU-Type Examination Certificates are required to comply with the conformity to type requirements defined in Article 13 of Directive 2014/34/EU.

Project Number 80175908

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

CSANe 22ATEX1037X
Issue 1

- 17.3 The laser power interlock and fibre-breakage interlock systems operation shall be verified.
- 17.4 Each unit will have a Dielectric Voltage Withstand test performed on it with a test voltage of 1400VAC for 2 seconds.
- 17.5 Each unit will have a Ground Bond/Continuity test performed on it.

Project Number 80175908

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands

Certificate Annexe



Certificate Number: CSANe 22ATEX1037X
Equipment: RXN Series RAMAN Analyzers
Applicant: Endress+Hauser Optical Analysis, Inc.

Issue 0

Drawing	Sheets	Rev.	Date (Stamp)	Title
2007871-101	1 of 1	R2	26 Apr 21	Jumper, interlock
2009234	1 of 1	R6	04 Oct 22	Block Diagram, laser and AC power interlocks
2011685	1 of 1	X3	26 Apr 21	RXN4, ATEX KIT
2011965	1 of 1	X7	26 Apr 21	Integrated Invictus Interlock System
2012000	1 of 1	X2	26 Apr 21	RXN2, 4 CHANNEL ATEX KIT
2012006	1 of 1	X1	26 Apr 21	Assembly, RXN3L, ATEX KIT
2013443	1 of 1	X3	04 Oct 22	RXN Interlock System, Laser Power Interlock, GEN II CSM
4002017	1 to 5	X1	26 Apr 21	Laser Power Control and safety interlock
4002019	1 to 6	X1	26 Apr 21	Safety statement, RXN Invictus Laser, IS Barrier, Interlock connector and probe system
4002251	1 of 1	R4	22 Sep 22	Haz Label, Base Non-Haz Zone Schematic
2017750	1 of 1	X2	16 Sep 22	Rear Panel

Issue 1

Drawing	Sheets	Rev.	Date (Stamp)	Title
4002251	1 to 2	02.23	04 Oct 23	Haz Label, Base Non-Haz Zone Schematic
2022055	1 to 2	B	04 Oct 23	ATEX Kit, RXN2 and RXN4 IoT

Project Number 80175908

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands