Safety Instructions **RID14**

PROFIBUS® PA, FOUNDATION Fieldbus™

ATEX: II 3G Ex nA IIC T6...T4 Gc

Safety instructions for electrical apparatus in explosion-hazardous areas







RID14 XA01001K

RID14

PROFIBUS® PA, FOUNDATION Fieldbus™

Table of contents

About this document	4
Associated documentation	4
Supplementary documentation	4
Manufacturer´s certificates	5
Manufacturer address	5
Safety instructions:	6
Safety instructions: Installation	6
Temperature tables	7
Electrical connection data	7

XA01001K RID14


About this document



This document has been translated into several languages. Legally determined is solely the English source text.

The document translated into EU languages is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Manuals and Datasheets -> Type: Ex Safety Instruction (XA) -> Text Search: ...
- In the Device Viewer: www.endress.com -> Product tools -> Access device specific information -> Check device features



Associated documentation

This document is an integral part of the following Operating Instructions:

- Operating instructions: BA00282R and BA01267K
- Brief operating instructions: KA00281R and KA01156K
- Technical information: TI00145R

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website:
 www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP000217.
- On the CD for devices with CD-based documentation

RID14 XA01001K

Manufacturer's certificates

EU Declaration of Conformity

Certificate number: EC_00170

Affixing the certificate number certifies conformity with the following standards (depending on the device version)


EN IEC 60079-0: 2018EN 60079-15: 2010

Manufacturer address

Endress+Hauser Wetzer GmbH + Co. KG Obere Wank 1 87484 Nesselwang, Germany

XA01001K RID14

Safety instructions:



A0048971

■ 1 Installation of the field indicator

Safety instructions: Installation

- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and any other valid standards and regulations (e.g. EN/IEC 60079-14).
- Seal the cable entries tight with certified cable glands (min. IP6X)
 IP6X according to EN/IEC 60529.
- For operating the field indicator at an ambient temperature under −20 °C, appropriate cables, cable entries and sealing facilities permitted for this application must be used.
- The housing of field indicator must be connected to the potential matching line.
- For ambient temperatures higher than +70 °C, use suitable heatresisting cables or wires, cable entries and sealing facilities for Ta +5 K above surrounding.
- The field indicator must be installed and maintained so, that even in the event of rare incidents, an ignition source due to impact or friction between the enclosure and iron/steel is excluded.

▲ WARNING

Explosive atmosphere

► In an explosive atmosphere, do not open the device when voltage is supplied (ensure that the IP67 housing protection is maintained during operation).

RID14 XA01001K

Temperature tables

Туре	Temperature class	Ambient temperature	
RID14	Т6	-40 °C ≤ Ta ≤ +50 °C	
	T5	-40 °C ≤ Ta ≤ +70 °C	
	T4	-40 °C ≤ Ta ≤ +80 °C	

Electrical connection data

Туре	Type of protection	Power supply (terminals + and -)
RID14	Ex nA IIC T6T4 Gc Output: FOUNDATION Fieldbus TM PROFIBUS PA® Current consumption ≤ 11 mA	$U_b \le 9 \text{ to } 32 \text{ V}_{DC}$

Category	Type of protection	Туре
II 3G	Ex nA IIC T6T4 Gc	RID14



www.addresses.endress.com