Safety Instructions Nivotester FTL325P

[Ex ia Ga] IIC







Nivotester FTL325P

Table of contents

About this document	4
Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Extended order code	4
Safety instructions: General	6
Safety instructions: Installation	7
Temperature tables	10
Connection data	10

About this document	This document has been translated into several languages. Legally determined is solely the English source text.
Associated documentation	This document is an integral part of the following Operating Instructions:
	BA01970F/00, BA01971F/00
Supplementary	Explosion-protection brochure: CP00021Z/11
documentation	 The Explosion-protection brochure is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP00021Z
	 On the CD for devices with CD-based documentation
Manufacturer's certificates	Certificate of Conformity
certificates	Certificate number: TÜV 13.0913 X
	Affixing the certificate number certifies conformity with the following standards (depending on the device version):
	ABNT NBR IEC 60079-0:2020ABNT NBR IEC 60079-11:2013
Manufacturer address	Endress+Hauser SE+Co. KG Hauptstraße 1
address	79689 Maulburg, Germany Address of the manufacturing plant: See nameplate.
Extended	The extended order code is indicated on the nameplate, which is affixed
order code	to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FTL325P	-	******	+	A*B*C*D*E*F*G*
(Device		(Basic		(Optional
type)		specifications)		specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications


The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Nivotester



- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type FTL325P

Basic specifications

Position 1 (Approval)		
Selected option Description		
FTL325P	1	INMETRO [Ex ia Ga] IIC
	2	INMETRO [Ex ia Ga] IIC; SIL

Position 2 (Housing)		
Selected option Description		
FTL325P	P 1 Rail mounting, 22.5 mm, 1-channel	
	3	Rail mounting, 45 mm, 3-channel

Position 3 (Power Supply)		
Selected option Description		
FTL325P	А	85-253 V AC
	Е	20-30 V AC / 20-60 V DC

Position 4 (Switch Output)		
Selected option Description		
FTL325P 1 1x SPDT level + 1x SPST alarm		1x SPDT level + 1x SPST alarm
	3	3x SPDT level + 1x SPST alarm

Optional specifications


No options specific to hazardous locations are available.

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging.

Safety instructions: Installation


One channel version



1


- 1 PFM sensor, Limit level
- 2 PFM sensor
- 3 Level relay
- 4 Fault signal relay
- 5 Power supply

Three channel version



፼ 2

- CH1 Channel 1
- CH2 Channel 2
- CH3 Channel 3
- 1 PFM sensor, Limit level
- 2 PFM sensor
- 3 Level relay
- 4 Fault signal relay
- 5 Power supply



🛃 3

- A Min. 6 mm
- 1 Intrinsically safe contacts
- 2 Nivotester FTL325P
- 3 Other type, other product
- To achieve an ingress protection of at least IP55: Protect the device from dust and humidity, e.g. in control rooms, or located in a suitable protective enclosure.
- The device is an associated apparatus: Only use the device outside explosion hazardous areas.
- There must be a distance (thread measure) of at least 50 mm between intrinsically safe and nonintrinsically safe terminals.
- When combining the device with other types and products on the same top-hat rail: Keep the distances comply to the relevant standards and rules.
- When combining with devices from other manufacturers: Observe ingress protection of the enclosure.

Intrinsic safety

- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- The intrinsically-safe input circuits are galvanically isolated from other circuits up to a peak value of the nominal voltage of 375 V.

Temperature tables

Ambient temperature range	
Individual installation	$-20 \ ^{\circ}\text{C} \le T_a \le +60 \ ^{\circ}\text{C}$
Series installation	$-20 \ ^{\circ}C \le T_{a} \le +50 \ ^{\circ}C$

Connection data

Power supply circuit					
Terminal connections: 1, 2	AC voltage	$\begin{array}{l} U=85 \mbox{ to } 253 \ V_{AC}, \ 50/60 \ Hz \\ P\leq 2.0 \ W \ (one \ channel \ version) \\ P\leq 4.2 \ W \ (three \ channel \ version) \end{array}$			
	DC voltage	$\begin{array}{l} U = 20 \mbox{ to } 60 \ V_{DC} \\ U = 20 \mbox{ to } 30 \ V_{AC}, \ 50/60 \ Hz \\ P \leq 1.7 \ W \ (one \ channel \ version) \\ P \leq 4.0 \ W \ (three \ channel \ version) \end{array}$			

Contact circuit	
Level relay Terminal connections: Channel 1 (CH1): 4, 5, 6 Channel 2 (CH2): 22, 23, 24 ¹⁾ Channel 3 (CH3): 26, 27, 28 ¹⁾	U \leq 250 V_AC, I \leq 2 A, P \leq 500 VA at cos ϕ \geq 0.7 U \leq 40 V_DC, I \leq 2 A, P \leq 80 W
Fault signal relay Terminal connections: 15, 16	

1) not available in one channel version

Sensor circuit					
Terminal connections: Channel 1 (CH1): 7, 8 Channel 2 (CH2): 33, 34 ¹⁾ Channel 3 (CH3): 37, 38 ¹⁾	Connection data:	U₀ ≤ 14.6 V I₀ ≤ 97 mA P₀ ≤ 633 mW Trapezium-shaped chan		$\begin{array}{l} R_i \geq 273 \; \Omega \\ C_i \leq 19 \; nF \\ L_i = 0 \end{array}$ racteristic	
		[Ex ia Ga]	IIC	[Ex ia Ga] IIB	
		Lo	Co	Lo	Co
	Max. external capacitance at max. external inductance	0.5 mH	300 nF	1.0 mH	1.0 µF
		1.0 mH	200 nF	5.0 mH	500 nF
	Max. external capacitance or max. external inductance	3.0 mH	640 nF	15 mH	3.9 µF
If using explosion protection group		[Ex ib Gb] IIC		[Ex ib Gb] IIB	
[Ex ib Gb] IIC/IIB the application is limited to II (2) G		L _o	Co	Lo	Co
	Max. external capacitance or max. external inductance	3.0 mH	640 nF	15 mH	3.9 µF

1) not available in one channel version



71570305

www.addresses.endress.com

