

# Safety Instructions

## Indumax CLS50D, CLS50

ATEX / NEPSI Ex ic IIC T3 T4/T6 Gc



---

# Indumax CLS50D, CLS50

ATEX / NEPSI Ex ic IIC T3 T4/T6 Gc

## Table of contents

Associated documentation . . . . .	4
Supplementary documentation . . . . .	4
Certificates . . . . .	4
Identification . . . . .	4
Safety instructions . . . . .	4
Temperature tables . . . . .	5
Connection . . . . .	5
Installation conditions . . . . .	5

**Associated documentation**

Operating Instructions for Indumax CLS50D/CLS50, BA00182C

**Supplementary documentation**

Competence Brochure CP00021Z

- Explosion Protection: Guidelines and General Principles
- [www.endress.com](http://www.endress.com)

**Certificates**

The number of the Nepsi certificate that applies to the product can be found on the product nameplate.

**Identification**

The nameplate provides you with the following information on your device:

- Manufacturer identification
  - Extended order code
  - Serial number
  - Safety information and warnings
  - Ex marking on hazardous area versions
- Compare the information on the nameplate with the order.

**Type code**

Type	Version						
CLS50D	-	BV	a <sup>1)</sup>	b <sup>2)</sup>	c <sup>3)</sup>	d <sup>4)</sup>	+ e ... e <sup>5)</sup>

- 1) Process connection (no Ex relevance)
- 2) Sensor, seal, adapter material; B: PEEK, VITON, PEEK; C: PEEK, Chemraz, PEEK; D: PFA, Chemraz, 1.4571
- 3) Cable length (no Ex relevance), 1: 3 m, 2: 7 m, 3: 15 m, 7: 1 to 50 m, 8: 1 to 164 ft
- 4) Cable connection (no Ex relevance), 1: Fixed cable, crimp sleeves, 2: Fixed cable with M12 connector
- 5) Additional options (no Ex relevance), calibration, service, other approvals, measuring point identification

Type	Version					
CLS50	-	V	a <sup>1)</sup>	b <sup>2)</sup>	c <sup>3)</sup>	+ d <sup>4)</sup>

- 1) Process connection (no Ex relevance)
- 2) Sensor, seal, adapter material; A: PFA, Chemraz, 1.4571; B: PEEK, VITON, PEEK; C: PEEK, Chemraz, PEEK
- 3) Cable connection (no Ex relevance), 1: 5 m (125 °C), 2: 10 m (125 °C), 3: 20 m (125 °C), 4: 10 to 55 m (125 °C), 5: 5 m (180 °C), 6: 10 m (180 °C)
- 4) Optional tagging (no Ex relevance)

**Certificates and approvals***Ex approvals*

ATEX / NEPSI Ex ic IIC T3 T4/T6 Gc

CLS50D and CLS50 type conductivity sensors have been certified by the National Supervision and Inspection Centre for Explosion Protection and Safety of Instrumentation (NEPSI).

**Safety instructions**

- The sensor may be operated in an environment specified as Ex Zone 2 (3G).
- The sensor may only be connected to the following transmitter:  
Liquiline type CM42-LV (CLS50D) or CM42-IV (CLS50), EU Declaration of Conformity EC\_00143
- Compliance with the specified ambient and medium temperature ranges is a prerequisite for safe use.
- The sensor must be connected and operated in accordance with the Operating Instructions of the sensor and of the transmitter to be connected. All sensor operating data must be observed.
- The sensors may only be used in liquid media with a conductivity >10 nS/cm.

- Avoid electrostatic charge. Metallic process connection parts have to be mounted electrostatically conductive at the mounting location ( $R \leq 1 \text{ M}\Omega$ ).
- Non-metal process connections must be protected against electrostatic charge.
- In order to avoid electrostatic charge clean the sensor with a damp cloth only.
- Full compliance with regulations for electrical systems in explosive atmospheres (EN/IEC 60079-14) is mandatory when using the devices and sensors.
- Ensure correct installation to maintain the housing protection type. (Use original seal. Fit cable entry properly. Tighten nut).
- The IP68 degree of protection applies only when the flange is mounted.
- When installing, using and maintaining the sensor, the operator must observe the following standards in addition to the Operating Instructions:
  - GB 50257-2014 "Code for construction and acceptance of electric equipment on fire and explosion hazard electrical equipment installation engineering"
  - GB 3836.13-2021 "Explosive atmospheres - Part 13: Equipment repair, overhaul, reclamation and modification"
  - GB/T 3836.15-2017 "Explosive atmospheres - Part 15: Electrical installations design, selection and erection"
  - GB/ T 3836.16-2017 "Explosive atmospheres - Part 16: Electrical installations inspection and maintenance"
  - GB/T 3836.18-2017 "Explosive atmospheres - Part 18: Intrinsically safe electrical systems"
- To ensure that the explosion protection of the device is maintained, the operator must not change the configuration. Any modification may affect safety.
- Observe the instructions of the NEPSI certificate. You can download these from the website of the product: [www.endress.com/cls50d](http://www.endress.com/cls50d) or [www.endress.com/cls50](http://www.endress.com/cls50).

### Temperature tables

Type	Temperature class	
	T4	T6
CLS50D-BV*B** CLS50D-BV*C**	$-20 \text{ }^\circ\text{C} \leq T_a \leq 120 \text{ }^\circ\text{C}$	$-20 \text{ }^\circ\text{C} \leq T_a \leq 70 \text{ }^\circ\text{C}$
CLS50D-BV*D**	$-20 \text{ }^\circ\text{C} \leq T_a \leq 110 \text{ }^\circ\text{C}$	$-20 \text{ }^\circ\text{C} \leq T_a \leq 70 \text{ }^\circ\text{C}$
CLS50-V***	$-20 \text{ }^\circ\text{C} \leq T_a \leq 125 \text{ }^\circ\text{C}$	$-20 \text{ }^\circ\text{C} \leq T_a \leq 75 \text{ }^\circ\text{C}$

The temperature tables apply only under the installation conditions described in the Operating Instructions. If the installation conditions cannot be met, the maximum process temperature  $T_p$  must not exceed the maximum ambient temperature  $T_a$ .

### Connection

#### Ex-specification

- The sensor may only be connected to the following transmitter:  
Liquiline type CM42-LV (CLS50D) or CM42-IV (CLS50)
- Only CLS50-V\*\*\*: The maximum permitted length of the measuring cable is 55 m (180 ft) here.

### Installation conditions



Operating Instructions for Indumax CLS50D/CLS50, BA00182C

---

---



71597541

[www.addresses.endress.com](http://www.addresses.endress.com)

---