

Field Xpert SMT77 – optimized mobile maintenance

Universal, high-performance tablet PC for mobile plant asset management

www.endress.com/smt77

Out of the box – with pre-installed applications and driver library

Saves time and effort by automatically uploading device configuration reports to Netilion Library

Intuitive operation via its touch-optimized user interface – no training needed

Faster commissioning and NAMUR NE 107 diagnosis with “one-click” automatic connectivity

Open Windows 10 IoT Enterprise Operating System to install 3rd party software as well

Netilion “Ready”
Enhanced part of Endress+Hauser’s IIoT ecosystem Netilion

Connectivity Anywhere
■ Wi-Fi IEEE 802.11 a/b/g/n/ac
■ Bluetooth 4.1 LE, Class 1
■ 4G LTE, GPS (optional)

Improved Productivity
Automatic online application software, DTM and driver update services offer new functionalities with maximum security

Durable Design
■ Built for use in Ex Zone 1

Languages
Touch-enabled device configuration software in 20 languages

All major protocols
Supports HART, PROFIBUS, FOUNDATION Fieldbus, Modbus, EtherNet/IP and more to come

Battery Life
Up to 3 hours standard or optional 5 hours

Netilion Library
... makes the collective knowledge of your production facility available to your employees immediately, anytime and anywhere

Bluetooth
Automatic connection to Endress+Hauser Bluetooth devices

Better Display
10.1” multi-touch HD display for more leeway to get your work done

Accessories for Flexibility
A number of accessories are available to customize it to your individual needs

Heartbeat Technology
Integrated Heartbeat Verification incl. PDF documentation

CP013775/04-REV/03.21

