# Safety Instructions Deltapilot M FMB50, FMB51

4-20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus

ATEX, IECEx: Ex ia IIC Ga/Gb Ex ia IIIC Da/Db



XA00476P-D/00/EN/

17.21 71538607 2021-08-19





# Deltapilot M FMB50, FMB51

4-20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus

## Table of contents

About this document	This document has been translated into several languages. Legally determined is solely the English source text.
	<ul> <li>The document translated into EU languages is available:</li> <li>In the download area of the Endress+Hauser website: www.endress.com -&gt; Downloads -&gt; Manuals and Datasheets -&gt; Type: Ex Safety Instruction (XA) -&gt; Text Search:</li> <li>In the Device Viewer: www.endress.com -&gt; Product tools -&gt; Access device specific information -&gt; Check device features</li> </ul>
	If not yet available, the document can be ordered.
Associated documentation	This document is an integral part of the following Operating Instructions:
	HART BA00382P/00
	PROFIBUS PA
	BA00383P/00
	FOUNDATION Fieldbus BA00384P/00
Supplementary	Explosion-protection brochure: CP00021Z/11
documentation	<ul> <li>The Explosion-protection brochure is available:</li> <li>In the download area of the Endress+Hauser website: www.endress.com -&gt; Downloads -&gt; Brochures and Catalogs -&gt; Text Search: CP00021Z</li> <li>On the CD for devices with CD-based documentation</li> </ul>
	- On the CD for devices with CD based documentation
Manufacturer's certificates	EU Declaration of Conformity
certificates	Declaration Number: EG10004
	The EU Declaration of Conformity is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Declaration -> Type: EU Declaration -> Product Code:
	EU type-examination certificate
	Certificate number:

KEMA 09ATEX0048 X

List of applied standards: See EU Declaration of Conformity.

#### **IEC Declaration of Conformity**

Certificate number: IECEx KEM 09.0016X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- IEC 60079-0:2017
- IEC 60079-11:2011
- IEC 60079-26 : 2014

Manufacturer	Endress+Hauser SE+Co. KG
address	Hauptstraße 1
	79689 Maulburg, Germany
	Address of the manufacturing plant: See nameplate.

**Other standards** Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres Explosion prevention and protection Part 1: Basic concepts and methodology"

ExtendedThe extended order code is indicated on the nameplate, which is affixedorder codeto the device in such a way that it is clearly visible. Additional<br/>information about the nameplate is provided in the associated<br/>Operating Instructions.

#### Structure of the extended order code

FMB5x	-	*********	+	A*B*C*D*E*F*G*
(Device		(Basic		(Optional
type)		specifications)		specifications)

\* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

#### Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

#### Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

#### Extended order code: Deltapilot M



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type FMB50, FMB51

Basic specifications

Position 1,	Position 1, 2 (Approval)	
Selected option		Description
FMB50	B1	ATEX II 1/2 G Ex ia IIC T6T4 Ga/Gb ATEX II 1/2 D Ex ia IIIC T <sub>200</sub> 100°C Da/Db
	I1	IECEx Ex ia IIC T6T4 Ga/Gb IECEx Ex ia IIIC T $_{200}$ 100°C Da/Db
FMB51	B1	ATEX II 1/2 G Ex ia IIC T6T4 Ga/Gb ATEX II 1/2 D Ex ia IIIC T <sub>200</sub> 85°C Da/Db
	I1	IECEx Ex ia IIC T6T4 Ga/Gb IECEx Ex ia IIIC T <sub>200</sub> 85°C Da/Db

Position 3 (Output)       Selected option     Description		
		Description
FMB5x	2	4-20 mA HART
	3	PROFIBUS PA
	4	FOUNDATION Fieldbus

#### **Optional specifications**


No options specific to hazardous locations are available.

#### Safety • The device is intended to be used in explosive atmospheres as defined in the scope of IEC 60079-0 or equivalent national standards. If no instructions: General potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications. • Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device: • Be suitably qualified for their role and the tasks they perform Be trained in explosion protection Be familiar with national regulations Comply with the installation and safety instructions in the Operating Instructions. Install the device according to the manufacturer's instructions and national regulations. • Only use the device in media to which the wetted materials have sufficient durability. • Avoid electrostatic charging: • Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ..) Of isolated capacities (e.g. isolated metallic plates) Safetv In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic instructions: Special conditions surfaces. • For light metal flanges or flange faces (e.g. titanium, zirconium), avoid sparks caused by impact and friction. • In the event of additional or alternative special varnishing on the enclosure or other metal parts:

- Observe the danger of electrostatic charging and discharge.
- Do not rub surfaces with a dry cloth.

#### Endress+Hauser

#### Safety instructions: Installation



- A Electronic; Zone 1 or Zone 21
- B Process; Zone 0 or Zone 20
- 1 Certified associated apparatus
- 2 FMB50, FMB51

The device is designed for operation in Zone 1 or Zone 21 (enclosure) as well as Zone 0 or Zone 20 (process connection). In the event of potentially explosive gas-air and dust-air mixtures occurring simultaneously: Suitability requires further assessment.

#### Intrinsic safety

- When the device is connected to an intrinsically safe circuit Ex ib, the type of protection changes to Ex ib. Do not operate intrinsically safe circuits Ex ib in Zone 0 or Zone 20.
- When the device is connected to an intrinsically safe circuit Ex ic, the type of protection changes to Ex ic. Do not operate intrinsically safe circuits Ex ic in Zone 0, Zone 1 or Zone 20, Zone 21.
- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least 500  $\rm V_{rms}.$

#### Device type FMB51

Mechanically fix probes which are more than 3 m (e.g. using guy ropes).

Safety instructions: Zone 20, Zone 21	<ul> <li>Seal the cable entry or piping tight (see protection type of enclosure in the "Temperature tables" chapter).</li> <li>Connect the device using suitable cable and wire entries of protection type "Equipment dust ignition protection by enclosure (Ex t)" or "Increased safety (Ex e)" (ingress protection of at least IP65). Lay connecting cable and secure.</li> </ul>
Temperature tables	<ul> <li>The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.</li> <li>Do not exceed the max. ambient temperature at the enclosure.</li> </ul>
	Device type FMB50 The process temperatures refer to the temperature at the separation membrane.
	<i>Device type FMB51</i> The process temperatures refer to the temperature at the rod.

#### Ex ia IIC T6...T4 Ga/Gb

Device type FMB50

Temperature class	Process temperature T <sub>p</sub> (process)	Ambient temperature range
Т6	≤ 80 °C	$-40 \ ^\circ C \le T_a \le +40 \ ^\circ C$
T4	≤ 100 °C	$-40 \ ^\circ C \le T_a \le +70 \ ^\circ C$

### Device type FMB51

Temperature class	Process temperature T <sub>p</sub> (process)	Ambient temperature range
Т6	≤ 80 °C	$-40 \ ^\circ C \le T_a \le +40 \ ^\circ C$
T4	≤ 85 °C	$-40 \ ^\circ\text{C} \le T_a \le +70 \ ^\circ\text{C}$

#### Ex ia IIIC T<sub>200</sub> xxx°C Da/Db

- The specified surface temperature takes into account all direct H heat influences from process heat and self-heating at the enclosure.
  - The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
  - Do not exceed the max. ambient temperature at the enclosure.
  - The process temperatures refer to the temperature at the separation membrane.

#### Device type FMB50

Maximum surface temperature	Process temperature range	Ambient temperature range
T100 °C	$-10 \ ^\circ\text{C} \le T_p \le +80 \ ^\circ\text{C}$	$-40 \ ^\circ\text{C} \le T_a \le +50 \ ^\circ\text{C}$
	$-10 \ ^\circ C \le T_p \le +100 \ ^\circ C$	$-40 \ ^\circ C \le T_a \le +45 \ ^\circ C$

Specific conditions of use:

The surface temperature is

- for equipment protection level (EPL) Da: T<sub>200</sub> 100 °C (with 200 mm) dust deposit)
- and equipment protection level (EPL) Db:  $T_L$  100 °C (with dust accumulation  $T_I$ )

Device type FMB51

- 11	Maximum surface temperature	Process temperature range	Ambient temperature range
	T85 ℃	$-10 \ ^\circ C \le T_p \le +85 \ ^\circ C$	$-40 \ ^\circ\text{C} \le T_a \le +40 \ ^\circ\text{C}$

Specific conditions of use:

The surface temperature is

- for equipment protection level (EPL) Da: T<sub>200</sub> 85 °C (with 200 mm dust deposit)
- and equipment protection level (EPL) Db: T<sub>L</sub> 85 °C (with dust accumulation  $T_{T}$ )



 $T_L$  marking:

The assigned surface temperature without dust layer is the same.

#### **Connection data** Basic specification, Position 3 = 2

Power supply	
$U_i \le 30 V_{DC}$	
I <sub>i</sub> ≤ 300 mÅ	
$P_i \le 1 W$	
C <sub>i</sub> ≤ 10 nF	
$L_i = 0$	

#### *Basic specification, Position* 3 = 3, 4

Power supply		
FISCO	Entity	
$ \begin{array}{l} U_i \leq 17.5 \ V_{DC} \\ I_i \leq 500 \ mA \\ P_i \leq 5.5 \ W \\ C_i \leq 5 \ nF \\ L_i \leq 10 \ \mu H \end{array} $	$\begin{array}{l} U_{i} \leq 24 \; V_{DC} \\ I_{i} \leq 250 \; mA \\ P_{i} \leq 1.2 \; W \\ C_{i} \leq 5 \; nF \\ L_{i} \leq 10 \; \mu H \end{array}$	

#### Cable entry: Connection compartment

Thread	Clamping range	Material	Sealing insert	O-ring
M20x1,5	ø 8 to 10.5 mm <sup>1)</sup> ø 6.5 to 13 mm <sup>2)</sup>	Ms, nickel-plated	Silicone	EPDM (ø 17x2)

#### 1) Standard

2) Separate clamping inserts available

- The tightening torque refers to cable glands installed by the manufacturer:
  - Recommended: 3.5 Nm
  - Maximum: 10 Nm
  - This value may be different depending on the type of cable. However, the maximum value must not be exceeded.
- Only suitable for fixed installation. The operator must pay attention to a suitable strain relief of the cable.
- To maintain the ingress protection of the housing: Install the housing cover, cable glands and blind plugs correctly.



71538607

# www.addresses.endress.com

