

**Company** Endress+Hauser SE+Co. KG, Hauptstraße 1, 79689 Maulburg

being the manufacturer, declares that the "Product contact materials" of the products

**Product** Minicap FTC260  
with sensor rod (PPS-GF)

are in conformity with following European Regulations:

**Regulations** Regulation (EC) No. 1935/2004, on materials and articles intended to come into contact with food, article 3, 5, 15 and 17.

Regulation (EC) No. 2023/2006 on good manufacturing practice for materials and articles intended to come into contact with food.

Regulation (EU) 10/2011 on plastic materials and articles intended to come into contact with food.

DIN 10955:2004-06 Sensory evaluation (Sensory analysis - Testing of packaging materials and packages for foodstuffs), June 2004

**Conditions** The total migration as well as the specific migrations are below the legal limits when used according to specifications.

The test was carried out in accordance with the guidelines:

- EN 1186 Materials and articles in contact with foodstuffs – Plastics, May 2002
- EN 14338 Paper and board intended to come into contact with foodstuffs – Conditions for determination of migration from paper and board using modified polyphenylene oxide (MPPO) as a simulant, March 2004

The materials and raw materials used comply with the latest version of EU/10/2011 regulation.

#### Specification for the intended use or restrictions:

Type of food or process for which the material is suitable:

- Aqueous, acidic, alcoholic, milky, fatty and oily, dry foodstuffs


Duration and temperature of treatment and storage in contact with the food:

- The material is suitable for long-term contact with solids and for multiple contact with food in liquid form

Ratio of the area in contact with foodstuffs to the volume by which conformity of the material or article was established:

- 6 dm<sup>2</sup> / 1 kg Foodstuff

Maulburg, 2018-05-02  
Endress+Hauser SE+Co. KG



i.V. Dr. Dietmar Frühauf  
Dept. Manager Level Limit  
Research & Development Devices