# Safety Instructions Prosonic S FMU90, FMU95

II 3 D Ex tc IIIC Dc







Prosonic S FMU90, FMU95 XA00326F-D

# Prosonic S FMU90, FMU95

### Table of contents

About this document 4
Associated documentation
Supplementary documentation
Manufacturer's certificates
Manufacturer address
Other standards
Extended order code
Safety instructions: General
Safety instructions: Special conditions
Safety instructions: Installation
Temperature tables
Connection data 8

XA00326F-D Prosonic S FMU90, FMU95

### About this document



This document has been translated into several languages. Legally determined is solely the English source text.

The document translated into EU languages is available:

- In the download area of the Endress+Hauser website:
   www.endress.com -> Downloads -> Manuals and Datasheets ->
   Type: Ex Safety Instruction (XA) -> Text Search: ...
- In the Device Viewer: www.endress.com -> Product tools -> Access device specific information -> Check device features



If not yet available, the document can be ordered.

# Associated documentation

This document is an integral part of the following Operating Instructions:

- BA00288F/00, BA00289F/00, BA00290F/00, BA00292F/00, BA00293F/00 (FMU90)
- BA00344F/00, BA00345F/00 (FMU95)

# Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website:
   www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP00021Z
- On the CD for devices with CD-based documentation

# Manufacturer's certificates

#### **EU Declaration of Conformity**

Declaration Number:

EG06006

The EU Declaration of Conformity is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Declaration -> Type: EU Declaration -> Product Code: ...

#### EU type-examination certificate

Certificate number:

EG 06 006 X

List of applied standards: See EU Declaration of Conformity.

Prosonic S FMU90, FMU95 XA00326F-D

# Manufacturer address

Endress+Hauser SE+Co. KG Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

#### Other standards

Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres Explosion prevention and protection - Part 1: Basic concepts and methodology"

# Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

#### Structure of the extended order code

FMU9x	-	******	+	A*B*C*D*E*F*G*
(Device		(Basic		(Optional
type)		specifications)		specifications)

\* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

### Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available.

The selected option of a feature can consist of several positions.

### Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

XA00326F-D Prosonic S FMU90, FMU95

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

#### Extended order code: Prosonic S



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

FMU90, FMU95

#### Basic specifications

Position 1 (Approval)			
Selected option	Description		
FMU9x J	ATEX II 3 D Ex tc IIIC T 90 °C Dc		

Position 5	(Power Su	pply)
Selected op	ption	Description
FMU9x	A	90-253VAC
	В	10.5-32VDC

### Optional specifications

No options specific to hazardous locations are available.

Prosonic S FMU90, FMU95 XA00326F-D

### Safety instructions: General


 Comply with the installation and safety instructions in the Operating Instructions.

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging:
  - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ..)
  - Of isolated capacities (e.g. isolated metallic plates)

### Safety instructions: Special conditions

- The device corresponds to the "low" strain level. It must be mounted in a protected position, if mechanical stress is to be expected.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts:
  - Observe the danger of electrostatic charging and discharge.
  - Do not rub surfaces with a dry cloth.

### Safety instructions: Installation



A0033252

- A Zone 1. Zone 2. Zone 20. Zone 21. Zone 22
- B Zone 22
- 1 Tank; Zone 1, Zone 2, Zone 20, Zone 21, Zone 22
- 2 Ultrasonic sensor FDU90, FDU91(F), FDU92, FDU93, FDU95
- 3 Analysing and controlling unit Prosonic S FMU90, FMU95

XA00326F-D Prosonic S FMU90, FMU95

- To maintain the ingress protection of the enclosure IP66: Install the enclosure cover, cable glands and blind plugs correctly.
- Connect the device using suitable cable and wire entries of protection type "Equipment dust ignition protection by enclosure (Ex t)" or "Increased safety (Ex e)" (ingress protection of at least IP65). Lay connecting cable and secure.
- Replace fuses only with identical parts.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection.

## Temperature tables

Maximum permissible ambient temperature	Maximum surface temperature
−10 to +60 °C	+90 °C 1)

1) Measured at an ambient temperatur of +60 °C

#### Connection data

#### **Supply voltage** (observe nameplate)

Alternating current	
Max. voltage range	U = 90 to 253 V <sub>AC</sub> , 50/60 Hz
Fuse (observe type)	400 mA
Max. power consumption	23 VA

Direct current	
Max. voltage range	U = 10.5 to 32 V <sub>DC</sub>
Fuse (observe type)	2 A
Max. power consumption	14 W







www.addresses.endress.com