Safety Instructions **Deltabar M PMD55**

4-20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus

Ex d IIC T4/T6 Gb



Document: XA00514P-D Safety instructions for electrical apparatus for explosion-hazardous areas $\rightarrow \cong 3$



Deltabar M PMD55

4-20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus

Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Extended order code	4
Safety instructions: General	5
Safety instructions: Special conditions	6
Safety instructions: Installation	6
Temperature tables	6
Connection data	6

Associated documentation	This document is ar	ı integral pa	rt of the following Operatin	g Instructio	ons:
	HART				
	BA00382P/00				
	PROFIBUS PA BA00383P/00				
	FOUNDATION Field BA00384P/00	lbus			
	511005011700				
Supplementary	Explosion-protectio	n brochure:	CP00021Z/11		
documentation	www.endress.com Documentation T	area of the E n -> Downl ype: Brochu	ure is available: Endress+Hauser website: loads -> Media Type: Docu res and catalogs -> Text Se D-based documentation		
Manufacturer's certificates	NEPSI Declaration	of Conform	ity		
	Certificate number: GYJ19.1357X				
	Affixing the certific device version):	ate number	certifies conformity with th	e following	g standards (depending on the
	GB3836.1-2010GB3836.2-2010				
Manufacturer address	Endress+Hauser SE Hauptstraße 1 79689 Maulburg, G Address of the man	ermany	olant: See nameplate.		
Extended order code		ble. Additior			ed to the device in such a way s provided in the associated
	Structure of the ex	tended ord	er code		
	PMD55	-	*****	+	A*B*C*D*E*F*G*
	(Device type)		(Basic specifications)		(Optional specifications)
	* = Placeholder At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.				
	Basic specifications				
	basic specifications.	The numbe	y essential for the device (m er of positions depends on th e can consist of several posit	ne number	eatures) are specified in the of features available.
	Optional specification	ons			
	The number of posi	tions depend		es available	(optional features). . The features have a 2-digit ne feature group and consists

of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Deltabar M

The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

PMD55

Basic specifications

Position 1, 2 (Approval)		
Selected option		Description
PMD55	NB	NEPSI Ex d IIC T4/T6 Gb

Position 3 (Output)		
Selected option		Description
PMD55	2	4-20 mA HART
	3	PROFIBUS PA
	4	FOUNDATION Fieldbus

Optional specifications


No options specific to hazardous locations are available.


- Comply with the installation and safety instructions in the Operating Instructions.
 - Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
 - Install the device according to the manufacturer's instructions and national regulations.
 - For installation, use and maintenance of the device, users must also observe the requirements stated in the Operating Instructions and the standards:
 - GB50257-2014: "Code for construction and acceptance of electric device for explosion atmospheres and fire hazard electrical equipment installation engineering".
 - GB3836.13-2013: "Explosive atmospheres, Part 13: Equipment repair, overhaul and reclamation".
 - GB/T 3836.15-2017: "Explosive atmospheres, Part 15: Electrical installations design, selection and erection".
 - GB/T 3836.16-2017: "Explosive atmospheres, Part 16: Electrical installations inspection and maintenance".
 - Only use the device in media to which the wetted materials have sufficient durability.
 - Avoid electrostatic charging:
 - Of plastic surfaces (e.g. housing, sensor element, special varnishing, attached additional plates, ..)
 - Of isolated capacities (e.g. isolated metallic plates)

Safety instructions: General

Safety instructions: Special conditions

- For light metal flanges or flange faces (e.g. titanium, zirconium), avoid sparks caused by impact and friction.
- In the event of additional or alternative special varnishing on the housing or other metal parts:
 Observe the danger of electrostatic charging and discharge.
 - Do not rub surfaces with a dry cloth.





- A Zone 1, Electronic
- B Zone 1, Process
- 1 Power supply U
- 2 PMD55
- In potentially explosive atmospheres: Do not open the connection compartment cover and the electronics compartment cover when energized.
- Before operation:
 - Screw in the cover all the way.
 - Tighten the securing clamp on the cover.
- Connect the device:
 - Using suitable cable and wire entries of protection type "Flameproof Enclosure (Ex d)".
 - Using piping systems of protection type "Flameproof Enclosure (Ex d)".
- When connecting through a conduit entry approved for this purpose, mount the associated sealing unit directly at the housing.
- For ambient temperatures higher than +70 °C, use suitable heat resisting cables or wires.
- Seal unused entry glands with supplied metal blind plug. Alternative use only suitable, separate approved Ex d blanking elements.
- The plastic sealing plug is used only as transport protection.

Temperature tables

Temperature class	Process temperature T _p (process)	Ambient temperature $\mathrm{T_a}$ (ambient): housing
Т6	≤ 80 °C	$-40 \degree C \le T_a \le +75 \degree C$
T4	≤ 120 °C	

Do not exceed the max. ambient temperature at the housing.

The process temperatures refer to the temperature at the separation membrane.

Connection data

Basic specification, Position 3 (Output) = 2

Power supply	
$\begin{array}{l} U \leq 45 \ V_{DC} \\ P \leq 1.1 \ W \end{array}$	

Basic specification, Position 3 (Output) = 3, 4

Power supply	
$\begin{array}{l} U \leq 32 \ V_{DC} \\ P \leq 1.25 \ W \end{array}$	



www.addresses.endress.com

