Safety Instructions Micropilot S FMR540

4-20 mA HART

Ex ia IIC T6...T1 Ga/Gb

Document: XA01739F-A

Safety instructions for electrical apparatus for explosion-hazardous areas \rightarrow $\stackrel{ all}{=}$ 3



Micropilot S FMR540 XA01739F-A

Micropilot S FMR540

4-20 mA HART

Table of contents

Associated documentation
Supplementary documentation
Manufacturer's certificates
Manufacturer address
Extended order code
Safety instructions: General
Safety instructions: Special conditions
Safety instructions: Installation
Safety instructions: Zone 0
Temperature tables
Connection data

XA01739F-A Micropilot S FMR540

Associated documentation

This document is an integral part of the following Operating Instructions:

BA00326F/00

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Media Type: Documentation -> Documentation Type: Brochures and catalogs -> Text Search: CP00021Z
- On the CD for devices with CD-based documentation

Manufacturer's certificates

Certificate of Conformity

Certificate number: CML 19IPN2474X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

JNIOSH-TR-46-1:2015JNIOSH-TR-46-6:2015IEC 60079-26:2014

Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FMR540 - ********* + A*B*C*D*E*F*G*..

(Device type) (Basic specifications) (Optional specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

Micropilot S FMR540 XA01739F-A

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Micropilot S



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

FMR540

Basic specifications

Position 1 (Approval)				
Selected option		Descr	iption	
FMR540	M	JPN E	x ia IIC T6T1 Ga/Gb	

Position 2 (Antenna; Seal)				
Selected option		Description		
FMR540 E, 5		Horn (different sizes)		
	G, H, 6	Parabolic (different sizes)		

Optional specifications

No options specific to hazardous locations are available.

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. housing, sensor element, special varnishing, attached additional plates. ..)
 - Of isolated capacities (e.g. isolated metallic plates)
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the electronics housing, depending on the range of application and the temperature class.


Safety instructions: Special conditions

Permitted ambient temperature range at the electronics housing:

- $-40~^{\circ}\text{C} \le T_a \le +80~^{\circ}\text{C}$
- Observe the information in the temperature tables.
- In the event of additional or alternative special varnishing on the housing or other metal parts:
 - Observe the danger of electrostatic charging and discharge.
 - Do not rub surfaces with a dry cloth.
- Avoid electrostatic charging of the antenna (e.g. friction, cleaning, maintenance, strong medium flow).

XA01739F-A Micropilot S FMR540

Safety instructions: Installation



A003644

■ 1

- 1 Tank; Hazardous area Zone 0
- 2 Housing
- 3 Certified associated apparatus (supply circuit)
- 4 Certified associated apparatus (signal circuit)
- 5 Tank; Hazardous area Zone 1
- 6 Local potential equalization
- After aligning (rotating) the housing, retighten the fixing screw.
- Continuous service temperature of the connecting cable: $\geq T_a + 5 \text{ K}$.
- The intrinsically safe input and output power circuits of the device are isolated from ground.
 The dielectric strength to earth is limited by 600 V electrode arresters.
- The device is equipped with an internal overvoltage protector (600 V electrode arresters). Connect the metallic housing to the tank wall directly with an electrically conductive lead to ensure reliable potential matching.
- Option:
 - Remote display, e.g. FHX40 (Observe Safety Instructions)
- Overvoltage protector, e.g. HAW56x
- Option (only for service purposes):

Service interface: Commubox with associated ToF cable (Observe Safety Instructions)

Alignment device with center nut

After the alignment of the antenna: Tighten the center nut with a torque between 65 Nm and 85 Nm.

Air purge connection


- \blacksquare In the closed state the minimum degree of protection of the installation must be IP67.
- Purging pressure > internal pressure of the tank.
- In the not purging state a respective stop cock or valve must be closed. With open stop cock or valve and without purging fluid explosible atmospheres may be released or flames may enter from the outside.

Intrinsic safety

- When the device is connected to an intrinsically safe circuit Ex ib, the type of protection changes to Ex ib. Do not operate intrinsically safe circuits Ex ib in Zone 0.
- When the device is connected to an intrinsically safe circuit Ex ic, the type of protection changes to Ex ic. Do not operate intrinsically safe circuits Ex ic in Zone 0 or Zone 1.
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.

Micropilot S FMR540 XA01739F-A

Overvoltage protection



A0026444

₽ 2

- 1 Tank; Hazardous area Zone 0
- 2 <1000 mm, e.g. armoured hose
- 3 Separate housing with overvoltage protector, e.g. HAW562Z; Metal housing
- 4 Cable with screening or metal sheath
- 5 Certified associated apparatus (supply circuit)
- 6 Certified associated apparatus (signal circuit)
- 7 Potential equalization connection
- 8 Potentiel equalization line
- 9 Potential equalization

If there is a risk of dangerous potential differences within Zone 0 (e.g. through the occurrence of atmospheric electricity), implement suitable measures for intrinsically safe circuits in Zone 0.

Overvoltage protector HAW56xZ

- Connect the external overvoltage protector and the device to the local potential equalization.
- Establish potential matching both inside and outside of the explosion-hazardous area.
- The cable connecting the overvoltage protector and the measuring device shall be no longer than 1 m.
- Route cable protected (e.g. in an armoured hose).

Safety instructions: Zone 0

- In the event of potentially explosive vapor/air mixtures, only operate the device under atmospheric conditions.
 - Temperature: -20 to +60 °C
 - Pressure: 80 to 110 kPa (0.8 to 1.1 bar)
 - Air with normal oxygen content, usually 21 % (V/V)
- If no potentially explosive mixtures are present, or if additional protective measures have been taken, the device may also be operated under non-atmospheric conditions in accordance with the manufacturer's specifications.
- Associated devices with galvanic isolation between the intrinsically safe and non-intrinsically safe circuits are preferred.

XA01739F-A Micropilot S FMR540

Temperature tables

Permitted process temperature range at the antenna: –40 °C \leq T_a \leq +200 °C

Zone 1 - Application

Temperature class	Max. permitted temperature at the antenna (Zone 1)	Max. permitted temperature at the electronics housing (Zone 1) dependent on the medium temperature
Т6	+80 °C +60 °C	+55 °C +60 °C
T5	+95 ℃ +75 ℃	+70 °C +75 °C
T4	+130 °C +80 °C	+75 °C +80 °C
T3	+195 °C +140 °C	+70 °C +75 °C
T2, T1 1)	+200 °C	+70 °C

1) Functional: Maximum permissible process temperature

Zone 0 - Application

Temperature class	Max. permitted temperature at the antenna (Zone 0)	Max. permitted temperature at the electronics housing (Zone 1) dependent on the medium temperature
Т6	+60 °C	+60 °C
T5	+60 °C	+75 °C
T4, T3, T2, T1	+60 °C	+80 °C

Connection data

Power supply and signal circuit with protection type: intrinsic safety Ex ia IIC, Ex ia IIB. Certified intrinsically safe circuit with the following maximum values

Power supply	
Power circuit	$\begin{split} &U_i = 30 \text{ V} \\ &I_i = 300 \text{ mA} \\ &P_i = 1 \text{ W} \end{split}$
	$L_i = 13.0 \ \mu H$ $C_i = 18.5 \ nF$
Signal circuit	$\begin{split} &U_i=30~V\\ &I_i=300~mA\\ &P_i=1~W\\ &\text{effective inner inductance}~L_i=0\\ &\text{effective inner capacitance}~C_i=20.7~nF \end{split}$

Micropilot S FMR540 XA01739F-A

Option

Remote display, e.g. FHX40:

Power supply and signal circuit with protection type: intrinsic safety Ex ia IIC, Ex ia IIB.

Power supply

 $U_0 = 4.2 \text{ V}$

 $I_0 = 34 \text{ mA}$

 $P_0 = 36 \text{ mW}$

effective inner inductance L_{i} = negligible effective inner capacitance C_{i} = negligible

Characteristic curve: linear

Only for service purposes:

Connecting the Commubox service interface with the associated ToF cable

Commubox output + ToF cable

 $U_0 = 3.74 \text{ V}$

 $I_0 = 9.9 \text{ mA}$

 $P_0 = 9.2 \text{ mW}$

effective inner inductance L_i = negligible

effective inner capacitance \hat{C}_i = negligible

Characteristic curve: linear

For material group IIC:

- permitted outer inductance $L_o \le 340 \text{ mH}$ ■ permitted outer capacitance $C_o \le 100 \text{ \muF}$

When interconnected to a Micropilot S, the following results apply:

	L _o =	0.15 mH	0.5 mH	1 mH	2 mH	5 mH
For material group IIC	C _o =	≤ 8 µF	≤ 7 µF	≤ 5.5 µF	≤ 5 µF	≤ 4 µF
For material group IIB	C _o =	10 μF				





www.addresses.endress.com