

CERTIFICATE OF CONFORMITY



1. **HAZARDOUS (CLASSIFIED) LOCATION ELECTRICAL EQUIPMENT PER US REQUIREMENTS**

2. **Certificate No:** FM20US0076X
3. **Equipment:** iTEMP type TMT18a
(Type Reference and Name) Temperature Head Transmitter
4. **Name of Listing Company:** Endress+Hauser Wetzer GmbH + Co. KG
5. **Address of Listing Company:** Obere Wank 1
D-87484 Nesselwang
Germany

6. The examination and test results are recorded in confidential report number:

3005591 dated 16th August 2000

7. FM Approvals LLC, certifies that the equipment described has been found to comply with the following Approval standards and other documents:

FM Class 3600:2018, FM Class 3610:2018, FM Class 3611:2018, FM Class 3810:2018,
ANSI/UL 121201:2018, ANSI/ISA 60079-0:2009, ANSI/ISA 60079-11:2009,
ANSI/ISA 61010-1:2012

8. If the sign 'X' is placed after the certificate number, it indicates that the equipment is subject to specific conditions of use specified in the schedule to this certificate.
9. This certificate relates to the design, examination and testing of the products specified herein. The FM Approvals surveillance audit program has further determined that the manufacturing processes and quality control procedures in place are satisfactory to manufacture the product as examined, tested and Approved.

Certificate issued by:

J. E. Marquedant
VP, Manager - Electrical Systems

13 July 2020

Date

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

SCHEDULE

US Certificate Of Conformity No: FM20US0076X



10. Equipment Ratings:

Intrinsically Safe for Class I, Division 1, Groups A, B, C and D; T*

Non-incendive for Class I, Division 2, Groups A, B, C and D; T*

Class I, Zone 0 AEx ia IIC; T*

T* = T6 Ta = -40°C to +55°C, T5 Ta = -40°C to +70°C, T4 Ta = -40°C to +85°C

11. The marking of the equipment shall include:

Class I, Division 1, Groups A, B, C and D; T*, 14 05 00 111 Entity

Class I, Division 2, Groups A, B, C and D; T*, 14 05 00 111 NIFW

Class I, Zone 0 AEx ia IIC; T*, 14 05 00 111 Entity

T* = T6 Ta = -40°C to +55°C, T5 Ta = -40°C to +70°C, T4 Ta = -40°C to +85°C

12. Description of Equipment:

General - The head transmitter iTEMP type TMT18a is a 2-wire transmitter with an analog output. It has measuring input for resistance thermometers (RTD) in 2-, 3- or 4-wire connection, thermocouples and voltage transmitters.

Ratings -

Entity/ Non-Incendive Wiring Parameters:

		Vmax	I _{max}	Pi	Ci	Li
	Groups	(V)	(mA)	(mW)	(μF)	(mH)
Terminals 1(+) and 2 (-)	A/B	30	100	750	0	0

Maximum Output Entity Parameters:

		Voc	Isc	Po	Ca	La
	Groups	(V)	(mA)	(mW)	(nF)	(mH)
Terminals 3, 4, 5, and 6	A/B	8.2	4.5	9.36	974	4.5

iTEMP type TMT18a Head Transmitters
a = Configuration 1, 7, or 8.

13. Specific Conditions of Use:

1) The equipment shall be installed in compliance with the enclosure, mounting, spacing and segregation requirements of the ultimate application.

14. Test and Assessment Procedure and Conditions:

This Certificate has been issued in accordance with FM Approvals US Certification Requirements.

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA

T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com

SCHEDULE

US Certificate Of Conformity No: FM20US0076X



15. Schedule Drawings

A copy of the technical documentation has been kept by FM Approvals.

16. Certificate History

Details of the supplements to this certificate are described below:

Date	Description
16 th August 2000	Original Issue.
13 th July 2020	<u>Supplement 3:</u> Report Reference: – RR224070 dated 13 th July 2020. Description of the Change: Updated FM standards to the latest editions. Added ANSI/UL 121201 and ANSI/ISA 61010-1. Updated Certificate format with new unique certificate number. Added T5 and T6 T-Codes and associated temperature ranges to match approval and labels.

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmaprovals.com www.fmaprovals.com