Safety Instructions **Nivotester FTC325**

II (1) G [Ex ia Ga] IIC
II (1) D [Ex ia Da] IIIC







Nivotester FTC325 XA02589F-A

Nivotester FTC325

Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Manufacturer address	4
Other standards	4
Extended order code	5
Safety instructions: General	6
Safety instructions: Special conditions	7
Safety instructions: Installation	7
Temperature tables	9
Connection data	9

XA02589F-A Nivotester FTC325

Associated documentation

This document is an integral part of the following Operating Instructions:

TI00380F/00. KA00221F/00

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

 In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP000217.

• On the CD for devices with CD-based documentation

Manufacturer's certificates

UK Declaration of Conformity

Declaration Number: UK 00242

The UK Declaration of Conformity is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Declaration -> Type: UKCA Declaration -> Product Code: ...

UKCA type-examination certificate

Certificate number: CML 21UKEX2455

List of applied standards: See UK Declaration of Conformity.

Manufacturer address

Endress+Hauser SE+Co. KG Hauptstraße 1 79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Other standards

Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres Explosion prevention and protection - Part 1: Basic concepts and methodology"

Nivotester FTC325 XA02589F-A

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FTC325	-	******	+	A*B*C*D*E*F*G*
(Device		(Basic		(Optional
type)		specifications)		specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Nivotester



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

FTC325

XA02589F-A Nivotester FTC325

Basic specifications

Position 1 (Approval)				
Selected option		Description		
FTC325	4	UK Ex II (1) G [Ex ia Ga] IIC, WHG UK Ex II (1) D [Ex ia Da] IIIC, WHG		

Position 2 (Input, Housing)				
Selected option		Description		
FTC325	1	2-wire PFM; 45mm, DIN Rail		

Position 3 (Power Supply)				
Selected option		Description		
FTC325	А	85-253 VAC		
	В	20-30 VAC / 20-60 VDC		

Position 4 (Switch Output)				
Selected option		Description		
FTC325	1	1x SPDT level + 1x SPST alarm N.C. (normal closed)		
	2	1x SPDT level + 1x SPST alarm N.O. (normal open)		

Optional specifications

No options specific to hazardous locations are available.


Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - $\ \, \blacksquare$ Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging.
- Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.

Nivotester FTC325 XA02589F-A

Safety instructions: Special conditions To avoid electrostatic charging: Do not rub surfaces with a dry cloth.


Safety instructions: Installation



■ 1

- 1 PFM sensor, Limit level Ex ia IIC/IIB
- 2 PFM sensor
- Level relay 3
- Fault signal relay/Level relay
- Power supply

XA02589F-A Nivotester FTC325



A0034678

№ 2

- A Min. 6 mm
- 1 Intrinsically safe contacts
- 2 Nivotester FTC325
- *3 Other type, other product*
- To achieve an ingress protection of at least IP55: Protect the device from dust and humidity, e.g. in control rooms, or located in a suitable protective enclosure.
- The device is an associated apparatus: Only use the device outside explosion hazardous areas.
- If an intrinsically safe circuit is connected to the device passes through dust explosion-hazardous areas of Zones 20 or Zone 21, make sure that the devices connected to this circuit meet the requirements of categories 1 D or 2 D and are certified accordingly.
- There must be a distance (thread measure) of at least 50 mm between intrinsically safe and nonintrinsically safe terminals.
- When combining the device with other types and products on the same top-hat rail: Keep the distances comply to the relevant standards and rules.
- When combining with devices from other manufacturers: Observe ingress protection of the enclosure.

Intrinsic safety

- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- The intrinsically-safe input circuits are galvanically isolated from other circuits up to a peak value of the nominal voltage of 375 V.

Nivotester FTC325 XA02589F-A

Temperature tables

Ambient temperature ra	nge	
Individual installation	$-20^{\circ}\text{C} \le \text{T}_{\text{a}} \le +60^{\circ}\text{C}$	
Series installation	$-20^{\circ}\text{C} \le \text{T}_{\text{a}} \le +50^{\circ}\text{C}$	

Connection data

Power supply circuit		
Terminal connections: 1, 2	AC voltage	$U = 85 \text{ to } 253 \text{ V}_{AC}, 50/60 \text{ Hz}$ $P \le 6.0 \text{ VA}$
	DC voltage	$U = 20 \text{ to } 60 \text{ V}_{DC}$ $U = 20 \text{ to } 30 \text{ V}_{AC}$, 50/60 Hz $P \le 2.0 \text{ W}$

Contact circuit				
Level relay Terminal connections: 22, 23, 24	$U \leq 250~V_{AC},~I \leq 2~A,~P \leq 500~VA~at~cos~\phi \geq 0.7$ $U \leq 40~V_{DC},~I \leq 2~A,~P \leq 80~W$			
Fault signal relay Terminal connections: 15, 16	$\begin{split} &U \leq 250 \ V_{AC}, I \leq 2 \ A, P \leq 500 \ VA \ at \cos \phi \geq 0.7 \\ &U \leq 40 \ V_{DC}, I \leq 2 \ A, P \leq 80 \ W \\ &optionally \ NC \ or \ NO, \rightarrow \ \blacksquare \ 1, \ \trianglerighteq \ 7 \end{split}$			

Sensor circuit					
Terminal connections: 11, 12	Connection data:	$U_0 \le 13.9 \text{ V}$ $I_0 \le 99 \text{ mA}$ $P_0 \le 874 \text{ mW}$ Trapezium-shaped cha		$\begin{aligned} R_i &\geq 391 \ \Omega \\ C_i &= 138 \ nF \\ L_i &= 0.13 \ mH \end{aligned}$ aracteristic	
		[Ex ia Ga] IIC		[Ex ia Ga] IIB [Ex ia Da] IIIC	
		L _o	C _o	L _o	C _o
	Max. external capacitance at max.	0.85 mH	0.18 μF	0.85 mH	2.06 μF
	external inductance	0.35 mH	0.26 μF	4.85 mH	1.06 μF
	Max. external capacitance or max. external inductance	3.50 mH	0.60 μF	14.3 mH	4.56 μF
If using explosion		[Ex ib Gb] IIC		[Ex ib Gb] IIB	
protection group [Ex ib Gb] IIC/IIB		Lo	C _o	Lo	C _o
the application is limited to II (2) G or EPL Gb	Max. external capacitance or max. external inductance	3.50 mH	0.60 μF	14.3 mH	4.56 µF





www.addresses.endress.com