
Technical Information Condumax CLS13

Conductivity sensor for high-temperature applications



Application

The sensor measures conductivity in water or steam circuits, such as in the power plant and energy industry:

- Condensate monitoring
- Boiler feedwater monitoring
- Boiler blowdown monitoring

The sensor can be used in all applications with a low conductivity and very high temperatures and pressures.

Sensor versions with explosion protection approval according to ATEX, FM or CSA are suitable for use in hazardous areas.

Your benefits

- Reliable and accurate measured values at low conductivities
- Optimized for high pressures and temperatures up to 250 °C (482 °F)
- Easy to clean thanks to stainless steel body and removable outer electrode
- Robust design for maximum durability
- Quality certificate with information on individual cell constants






Conductivity of liquids is determined with a measuring

arrangement where two electrodes are located in the medium. An alternating voltage that causes a current to flow through the medium is applied at these electrodes. The electrical resistance, or its reciprocal value - conductance G - is calculated based on Ohm's law. The specific conductance κ is determined from the conductance value using the cell constant k, which

depends on the sensor geometry.



Function and system design


Measuring principle

■ 1 Conductive measurement of conductivity

- AC Alternating voltage source
- *I* Current intensity measurement
- U Voltage measurement

Measuring system

- A complete measuring system consists of the following components at least:
- The contacting conductivity sensor CLS13
- A transmitter, e.g. Liquiline M CM42
- A measuring cable, e.g. CYK71 for analog sensors



- 2 Example of a measuring system
- 1 Sensor CLS13
- 2 Transmitter CM42
- 3 Sensor cable
- 4 Pipe nozzle, process connection

Dependability

Reliability

Electrodes

The sensor has particularly large coaxial measuring electrodes. This enables fast medium throughput and a high level of measuring accuracy.

Temperature compensation

In addition, a Pt 100 temperature sensor is integrated in the inner electrode. The high thermal conductivity of the sensor means that the temperature adjusts quickly to the fluid temperature. This enables precise temperature compensation using the connected transmitter.

Robustness

The sensor is characterized by excellent thermal, chemical and mechanical resistance properties.

Use in superheated steam and ultrapure water

Special materials are available for these applications. A nominal operating life cannot be indicated for the FFKM standard material in these cases.


Input

Measured variables	ConductivityTemperature	
Measuring ranges	Conductivity	(in relation to water at 25 °C (77 °F))
	CLS13 -A	0.04 to 20 μS/cm
	CLS13 -B	0.10 to 200 μS/cm
	Temperature	
	CLS13	-20 to 250 °C (-4 to 480 °F)

Power supply

Electrical connection

The sensor is connected via the fixed cable or via the measuring cable CYK71 with a shield. The wiring diagram is provided in the Operating Instructions of the transmitter used.




- ☑ 3 Measuring cable CYK71
- 1 Coax BK, shield (outer electrode)
- 2 Coax, inner, conductivity (inner electrode)
- Pt100 Temperature
- 3 Outer shield, pay attention to the wiring diagram of the transmitter
- n.c. Do not connect

A VMB junction box and another CYK71 cable are required for the cable extension.

	Installation
Installation instructions	1. Mount the sensor directly on a process connection that matches the version or alternatively install it in a CLA751 flow assembly.
	2. Ensure that the electrodes are fully immersed in the medium during measurement.The insertion depth must be at least 50 mm (1.97 in).
	 If using the sensor in the ultrapure water range: Work under air-evacuated conditions. This prevents CO₂ in the air from dissolving in the water and increasing the conductivity by up to 3 µS/cm as a result of (weak) dissociation.

Environment

Ambient temperature range	-20 to 60 °C (-4 to 140 °F)
Storage temperature	-25 to +80 °C (-10 to +180 °F)
Degree of protection	IP67



Mechanical pressure-temperature resistance

A0048119

Design, dimensions		
	1	
	7	
		[1] AF 60
		AF 60 *(L6:
	6	G1 / NPT 1"
	5	<u> </u>
		A0046763 A0046764
	☑ 5 Design	E 6 Dimensions in mm (in)
	 Terminal head Cable connection 	* Minimum immersion depth
	3 Dissipator	
	 4 Sealing surface as per DIN 3852 B. 5 Electrodes (coaxially arranged) 	I 2, Form A
	5 Electrodes (coaxially arranged)6 Threaded connection	
	7 Nameplate	
Weight	Approx. 1.7 kg (3.75 lbs) dependin	ng on version
Materials (in contact with	Electrodes	Stainless steel 1.4571 (AISI 316Ti)
medium)	Process connection	Stainless steel 1.4571 (AISI 316Ti)
	Terminal head	Die-cast aluminum
	Dissipator	Die-cast aluminum
	Seals	FFKM
	Insulator body	Ceramic
Process connections	Thread G1	
	NPT 1" thread	
Cell constant	CLS13 -A	$k = 0.01 \text{ cm}^{-1}$
	CLS13 -B	$k = 0.1 \text{ cm}^{-1}$
Temperature sensor	Pt 100 (class B as per IEC 60751)	
Temperature sensor	Ft 100 (class D as per IEC 00751)	

Mechanical construction

Ordering information

Product page	www.endress.com/cls13	
Product Configurator	1. Configure : Click this button on the product page.	
	2. Select Extended selection .	
	← The Configurator opens in a separate window.	

	 Configure the device according to your requirements by selecting the desired option for ea feature. 	
	└ In this way, you receive a valid and complete order code for the device.	
	4. Apply : Add the configured product to the shopping cart.	
	For many products, you also have the option of downloading CAD or 2D drawings of the selected product version.	
	5. Show details : Open this tab for the product in the shopping cart.	
	The link to the CAD drawing is displayed. If selected, the 3D display format is displayed along with the option to download various formats.	
Scope of delivery	The scope of delivery includes:Sensor in the version orderedOperating Instructions	
	Accessory	


The following are the most important accessories available at the time this documentation was issued.

► For accessories not listed here, please contact your Service or Sales Center.

Device-specific accessories Assemblies

Flow assembly CLA751


- For installing conductivity sensors with G1 thread (CLS12, CLS13, CLS21, CLS30)
- Inlet (below) and outlet (lateral) DN 20 with G1 thread adapter nut
- Stainless steel 1.4571 (AISI 316Ti)
- Max. temperature 160 °C (320 °F), max. pressure 12 bar (174 psi)
- Order No. 50004201



☑ 7 Dimensions in mm (inch)

Flow assembly CLA752

- For installing conductivity sensors with G1 thread (CLS12, CLS13, CLS21, CLS30)
- Inlet (lateral) and outlet (lateral) DN 20 with G½ internal thread
- Polypropylene (PP)
- Max. temperature 90 °C (194 °F), max. pressure 6 bar (87 psi)
- Order No. 50033772



B Dimensions in mm (inch)

Measuring cable

Measuring cable CYK71

- Unterminated cable for connecting analog sensors and for extending sensor cables
- Sold by the meter, order numbers:
 - Non-Ex version, black: 50085333
 - Ex-version, blue: 50085673

Junction boxes

VBM

- Junction box for cable extension
- 10 terminal strips
- Cable entries: 2 x Pg 13.5 or 2 x NPT ¹/₂"
- Material: aluminum
- Degree of protection: IP 65
- Order numbers
 - Cable entries Pg 13.5 : 50003987
 - Cable entries NPT ¹/₂": 51500177

VBM-Ex

- Junction box for cable extension in hazardous area
- 10 terminal strips (blue)
- Cable entries: 2 x Pg 13.5
- Material: aluminum
- Order number: 50003991

Service-specific accessories	Calibration solutions
	 Conductivity calibration solutions CLY11 Precision solutions referenced to SRM (Standard Reference Material) by NIST for qualified calibration of conductivity measuring systems in accordance with ISO 9000 CLY11-A, 74 μS/cm (reference temperature 25 °C (77 °F)), 500 ml (16.9 fl.oz) Order No. 50081902 CLY11-B, 149.6 μS/cm (reference temperature 25 °C (77 °F)), 500 ml (16.9 fl.oz) Order No. 50081903
	Technical Information TI00162C

Calibration set

Conducal CLY421

- Conductivity calibration set (case) for ultrapure water applications
- Complete, factory-calibrated measuring system with certificate, traceable to SRM by NIST and PTB, for comparison measurement in ultrapure water up to max. $20 \ \mu$ S/cm
- Product Configurator on the product page: www.endress.com/cly421

Technical Information TI00496C/07/EN



www.addresses.endress.com

