

CERTIFICATE

(1) EU-Type Examination

(2) **Equipment or protective systems intended for use in potentially explosive atmospheres - Directive 2014/34/EU**

(3) EU-Type Examination Certificate Number: **KEMA 03ATEX1448 X** Issue Number: **11**

(4) Product: **Converter, Temperature and Water Level Transmitter Prothermo Type NMT 539-B and Average Temperature Transmitter Prothermo Type NMT 532-B**

(5) Manufacturer: **Endress+Hauser Yamanashi Co., Ltd.**

(6) Address: **862-1 Mitsukunugi Sakaigawa-cho, Fuefuki-shi Yamanashi Pref. 406-0846, Japan**

(7) This product and any acceptable variation thereto is specified in the schedule to this certificate and the documents therein referred to.

(8) DEKRA Certification B.V., Notified Body number 0344 in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of products intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in confidential test report number NL/KEM/ExTR10.0061/06.

(9) Compliance with the Essential Health and Safety Requirements has been assured by compliance with:

EN IEC 60079-0 : 2018

EN 60079-11 : 2012

EN 60079-26 : 2015

except in respect of those requirements listed at item 18 of the Schedule.

(10) If the sign "X" is placed after the certificate number, it indicates that the product is subject to the Specific Conditions of Use specified in the schedule to this certificate.

(11) This EU-Type Examination Certificate relates only to the design and construction of the specified product. Further requirements of the Directive apply to the manufacturing process and supply of this product. These are not covered by this certificate.

(12) The marking of the product shall include the following:



**II 1/2 G Ex ia IIB T6...T2 Ga/Gb or
II 2 G Ex ia IIB T6...T2 Gb**

Date of certification: 19 January 2023

DEKRA Certification B.V.

R. Schuller
Certification Manager



(13) **SCHEDULE**

(14) **to EU-Type Examination Certificate KEMA 03ATEX1448 X**

Issue No. 11

(15) **Description**

Prothermo NMT 539-B Series Converters, Temperature and Water Level Detectors and Prothermo NMT 532-B Series Average Temperature Transmitters are used either for average temperature measurement, using a separate or an integral temperature probe, or for the measurement of the water interface level at the bottom of a tank, or for combinations of these measurements.

The maximum lengths of measurement probes are 99999 mm for NMT 539-B series, and 40000 mm for NMT 532-B series, respectively.

The output signal is a 4 - 20 mA current with digital communication (HART).

Ambient temperature range -40 °C to +85 °C.

The relation between the ambient temperature, the process temperature and the temperature class is shown in the following table:

Temperature class	Ambient temperature	Process temperature (sensor)	
		Temperature measurement only	Temperature measurement and water level or water level only
T6	≤ 60 °C	≤ 60 °C	≤ 60 °C
T5	≤ 85 °C	≤ 80 °C	≤ 80 °C
T4	≤ 85 °C	≤ 100 °C	≤ 100 °C
T3*	≤ 85 °C	≤ 175 °C	≤ 125 °C
T2*	≤ 85 °C	≤ 235 °C	---

Note: * is applicable to Prothermo NMT 539 only.

Electrical data

All versions:

Supply and output circuit (terminals H1+ and H1-):

in type of protection intrinsic safety Ex ia IIB, only for connection to a certified intrinsically safe circuit, with the following maximum values:

$U_i = 30 \text{ V}$; $I_i = 120 \text{ mA}$; $P_i = 1 \text{ W}$; $C_i = 7,9 \text{ nF}$; $L_i = 48 \text{ }\mu\text{H}$.

Converter only:

Temperature sensor circuit (connectors CN4 and CN5, module 3):

in type of protection intrinsic safety Ex ia IIB, for connection to an external temperature probe, with following maximum values (trapezoidal characteristic):

$U_o = 8,6 \text{ V}$; $I_o = 71 \text{ mA}$; $P_o = 153 \text{ mW}$; $C_o = 9,5 \text{ }\mu\text{F}$; $L_o = 7,5 \text{ mH}$.

The level sensor circuit is connected to ground and is infallibly galvanically isolated from the supply and output circuit and from the temperature measurement circuit.

Installation instructions

The instructions provided with the product shall be followed in detail to assure safe operation.

(16) **Report Number**

No. NL/KEM/ExTR10.0061/06.

(13) **SCHEDULE**

(14) **to EU-Type Examination Certificate KEMA 03ATEX1448 X**

Issue No. 11

(17) **Specific conditions of use**

When the enclosure of the Transmitter Model Prothermo is made of aluminium, if it is mounted in an area where the use of EPL Ga equipment is required, it must be installed such, that, even in the event of rare incidents, ignition sources due to impact and friction sparks are excluded the temperature sensor tube shall not be subject to environmental stress, such as impact from moving parts, and the bottom part shall be secured.

Precautions shall be taken to minimize the risk from electrostatic discharge of painted parts.

(18) **Essential Health and Safety Requirements**

Covered by the standards listed at item (9).

(19) **Test documentation**

As listed in Report No. NL/KEM/ExTR10.0061/06.

(20) **Certificate history**

Issue 1	- 203604700	initial certificate
Issue 2...7	-	changes of electronics or constructions
Issue 8	- 420091100	change of electronics
Issue 9	- 420157500	minor constructional changes and assessment per EN 60079-26:2015
Issue 10	- 420293500	assessment per EN IEC 60079-0:2018
Issue 11	- 227048300	minor changes in nameplates and instructions