

Safety Instructions

RN22, RN42

ATEX, IECEx: II(1)G [Ex ia Ga] IIC
II(1)D [Ex ia Da] IIIC
II3G Ex ec IIC Gc



RN22, RN42

Table of contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Certificate holder	4
Safety instructions: Intrinsic safety	5
Safety instructions: Installation in Zone 2 (EPL Gc)	6
Safety instructions: Specific conditions of use	6

Associated documentation

All documentation is available on the Internet:
www.endress.com/Deviceviewer
 (enter the serial number from the nameplate).



If not yet available, a translation into EU languages can be ordered.

To commission the device, please observe the Operating Instructions pertaining to the device:

www.endress.com/<product code>, e.g. RN22

Supplementary documentation

Explosion protection brochure: CP00021Z

The explosion protection brochure is available on the Internet:

www.endress.com/Downloads

Manufacturer's certificates**IECEX certificate**

Certificate number: IECEX EPS 19.0100X, IECEX EPS 21.0016U

Affixing the certificate number certifies conformity with the following standards (depending on the device version)

- IEC 60079-0 : 2017
- IEC 60079-11 : 2011
- IEC 60079-7 : 2015

ATEX certificate

Certificate number: EPS 19ATEX1231 X

EU Declaration of Conformity

Declaration number: EC_00919, EC_00926 or EC_00901, EC_00927

The EU Declaration of Conformity is available on the Internet:

www.endress.com/Downloads

UKCA certificate

Certificate number: CML 21UKEX2998X

UKCA Declaration of Conformity


Declaration number: UK_00404, UK_00405 or UK_00414, UK_00415

Certificate holder

Endress+Hauser Wetzler GmbH + Co. KG
 Obere Wank 1
 87484 Nesselwang, Germany

Safety instructions:

Intrinsic safety



A0046146

- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and any other valid standards and regulations (e.g. EN/IEC 60079-14).
- The unit is an associated electrical apparatus and can only be installed outside the hazardous area.
- The unit must be installed in such way that a minimum ingress protection of IP 20 is achieved.
- When installing the unit care must be taken that there must be a spacing of at least 50 mm (zone radius) to the intrinsically safe terminals
- Screw tight the unused terminals for keeping the required distances between intrinsically safe circuits/terminals.

**Safety instructions:
Installation in Zone 2 (EPL Gc)**

These instructions concern the required enclosure, accessories and supply cables in final application.

- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and any other valid standards and regulations (e.g. EN/IEC 60079-14).
- Seal the cable entries tight with certified cable glands which have at least type of protection Ex ec suitable for Group IIC (degree of protection IP54).

**Safety instructions:
Specific conditions of use**

- If several devices are installed side by side, it is important to ensure that the maximum side wall temperature of the individual device of 80 °C (176 °F) is not exceeded. If this cannot be guaranteed, mount the devices at a distance from one another or ensure sufficient cooling.
- When install the unit in EPL Gc a certified enclosure shall be used providing a degree of protection of at least IP54 and compliance with the enclosure requirements to IEC/EN 60079-0.
- In an explosive atmosphere, do not open the certified enclosure when voltage is supplied (ensure that at least IP 54 is maintained during operation).
- For full certification as an electrical equipment for use in EPL Gc the tests according to IEC 60079-0:2017 section 5.2 and 5.3 have to be carried out. Based on the test results a temperature class shall be assigned.

Category	Type of protection (ATEX)
II(1)G	Ex ia Ga IIC
II(1)D	Ex ia Da IIIC

Type of protection (IECEx)
Ex ia Ga IIC
Ex ia Da IIIC
Ex ec IIC Gc

Ambient temperature: -40 to +60 °C

Type	Electrical data			
RN22, RN42	Supply RN22: terminals 1.1 (+), 1.2 (-)		U = 24V DC (-20%/+25%) Um = 250 V	
	Supply RN42: terminals 1.1 (L/+), 1.2 (N/-)		U = 24 to 230 V AC/DC (-20 %/+10 %) 50/60Hz Um = 250 V	
	Output circuit: terminal 3.1 (+), 3.2 (-) terminal 2.1 (+), 2.2 (-)		U = 30V DC I = 0/4 - 20 mA Um = 30 V	
	Input circuit: Connection 2-wire (active) RN22: terminal 4.1 (+), 4.2 (-) terminal 6.1 (+), 6.2 (-) RN42: terminal 4.1 (+), 4.2 (-)		Uo ≤ 27.3V DC Io ≤ 87.6 mA Po = 597 mW Ci = negligibly small Li = negligibly small	
	Maximum connection values			
	Single values:	Ex ia IIC Ex ia IIB Ex ia IIA	Lo = 5.2 mH Lo = 20.8 mH Lo = 44.8 mH	Co = 88 nF Co = 683 nF Co = 2280 nF
	Combined values Lo/Co:	Ex ia IIC	1.3 mH/0.05 µF; 1 mH/0.052 µF; 0.5 mH/0.065 µF	
		Ex ia IIB	26 mH/0.39 µF; 2 mH/0.44 µF; 1 mH/0.53 µF; 0.5 mH/0.64 µF; 0.2 mH/0.683 µF	
		Ex ia IIA	49 mH/1.3 µF; 20 mH/1.6 µF; 1 mH/1.8 µF; 0.5 mH/2.2 µF; 0.2 mH/2.28 µF	
	Connection 4-wire (passive) RN22: terminal 4.2 (+), 5.1 (-) terminal 6.2 (+), 5.2 (-) RN42: terminal 4.2 (+), 4.3 (-)		Uo ≤ 27.3V DC Io ≤ 10 mA Po = 68 mW Ci = negligibly small Li = negligibly small	
Maximum connection values				
Combined values Lo/Co:	Ex ia IIC	100 mH/0.065 µF; 2 mH/0.072 µF; 1 mH/0.081 µF; 0.5 mH/0.088 µF		
	Ex ia IIB	100 mH/0.48 µF; 2 mH/0.52 µF; 1 mH/0.59 µF; 0.5 mH/0.683 µF		

Type	Electrical data		
		Ex ia IIA	100 mH/1.7 μ F; 1 mH/1.9 μ F; 0.5 mH/2.28 μ F
	Connection 4-wire (passive) RN22: terminal 4.2 (+), 5.1 (-) terminal 6.2 (+), 5.2 (-) RN42: terminal 4.2 (+), 4.3 (-)		$U_i \leq 30$ V DC I_i = not applicable when keeping U_i P_i = not applicable when keeping U_i C_i = negligibly small L_i = negligibly small



71614007

www.addresses.endress.com
