



1 **EU-TYPE EXAMINATION CERTIFICATE**

2 Equipment intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU

3 Certificate Number: **CSANe 22ATEX1097X** Issue: **1**

4 Equipment: **Optograf Analyser Raman RXN5 Series Analyser**

5 Applicant: **Endress+Hauser Optical Analysis, Inc.**

6 Address: **371 Parkland Plaza
Ann Arbor,
Michigan 48103
United States of America**

7 This equipment and any acceptable variation thereto is specified in the schedule to this certificate and the documents therein referred to.

8 CSA Group Netherlands B.V., notified body number 2813 in accordance with Articles 17 and 21 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in the confidential reports listed in Section 14.2.

9 Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the schedule to this certificate, has been assured by compliance with the following documents:

EN IEC 60079-0: 2018	EN 60079-2: 2015	EN 60079-11: 2012
EN IEC 60079-7: 2015 +A1:2018	EN 60079-28: 2015	EN 50495: 2010

10 If the sign 'X' is placed after the certificate number, it indicates that the equipment is subject to Specific Conditions of Use identified in the schedule to this certificate.

11 This EU-Type Examination Certificate relates only to the design and construction of the specified equipment. If applicable, further requirements of this Directive apply to the manufacture and supply of this equipment.

12 The marking of the equipment shall include the following:



II 3 (2) (1) G
Ex ec ic [ia Ga] [op sh Gb] pzc IIC T4 Gc
Ta = -20°C to +50°C

Signed: Michelle Halliwell

Title: Director of Operations



Project Number 80186984

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

CSANe 22ATEX1097X
Issue 1

13 DESCRIPTION OF EQUIPMENT

The Optograf/ RXN5 analyser is designed to monitor, analyze, or optimize reaction chemistry in multiple vessels using the analytical technique of "Raman" spectroscopy. The equipment utilizes a computer-controlled spectrometer and laser to accomplish this.

General

The Optograf analyser (which may also be referred to as "RXN5" in addition to or as an alternative to "Optograph") consists of a steel enclosure, painted mild steel or stainless steel, which is mounted in a Zone 2 hazardous location and provides intrinsically safe and fiber-optical signals up to 4 probes located in either Zone 1 or Zone 0 hazardous areas.

The system enclosure is protected by purge and pressurization, provided by a certified [pzc] purging controller ("CYCLOPS Z" Purge Indicator) manufactured by Purge Solutions, Inc. (not part of this certification).

The purged and pressurized enclosure includes a TFT display touchscreen mounted behind a toughened glass window.

Main Enclosure Laser Output & Spectrometer Input

The laser beam within the enclosure is routed through various optical instruments before being made available at up to 4 bulkhead connectors contained within the connector box compartment. From here, fibre optic cables take the laser light to the process probe which is in contact with the process being monitored. Up to 4 probes may be connected.

The laser power level is controlled by the computer within the pressurized enclosure and monitored by the power interlock circuitry. This arrangement is 2 fault tolerant and suitable for Category 1 applications / EPL Gb.

Fibre Breakage Interlock

A special condition of safe use is listed on the certificate that the fibre optic cable must be installed taking into account the minimum bend radius specified by the cable manufacturer.

Cutting the wires or shorting them together is detected by an IS Galvanic Isolator (GM International Galvanic Isolator D1032Q – which is not part of this certification as it has its own certification) within the pressurized enclosure, which provides a volt-free relay contact for each probe to the laser power interlock mechanism, which will turn the laser off. Either a single, 4 channel isolator may be used, or up to 2 dual channel units, depending upon the system specification. The output contacts of the isolator's output channel are connected to the interlock input of the respective laser for that channel.

The arrangement for detective fibre breakage is single fault tolerant and considered to be acceptable for category 2 applications, with the exception of the Galvanic Isolator providing the IS signal to the monitoring loop.

Laser Power Interlock

The laser power is adjusted for each application so that the appropriate optical power level exits the probe. Because the length of the fibre optic cable is variable, the power input into the fibre will be higher than the power that exits from the probe.

Project Number 80186984

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

CSANe 22ATEX1097X
Issue 1

The laser power is set by the laser module and a dual channel laser power monitoring circuit is provided that checks the power level produced by the laser and turns off the laser should the power exceed the pre-set maximum limit.

The output of the laser is routed through a beam splitter that divides the light between 2 photo detectors and the main output. The interlock circuitry provides 2 separate paths where the voltage generated by the current through the photo detectors is compared against a pre-set voltage. Provided that the generated voltage is lower than the pre-set voltage and corresponding to the laser power being lower than the limit, the power to the laser shall remain connected. Consequently, if either channel of the circuit detects that the power exceeds the limit, the laser is turned off.

Variation 1 - This variation introduced the following changes:

- i. Update Rxn5 label by changing minimum overpressure rating from 0.4" to 0.2" water column.
- ii. Change adhesive label material from "3M-9502" to "3M-9472LE".

14 DESCRIPTIVE DOCUMENTS

14.1 Drawings

Refer to Certificate Annexe.

14.2 Associated Reports and Certificate History

Issue	Date	Report number	Comment
0	16 March 2023	R80069333A	The release of the prime certificate.
1	23 November 2023	R80186982A	The introduction of Variation 1.

15 SPECIFIC CONDITIONS OF USE (denoted by X after the certificate number)

- 15.1 The fibre optic cable linking the laser output to the pilot probe shall be installed so that the minimum bend radius specified by the cable manufacturer is not exceeded.
- 15.2 Where it is necessary to monitor the process level to ensure that the optical beam is not exposed to a potentially explosive atmosphere, the devices used to monitor the level shall be intrinsically safe or classed as simple apparatus and be installed so as to provide a fault tolerance of 2 for EPL Ga equipment or a fault tolerance of 1 for EPL Gb equipment. The functional safety of this arrangement has not been assessed as part of this certification and it is the responsibility of the installer/user to ensure that an appropriate mechanism is in place.
- 15.3 The user shall purge the enclosure prior to start-up and upon loss of pressurization in accordance with the instructions marks on the Optograf enclosure. An appropriate means of isolation shall be provided by the user, appropriately certified for the area of use and correctly installed.
- 15.4 Parts of the enclosure may represent an electrostatic risk. Refer to the manufacturer's instructions.
- 15.5 Where IS Galvanic Isolators are added to the main enclosure in order to produce IS signals to external apparatus not covered by this certification, the IS Galvanic Isolators shall have an ambient working temperature upper limit of at least 60°C. The IS parameters pertaining to these isolators shall be conveyed to the user in an appropriate manner. The IS nature of any such circuits has not been assessed as part of this certification and this certificate is not to be taken as indication that these IS circuits comply with relevant requirements.

Project Number 80186984

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

CSANe 22ATEX1097X
Issue 1

16 ESSENTIAL HEALTH AND SAFETY REQUIREMENTS OF ANNEX II (EHSRs)

The relevant EHSRs that are not addressed by the standards listed in this certificate have been identified and individually assessed in the reports listed in Section 14.2.

17 CONDITIONS OF MANUFACTURE

17.1 The use of this certificate is subject to the Regulations Applicable to Holders of CSA Group Netherlands B.V. certificates.

17.2 Holders of EU-Type Examination Certificates are required to comply with the conformity to type requirements defined in Article 13 of Directive 2014/34/EU.

17.3 The pressurized enclosure shall be subject to the routine tests:

- Leakage test
- Functional test of the pressurization controls and purge timer

17.4 The laser power interlock and fibre-breakage interlock systems operation shall be verified.

17.5 The equipment covered by this certificate incorporates previously certified devices; it is therefore the responsibility of the manufacturer to continually monitor the status of the certifications of the following Ex equipment:

- GM Galvanic Isolator (D1032Q) (IECEX BVS 07.0027X)
- Purge Solutions CYCLOPS Z- Purge Indicator (IECEX EXV 19.0006X)
- Hummel AG Cable Gland (IECEX BVS 07.0019X)

Project Number 80186984

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands

Certificate Annexe



Certificate Number: CSANe 22ATEX1097X
Equipment: Optograf Analyser Raman RXN5 Series Analyser
Applicant: Endress+Hauser Optical Analysis, Inc.

Issue 0

Drawing	Sheets	Rev.	Date (Stamp)	Title
2011827	1 to 3	X11	22 Sep 22	Assembly, base unit Optograf
2011828	1 of 1	X6	02 Aug 22	Purge Diagram, Optograf
2011829	1 of 1	X4	02 Aug 22	Block Diagram, Optograf Fan Unit
4002017	1 to 5	X1	02 Aug 22	Laser Power control and safety interlock
4002019	1 to 6	X1	02 Aug 22	Safety statement, RXN Invictus Laser, IS Barrier, Interlock connector and probe system
2011376	1 of 1	X3	02 Aug 22	Block Diagram, Thermal Interlock System, Optograf
2011881	1 of 1	X3	02 Aug 22	Block Diagram, Laser Interlock System, Optograf
4002315	1 to 2	R6	06 Mar 23	ATEX label, Optograf Base in Haz Zone Schematic
2017540	1 of 1	X1	02 Aug 22	Schematic, Invictus Laser with Laser Power Interlock, Alt Scheme
BA02179CEN_0121	1 to 116	0X2X	05 Oct 22	Optograf™ Analyzer Operations Manual

Issue 1

Drawing	Sheets	Rev.	Date (Stamp)	Title
4002315	1 to 2	01.23	21 Nov 23	Label Requirements Optograf Base in Haz-Zone Schematic

Project Number 80186984

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands