

PRODUCT CONFORMITY CERTIFICATE

This is to certify that the

Stationary Sampler Liquistation CSF48 & CSF33

manufactured by:

Endress+Hauser Conducta GmbH

Dieselstrasse 24

D-70839

Gerlingen

Germany

has been assessed by Sira Certification Service
and for the conditions stated on this certificate complies with:

MCERTS Performance Standards for Water Monitoring Equipment Part 1, Version 2.1 dated November 2009

Certification Ranges :

CSF48/ CSF33 Suction head 0 - 6m vacuum

CSF48/ CSF33 Suction head 0 - 8m vacuum

CSF48/ CSF33 Suction head 0 - 8m peristaltic

Project No. : 16W22425
Certificate No : Sira MC100176/02
Initial Certification : 09 November 2010
This Certificate issued : 23 July 2012
Renewal Date : 08 November 2015

R Cooper | Eng MInst MC
Technical Director

MCERTS is operated on behalf of the Environment Agency by

Sira Certification Service

12 Acorn Industrial Park, Crayford Road, Crayford
Dartford, Kent, UK DA1 4AL

Tel: +44 (0)1322 520500 Fax: +44 (0)1322 520501



This certificate may only be reproduced in its entirety and without change

Registered Office: Rake Lane, Eccleston, Chester, UK CH4 9JN

To authenticate the validity of this certificate please visit www.siracertification.com/mcerts

Approved Site Application

The Liquistation CSF48 & CSF33 sampler are suitable for use on municipal and industrial applications to take and store liquid samples.

The product is designed for mainly outdoor sites where the ambient temperature is between -20°C and +40°C. The sampler is suitable for applications where samples are biological and required to be stored at 4°C.

Any potential user should ensure, in consultation with the manufacturer, that the water monitoring system is suitable for the process on which it will be installed.

Basis of Certification

This certification is based on the following Test Report(s) and on Sira's assessment and ongoing surveillance of the product and the manufacturing process:

Sira Report Sira Report number 16W22425 dated 4/10/10

Product Certified

The Liquistation CSF48 & CSF33 sampler consist of the following parts:

- Sample intake system with vacuum or peristaltic pump
- Low voltage refrigeration system with active sample cooling
- Distribution assembly

This certificate applies to all instruments fitted with software version V 01.01.00-0001, Software Version FMSY1 V1.00.00 and FMSY1 Projecting Version V.103 (serial number DA000105D00 onwards).

Certificate No : Sira MC100176/02
This Certificate issued : 23 July 2012

*This certificate may only be reproduced in its entirety and without change
To authenticate the validity of this certificate please visit www.siracertification.com/mcerts*

Certified Performance

The instrument was evaluated for use under the following conditions:

Ambient Temperature Range: With temperature control unit: -20^oC to +40^oC
 Without temperature control unit: 0^oC to +40^oC

The following results are on the CSF48 sampler and expressed as error % reading, unless otherwise stated.

Test	Results	MCERTS specification
Sample Collection	Flow proportional, timed or quantity sampling available. Options available for single or multiple containers.	Clause 3.1.3
Sample interval <ul style="list-style-type: none"> • Time proportional sampling • Flow proportional sampling 	Possible range from 1 to 5,999 minutes. Increments of 1 minute. 4-20mA and pulse inputs available Number of pulses per sample adjustable	Clause 3.1.4 & 3.1.5
Sample failure	Fault indicated on display. The meaning of the error can be found in the diagnostic menu. Sample failures recorded.	Clause 3.1.6 & 3.1.7
Sample line diameter	Vacuum: internal diameter 10mm, 13mm, 16mm (8m only) Peristaltic: internal diameter 10mm	Clause 3.1.8 >9mm
Sample volume	Sample volume adjustable	Clause 3.1.9
Maximum volume of a discrete sample that can be set Total storage capacity both by numbers and volumes of individual bottles and in a composite container	Manual sampling: 10000ml for peristaltic, 350ml for vacuum Automatic: 10000ml for peristaltic, 350ml for vacuum Composite: 30L and 60L <u>PE</u> 1L, 2L, 3L, 5L, 13L, 20L bottles. <u>Glass</u> 1.8L bottles	Clause 3.2.1
Maximum sampling head	Vacuum 6m variant: 6m Vacuum 8m variant: 8m Peristaltic: 8m	Clause 3.2.2

Certificate No : Sira MC100176/02
 This Certificate issued : 23 July 2012

*This certificate may only be reproduced in its entirety and without change
 To authenticate the validity of this certificate please visit www.siracertification.com/mcerts*

Test	Results	MCERTS specification																				
Sample timing	Error was 5 seconds \pm 1 sec in 24 hours	Clause 6.2.4 < \pm 10 sec/24h																				
Sample Temperature Control a) Volume	<table border="0"> <tr> <td colspan="2" style="text-align: center;">U*</td> <td colspan="2" style="text-align: center;">X*</td> </tr> <tr> <td>-20°C</td> <td>2.3%</td> <td>-20°C</td> <td>0.8%</td> </tr> <tr> <td>40°C</td> <td>2.4%</td> <td>40°C</td> <td>-1.4%</td> </tr> </table>	U*		X*		-20°C	2.3%	-20°C	0.8%	40°C	2.4%	40°C	-1.4%	\pm 5%								
U*		X*																				
-20°C	2.3%	-20°C	0.8%																			
40°C	2.4%	40°C	-1.4%																			
Sample Temperature Control b) Temperature	<table border="0"> <tr> <td colspan="2" style="text-align: center;">During 24 hrs sampling:</td> <td colspan="2" style="text-align: center;">24 hrs post sampling</td> </tr> <tr> <td colspan="2" style="text-align: center;">Mean sample temp</td> <td colspan="2" style="text-align: center;">Mean sample temp</td> </tr> <tr> <td>-10 °C</td> <td>4.1 °C</td> <td>-10 °C</td> <td>-----</td> </tr> <tr> <td>20 °C</td> <td>3.7 °C</td> <td>20 °C</td> <td>-----</td> </tr> <tr> <td>40 °C</td> <td>5.0 °C</td> <td>40 °C</td> <td>3.8 °C</td> </tr> </table>	During 24 hrs sampling:		24 hrs post sampling		Mean sample temp		Mean sample temp		-10 °C	4.1 °C	-10 °C	-----	20 °C	3.7 °C	20 °C	-----	40 °C	5.0 °C	40 °C	3.8 °C	Clause 6.2.5b Maintain sample between 0°C to +5°C Annex B4 (4.1.5)
During 24 hrs sampling:		24 hrs post sampling																				
Mean sample temp		Mean sample temp																				
-10 °C	4.1 °C	-10 °C	-----																			
20 °C	3.7 °C	20 °C	-----																			
40 °C	5.0 °C	40 °C	3.8 °C																			

*X: Mean error

*U: Expanded uncertainty

Certificate No : Sira MC100176/02
This Certificate issued : 23 July 2012

*This certificate may only be reproduced in its entirety and without change
To authenticate the validity of this certificate please visit www.siracertification.com/mcerts*

Description:

The Liquistation wastewater sampler is designed for indoor or outdoor use, to collect representative liquid water samples, to monitor influent and effluent waters from municipal and industrial facilities, monitor effluent waters from indirect industrial dischargers for compliance with pre-treatment regulations, and environmental monitoring. The sampler is suitable for the representative collection of toxic and conventional pollutants.

The sampler is available with two sample intake options: Vacuum pump or peristaltic pump for collection of the liquid sample. The method of sample detection is conductive or capacitive (vacuum pump) or pressure (peristaltic pump). The intake air purge is made automatically before and after each sample. The duration automatically compensates for varying intake line lengths. The sample collection cycle is optionally repeated from one to three times if a sample is not obtained on the initial attempt. The intake line is optionally rinsed with source liquid prior to each sample from one to three times (peristaltic only).

The sampling methods with vacuum pump & peristaltic pump include event, single and multiple samples and use of the sampling table, with vacuum pump additionally includes time proportion and volume proportion sampling, and with peristaltic pump additionally includes time, volume and flow proportion sampling.

The sampler comprises a 2 door housing with 4 different cabinet materials to match all application sites. The CSF33 has options of 2 different cabinet materials. The housing is divided into a separately lockable upper sampler compartment, and lower sample collection vessel compartment. The individual samples can be collected from a wastewater channel, vessel or pipe, according to a predetermined programme. The samples taken using the CSF48 are stored into various options of detachable sample collection vessels in polyethylene or glass (60L, 30L, 2x 20L, 4x 13L, 4x 5L, 12x 3L, 12x 2L, and 24x 1L). The samples taken using the CSF33 are stored into various options of detachable sample collection vessels in polyethylene (30L, 4x 13L, 12x 3L and 24x 1L).

The user interface is self-prompting/menu driven program using four function keys, and navigator dial. The graphics display is 9 line high contrast backlit LCD making the measurements visible in direct sunlight. The sampler stores up to 100 sampling program entries while the main program can run up to 24 sub-programs at one time. The memory can store up to 8 data logbooks with each 150000 measured values and dates/times, the stored data can be visualized on the sampler display as graph or table. All other sampling activities are stored in program logbooks, and event logbooks.

The sampling pacing modes include composite and discrete multiple bottle time, multiple bottle flow, single bottle time, single bottle flow, flow with time over ride, variable interval, user start/stop, and external set point. Manual grab sample can be made to deliver a grab sample to a specific bottle location. For worldwide use the refrigerated Liquistation CSF48 can be powered by 24VDC or 90...265VAC. The Liquistation CSF33 can be powered by 90...265VAC. The standard configuration includes 2 analogue inputs, 2 binary inputs and 2 binary outputs.

Certificate No : Sira MC100176/02
This Certificate issued : 23 July 2012

*This certificate may only be reproduced in its entirety and without change
To authenticate the validity of this certificate please visit www.siracertification.com/mcerts*

General Notes

1. This certificate is based upon the equipment tested. The Manufacturer is responsible for ensuring that on-going production complies with the standard(s) and performance criteria defined in this Certificate. The Manufacturer is required to maintain an approved quality management system controlling the manufacture of the certified product. Both the product and the quality management system shall be subject to regular surveillance according to 'Regulations Applicable to the Holders of Sira Certificates'. The design of the product certified is defined in the Sira Design Schedule for certificate No. Sira MC 100176/02
2. If certified product is found not to comply, Sira Certification Service should be notified immediately at the address shown on this certificate.
3. The Certification Marks that can be applied to the product or used in publicity material are defined in 'Regulations Applicable to the Holders of Sira Certificates'.
4. This document remains the property of Sira and shall be returned when requested by the company.

Certificate No : Sira MC100176/02
This Certificate issued : 23 July 2012

*This certificate may only be reproduced in its entirety and without change
To authenticate the validity of this certificate please visit www.siracertification.com/mcerts*