



71361425

CSA Control Drawing 960014219 A

Deltabar M PMD55
 PROFIBUS PA, FOUNDATION Fieldbus

Endress+Hauser



People for Process Automation

HAZARDOUS (CLASSIFIED) LOCATION

Class I, Zone 0, IIC
 Class I, Division 1, 2, Groups A, B, C, D
 Class II, Division 1, 2, Groups E, F, G
 Class III

Any
 CSA Approved
 Associated
 Apparatus
 suitable for
 Entity-concept
 or
 FISCO-concept

Deltabar M with electronic insert for PROFIBUS PA/ FOUNDATION Fieldbus (Entity-Concept)	
U _i (V _{max}) = 24 V	T4
I _i (I _{max}) = 250 mA	T6
P _i (P _{max}) = 1.2 W	40 °C 104 °F
C _i ≤ 5 nF L _i ≤ 10 µH	70 °C 158 °F
Leakage current ≤ 50 µA	
Temperature classification	Min. ambient temp: -40 °C (optional -50 °C)

Deltabar M is suitable for the connection to a PROFIBUS PA/ FOUNDATION Fieldbus system according to the Entity- or FISCO-Concept (as described below).

FISCO-Concept

The FISCO-Concept allows interconnection of intrinsically safe apparatus to associated apparatus not specifically examined in such combination. The criteria for interconnection is that the voltage (U_i or V_{max}), the current (I_i or I_{max}) and the power (P_i or P_{max}) which intrinsically safe apparatus can receive and remain intrinsically safe, considering faults, must be equal or greater than the voltage (U_o or V_{oc} or V_t), the current (I_o or I_{sc} or I_t) and the power (P_o or P_{max}) levels which can be delivered by the associated apparatus, considering faults and applicable factors. In addition, the maximum unprotected capacitance (C_i) and inductance (L_i) of each apparatus (other than the termination) connected to the fieldbus must be less than or equal to 5 nF and 10 µH respectively.

Any
 CSA approved
 Intrinsically
 Safe Apparatus
 suitable for
 Entity-concept
 or
 FISCO concept

In each segment only one active device, normally the associated apparatus, is allowed to provide the necessary energy for the fieldbus system. The voltage U_o (or V_{oc} or V_t) of the associated apparatus has to be limited to the range of 14 V to 24 V d.c. All other equipment connected to the bus cable has to be passive, meaning that they are not allowed to provide energy to the system, except to a leakage current of 50 µA for each connected device. Separately powered equipment needs a galvanic isolation to assure that the intrinsically safe fieldbus circuit remains passive.

The cable used to interconnect the devices needs to have the parameters in the following range:
 loop resistance R : 15...150 Ohm/km inductance per unit length L : 0.4...1 mH/km
 capacitance per unit length C : 80...200 nF/km
 C = C' line/line + 0.5 C' line/screen, if both lines are floating or C' = C' line/line + C' line/screen,
 if the screen is connected to one line
 length of spur cable: 30 m length of trunk cable: 1 km length of splice: 1 m
 At each end of the trunk cable an approved infallible line termination with the following parameters is suitable:
 R = 90...100 Ohm C = 0...2.2 µF
 One of the allowed terminations might already be integrated in the associated apparatus.

NONHAZARDOUS LOCATION

Any
 CSA Approved
 Associated
 Apparatus
 suitable for
 Entity-concept
 or
 FISCO-concept

Deltabar M with electronic insert for PROFIBUS PA/ FOUNDATION Fieldbus (Entity-Concept)	
U _i (V _{max}) = 24 V	T4
I _i (I _{max}) = 250 mA	T6
P _i (P _{max}) = 1.2 W	40 °C 104 °F
C _i ≤ 5 nF L _i ≤ 10 µH	70 °C 158 °F
Leakage current ≤ 50 µA	
Temperature classification	Min. ambient temp: -40 °C (optional -50 °C)

Deltabar M with electronic insert for PROFIBUS PA/ FOUNDATION Fieldbus (FISCO-Concept)	
U _i (V _{max}) = 17.5 V	T4
I _i (I _{max}) = 500 mA	T6
P _i (P _{max}) = 5.5 W	40 °C 104 °F
C _i ≤ 5 nF L _i ≤ 10 µH	70 °C 158 °F
Leakage current ≤ 50 µA	
Temperature classification	Min. ambient temp: -40 °C (optional -50 °C)

Any CSA approved Termination with
 R = 90...100 Ω
 C = 0...2.2 µF

INTRINSICALLY SAFE.

CLASS I, DIV.1, GROUPS A,B,C,D CLASS II, DIV.1, GROUPS E,F,G CLASS III, Ex Ia IIC T6
 1. CSA certified apparatus must be installed in accordance with manufacturer instructions.
 2. CSA certified associated apparatus must meet the following requirements:
 U_o or V_{oc} or V_t ≤ U_i (V_{max}) and I_o or I_{sc} or I_t ≤ I_i (I_{max}) and P_o or P_{max} ≤ P_i (P_{max}).
 3. The maximum non-hazardous area voltage must not exceed 250 V.
 4. The installation must be in accordance with the Canadian Electrical Code or National Electrical Code (ANSI/NFPA70) and ISARP 12.06.01.
 5. Be aware of multiple earthing of screen. The screen must be connected in accordance with Canadian Electrical Code or National Electrical Code (ANSI/NFPA70) and ISARP 12.06.01.

6. Caution: Use only supply wires suitable for 5 °C above surrounding temperature.
 7. Warning: Substitution of components may impair intrinsic safety.
 8. The polarity for connecting is of no importance due to an internal rectifier.
 9. Warning: Avoid electrostatic charging of plastic surfaces, plastic process connections or coatings.

Suitable for CLASS I, DIV.2, GROUPS A,B,C,D CLASS II, DIV.1, GROUPS E,F,G.

HAZARDOUS LOCATION INSTALLATION
 1. Install per Canadian Electrical Code (CEC) or National Electrical Code (ANSI/NFPA70) and ISARP 12.06.01.

2. WARNING: Explosion Hazard - Do not disconnect equipment unless power has been switched off or the area is known to be Non-Hazardous.

AVERTISSEMENT : Risque d'explosion - Ne pas débrancher tant que le circuit est sous tension, à moins qu'il s'agisse d'un emplacement non dangereux.

WARNING: Explosion Hazard - Substitution of components may impair suitability for Class I, Div.2.

AVERTISSEMENT : Risque d'explosion - La substitution de composant peut rendre ce matériel inacceptable pour les emplacements de Class I, Div.2.

The devices are CSA Certified as Dual Seal per ANSI/ISA 12.27.01 as tabulated below; therefore installation of external secondary seals is not required.

Dual Seal	Model	Media	Annunciation in case of primary seal failure	
			Annunciation method	Pressure range for effective annunciation min
PMD55		gas	audible	MWP*
		liquid	audible/visible	160 bar (2320 psi) 3.2 bar (46.4 psi)

* Limitations of the Maximum Working Pressure (MWP) are marked on the nameplate and must be considered!