Technical Information Source Container QG2000

Radiometric Measurement



Compact transmitter for non-contact point level detection (including protection equipment) level, interface and density measurement

Application

The source container QG2000 encloses the radioactive source used for radiometric limit, level and density measurement. It allows the beam to emerge unattenuated only in one direction and gives an extremely high attenuation in all other directions. When operating with very high sensitivity rod scintillation detectors, the QG2000 provides the lowest possible radiation loads in the surrounding.

It is therefore always used if the shielding effects of smaller source containers (FQG60, FQG61, FQG62) are too low due to the high activity of the source or if no control area is permitted. The QG2000 complies to all international standards and fulfils the strict requirements of the chemical industry.

Your benefits

- Extremely high shielding ensure that no control areas are generally required and that installation in accessed areas is possible.
- Simple and safe source replacement.
- Highest safety classification for the source supplied (DIN 25426/ISO 2919, Classification C 66646).
- Additional metallic protective capsule with O-ring seal to protect the source against mechanical and chemical influences.
- Various angles of emission for optimum adaption to the application.
- Padlock for fixing the ON/OFF switch position and to protect against theft.
- Easy identification of switch status through sight glasses on the cover or by remote display with proximity switches.
- Optional with pneumatic ON/OFF circuit.



People for Process Automation

Table of Contents

Function and system design
Function
System Design 3
Attenuation factor and half-value layers
Maximum source-activity
Calculating the local dose rate or control area 3
Operating conditions4
Level Measurement 4
Density measurement 4
Ambient conditions 4
Mechanical construction5
Standard design 5
Design with remote display /
with pneumatic ON/OFF circuit
Fitting position/emission angle (when switched on) 6
Width of the beam emission channel (when switched on) 6
Weight
Housing materials
Shielding material 6
Operating elements7
Standard design 7
Design with proximity switches for remote
display of switch status
Design with pneumatic ON/OFF circuit 7
Technical Data
Pneumatic actuator
Display of switching status 7
Certificates and Approvals
РТВ
Germanischer Lloyd
Proximity switches supplied by Pepperl+Fuchs
CNSC Certificate
Ordering information9
Ordering information
Delivery
Supplementary documentation
System Information
Operating Instructions
Technical Information
Certificates
Special documentation 10

Function and system design


Function	gamma radiation. The radiation ca	led by a lead sheathing in the QG20 an only be emitted along one chann ot exceeded even with maximum a	el almost unattenuated. The limit
System Design	The stainless steel housing ensures that the radiation source and lead shielding cannot be lost when the housing is heated above the melting point of lead (tested to DIN VDE 0412-1, Section 6.4, i.e. 30 min at +800 °C (+1472 °F)). The source itself is protected from mechanical and chemical influences by a stainless steel protective capsule with an O-ring seal and can be placed in the emission channel (switching on the radiation) and removed from it (switching off) by sliding the source support rod. The mechanical resistance of the switching device has been tested according to DIN VDE 0412-1, Section 9.4. The switch position is secured by a padlock. It can easily be observed through the sight glasses from outside the container or can be transmitted to a remote electronic display in the control room. The QG2000 can also be optionally supplied with a pneumatic ON/OFF switching device.		
Attenuation factor and half-		⁶⁰ Co	¹³⁷ Cs

value layers		⁶⁰ Co	¹³⁷ Cs
2	Attenuation factor F_{S}	4.096	8.388.000
	Number of half-value layers	12	23

Maximum source-activity	⁶⁰ Co	¹³⁷ Cs
	2000 mCi respectively 74 GBq	20 Ci respectively 740 GBq

Calculating the local dose rate or control area

The control area is defined as that particular distance A from the source by which the local dose rate is attenuated to a value F_i when using an activity P.



1

QG2000 Activity of source[GBq] Ρ

 $A F_i$ Distance from source (control area) [m] Local dose rate [µSv/h]

Formula for the local dose rate Formula for the distance from source $A = \sqrt{\frac{P \cdot K}{F_i \cdot F_s}}$ $F_i = \frac{P \cdot K}{F_A \cdot F_S}$ $F_A = A^2$ for ⁶⁰Co $K = 356,7 \ \mu Sv/h \cdot m^2 \ GBq$ for ¹³⁷Cs K = 95,95 μ Sv/h \cdot m² GBq




The "Applicator" program can be used to select the source containers that suits your application. See: www.endress.com/applicator

Operating conditions


2

Level Measurement




QG2000; firm bracket (supplied by customer) = 350 kg (771,75 lbs) Detector Gammapilot M FMG60

In order to ensure stable measurement and lasting radiation protection, the QG2000 must be tightly screwed onto a rugged, low-vibration bracket that can withstand a weight of 350 kg (771.75 lbs) under all operating conditions. Additional supports are generally required when mounting directly onto the vessel. A fastening for a crane on the QG2000 is provided for transporting it.



Mechanical construction


Standard design



A Space is necessary for taking off the protective hood: see table below

The standard design can be upgraded to the designs with remote display and pneumatic ON/OFF circuit by a set.


Design with remote display / with pneumatic ON/OFF circuit



A Space is necessary for taking off the protective hood: see table below


Version	L in mm (in)	A in mm (in)
Remote display	635 (25)	145 (5.71)
Pneumatic ON/OFF circuit	735 (28.9)	245 (9.65)

Fitting position/emission angle (when switched on)



Width of the beam emission channel (when switched on)

The width of the emission channel is 6° for all designs. The emission channel is marked on the external container wall.



Weight	approx. 350 kg (771.75 lbs); for all designs
Housing materials	Stainless steel 316Ti (1.4571), for surface treated versions: Glass bead blasted Epoxy enamel coated Seawater-resistant coated
Shielding material	Lead

Operating elements

Standard design	 ON/OFF switching by manually sliding the source support rod Fixing and securing the switching status (ON/OFF) with a padlock
Design with proximity swit- ches for remote display of switch status	 Reading of the switching status through the sight glasses In addition to the sight glasses supplied, with this design the switching status is also detected by two proximity switches NJ4-12GK-SN supplied by Pepperl+Fuchs. For signal evaluation, the following isolating switch amplifiers from, e.g. Pepperl+Fuchs can be used: KFA6-SH-Ex1 (230 V AC) KFD2-SH-Ex1 (24V DC) The PG7 cable glands on the connecting box are assigned to the proximity switches on delivery. The PG9 cable gland connects the isolating switch amplifier
	$1 \rightarrow 2 \rightarrow 2 \rightarrow 4$ $2 \rightarrow 4 \rightarrow 5$
	A00196 1 From initiator 2 (OFF) 2 PG7 3 From initiator 1 (ON) 4 PG7 5 PG9
Design with pneumatic ON/ OFF circuit	 In this design: The beam is switched ON by compressed air, 4 to 6 bar (58 to 87 psi), to be connected to a G1/8" thread in the additional ring. When the pressure falls below 4 bar (58 psi) the radiation beam is automatically switched OFF. There should be a pressure relief hole to ensure automatic switch-off in all cases. Proximity switches for remote display of the switching status are built in (see above).
	Technical Data The technical data of source container QG2000 with pneumatic actuator are identical to the technica data listed in Operating Manual or Technical Information of the standard version. Additional or
Pneumatic actuator	 differing data are listed below: Comp. air connection G1/8" Actuating pressure : ON: 6 bar (87 psi)
	 OFF: 0 bar (0 psi) In unpressurised operation the QG2000 is switched off, reset by means of spring

Display of switching status	 Sight glasses in the protection hood Initiator signal 	

РТВ	Isodose curve with 60Co (37GBq/1000 mCi)	
Germanischer Lloyd	For applications on dredgers	
Proximity switches supplied by Pepperl+Fuchs	Ingress protection IP 67 to IEC 60529	
CNSC Certificate	For application in Canada the following CNSC Certificate is available: QG2000: No. 094-0159-0-2017	
	When using the CNSC Certificate, the additional Safety Instructions SD00142F/00/EN has to be observed.	

Certificates and Approvals

Ordering information

Ordering information	 Detailed ordering information is available as follows: In the Product Configurator on the Endress+Hauser website: www.endress.com → Select country → Instruments → Select device → Product page function: Configure this product From your Endress+Hauser sales center: www.endress.com/worldwide
	 Product Configurator - the tool for individual product configuration Configuration data updated on a daily basis Depending on the device: Direct input of data specific to measuring point, such as measuring range or operating language Automatic verification of exclusion criteria Automatic generation of order code with breakdown in PDF or Excel output format Possibility to order directly from the Endress+Hauser online shop
Delivery	Germany
	Padioactive sources may only be delivered when we have received a conv of the authorisation for

Radioactive sources may only be delivered when we have received a copy of the authorisation for handling radioactive materials. Endress+Hauser will gladly help you acquire the necessary documents. Please contact your nearest Sales Organisation.

For reasons of safety and cost, the radioactive source is usually shipped already loaded in the source container. Arrangements can also be made to ship the source seperately in a special transport drum. They will only be transported by approved shipping agents according to current GGVS/ADR guidelines, with all safety regulations being observed.

Other countries

Radioactive sources may only be delivered when we have received a copy of the import license. Endress+Hauser will gladly help you acquire the necessary documents. Please contact your nearest Sales Organisation.

They will only be transported by approved shipping agents according to current GGVS/ADR and DGR/IATA guidelines, with all safety regulations being observed.

System Information	 PK00001F/00/EN Radiometric measurement - Applications in all industries
Operating Instructions	 BA00223F/00/EN Operating instructions for the source container QG2000
Technical Information	 TI00363F/00/EN Technical Information for Gammapilot M FMG60 TI00439F/00/EN Technical Information for Gamma Source FSG60/61 TI01023F/00/EN Technical Information for Gammapilot FTG20
Certificates	 ZE00251F/00/EN Test certificate Germanischer Lloyd (for applications on dredgers)
Special documentation	 SD00142F/00/EN Supplementary Safety Instructions for Radioactive Sources and Source Containers approved for use in Canada. SD00276F/00/EN Supplementary Instruction Manual, especially for QG020/100 and QG2000 for the USA

Supplementary documentation



www.addresses.endress.com

